



Material	56894-540
Material description	Methanol
Grade	Accusolv™
CAS Number	67-56-1
Molecular formula	CH ₄ O
Molecular mass	32,04

Characteristics

Specifications

Assay (GC, not corrected for water)	Min. 99,9 %
Titration acid	Max. 0,0003 meq/g
Titration base	Max. 0,0002 meq/g
Residue on evaporation	Max. 1 mg/l
Water	Max. 0,05 %
Absorbance (205 nm)	Max. 1,000
Absorbance (225 nm)	Max. 0,160
Absorbance (250 nm)	Max. 0,020
Absorbance (300 nm)	Max. 0,005
Absorbance (400 nm)	Max. 0,005
Electron capture GC (Heptachlor epoxide)	Max. 10 ng/l

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Alicia Bourdeau, Head of the Laboratory - Rouses Point
VWR Chemicals, LLC, 3 Lincoln Blvd, Rouses Point, NY
12979-1045, USA