

Macco Organiques, S.R.O.

## Your mineral source for cGMP biopharmaceutical, pharmaceutical, diagnostic, and medical device applications.

Our mission at Macco Organiques is to produce high quality products that meet our customers' demands in an enthusiastic and efficient manner.

High quality has always been an absolute priority at Macco Organiques, and our products and production processes reflect this ethos. Our dedicated professional team provides a level of service admired throughout the industry, and our fine chemicals are suitable for a wide variety of life science research and production applications. Our chemicals are certified to ISO, Halal, and Kosher standards, as well as cGMP according to ICH Q7A guidelines. In addition, we are a world leader in the production of pharmaceutical and food grade Calcium Chloride Dihydrate and Magnesium Chloride Hexahydrate.



### cGMP Mineral Salts

Description	Size	Cat. No.
Ammonium Sulphate	200 g (7 oz.)	89234-892
Ammonium Sulphate	12 kg (26.5 lbs.)	89234-890
Ammonium Sulphate	50 kg (110.2 lbs.)	89370-942
Calcium Carbonate	200 g (7 oz.)	89234-898
Calcium Chloride Dihydrate	200 g (7 oz.)	89234-900
Calcium Chloride Dihydrate	12 kg (26.5 lbs.)	89234-902
Magnesium Chloride Hexahydrate	200 g (7 oz.)	89234-910
Magnesium Chloride Hexahydrate	12 kg (26.5 lbs.)	89234-906
Magnesium Sulphate, Anhydrous	200 g (7 oz.)	89234-918
Magnesium Sulphate Heptahydrate	200 g (7 oz.)	89234-914
Potassium Chloride	200 g (7 oz.)	89234-922
Potassium Chloride	12 kg (26.5 lbs.)	89234-920
Potassium Phosphate Dibasic	12 kg (26.5 lbs.)	89523-434
Potassium Phosphate Monobasic	12 kg (26.5 lbs.)	89523-436
Potassium Phosphate Monobasic	50 kg (110.2 lbs.)	89523-438
Sodium Acetate Trihydrate	200 g (7 oz.)	89234-926
Sodium Acetate Trihydrate	12 kg (26.5 lbs.)	89234-924
Sodium Bicarbonate	12 kg (26.5 lbs.)	10769-334
Sodium Bicarbonate	45.5 kg (100.3 lbs.)	89492-716
Sodium Carbonate, Anhydrous	200 g (7 oz.)	89234-930
Sodium Carbonate, Anhydrous	12 kg (26.5 lbs.)	89492-712
Sodium Carbonate, Anhydrous	45.5 kg (100.3 lbs.)	89492-714
Sodium Chloride	200 g (7 oz.)	89234-936
Sodium Chloride	12 kg (26.5 lbs.)	89234-934
Sodium Chloride	50 kg (110.2 lbs.)	10768-394
Sodium Dihydrogen Phosphate	12 kg (26.5 lbs.)	89523-442
Sodium Phosphate Dibasic, Anhydrous	12 kg (26.5 lbs.)	10755-340
Sodium Phosphate Dibasic, Anhydrous	50 kg (110.2 lbs.)	10755-746
Sodium Phosphate Dibasic Heptahydrate	12 kg (26.5 lbs.)	89523-444
Sodium Phosphate Monobasic Dihydrate	12 kg (26.5 lbs.)	89523-440
Sodium Phosphate Monobasic Monohydrate	12 kg (26.5 lbs.)	89523-446
Sodium Sulphate, Anhydrous	200 g (7 oz.)	89234-938
Sodium Sulphate, Anhydrous	12 kg (26.5 lbs.)	89234-940
Zinc Sulphate Heptahydrate	200 g (7 oz.)	89234-944
Zinc Sulphate Heptahydrate	12 kg (26.5 lbs.)	89234-946
Zinc Sulphate Monohydrate	200 g (7 oz.)	89234-948

Contact your VWR Sales Representative, Production Chemical Specialist, or call 800.932.5000 for more information.