




## Tissue Diagnostics Workflow

## CYTOLOGY





VWR Cat. No.	Product Name	Size	Stage	Directions for Use
34172-020	HARLECO® Alcohol, 100%	4 L	2 Fixation	Used to hydrate or dehydrate tissue samples in tissue processing and staining protocols.
EM1.03981.0102	M-FIX™ spray fixative	100 mL, 1 L (refill)	2 Fixation	Spray fixative for cytodiagnosis
15204-176	HARLECO® Hemacolor® Stain Set	1 PAC	3 Staining	Staining of non-gynecological specimens.
15204-178	HARLECO® Hematoxylin, Gill I	4 L	3 Staining	Nuclear staining
15204-180	HARLECO® Hematoxylin, Gill II	4 L	3 Staining	Equivalent to Gill I but double the strength. May be used for progressive or regressive staining in cytology and histology.
15204-268	HARLECO® Hematoxylin, Gill III	1 L	3 Staining	Equivalent to Gill I but triple the strength. Routine tissue staining, glycol and methylmethacrylate sections. For regressive staining.
15204-184	HARLECO® EA Solution, Gill (with Eosin and Light Green)	4 L	3 Staining	EA stain modified to exclude Bismarck Brown.
15204-186	HARLECO® Orange G Solution, Gill	4 L	3 Staining	Modification of OG-6 counterstain used in Pap staining.
15204-150	HARLECO® Hematoxylin, Harris Alum, Hg-Free	500 mL	3 Staining	Mercury-free formulation. Uses sodium iodate as an oxidizer. Nuclear stain used in routine hematoxylin and eosin staining.
15204-206	HARLECO® Papanicolaou, OG-6	4 L	3 Staining	Cytoplasmic counterstain for Pap staining technique.
15204-210	HARLECO® Papanicolaou, EA-65	4 L	3 Staining	Cytoplasmic counterstain for Pap staining technique.
15204-212	HARLECO® Papanicolaou, EA-36	4 L	3 Staining	Cytoplasmic counterstain for Pap staining technique.
15204-216	HARLECO® Papanicolaou, EA-50	4 L	3 Staining	Cytoplasmic counterstain for Pap staining technique.
EM1.09275.0500	Shorr Staining solution	500 mL	3 Staining	Diagnosis of hormonal disorders
15204-144	HARLECO® Giemsa Stain Solution, Original Azure Blend	1L	3 Staining	Specially formulated for staining G-bands of chromosomes in genetic studies.
34172-020	HARLECO® Alcohol, 100%	4 L	4 Dehydration/ Clearing	Used to hydrate or dehydrate tissue samples in tissue processing and staining protocols.
34172-022	HARLECO® Alcohol, 95%	4 L	4 Dehydration/ Clearing	Used to hydrate or dehydrate tissue samples in tissue processing and staining protocols.
34172-018	HARLECO® Blueing Reagent	4 L	4 Dehydration/ Clearing	An alkaline solution used to blue nuclear chromatin preceding differentiation in routine staining methods.
15204-266	HARLECO® Acid Alcohol, 70% (3% HCI)	1 L	4 Dehydration/ Clearing	Decolorizer for differentiating nuclear chromatin in regressive staining methods.
EM1.09843.5000	Neo-Clear®	5 L	4 Dehydration/ Clearing	Xylene substitute for histoprocessing, deparaffination, dehydration
34172-034	HARLECO® Krystalon™ Mounting Medium	300 mL, 500 mL	5 Mounting	Toulene-based. Use as a liquid coverslip or with a coverglass.
EM1.07961.0500	Entellan™ <b>NEW</b>	500 mL	5 Mounting	Rapid mounting agent, permanent slides, no bubble formation at high ambient temperatures (contains xylene)
EM1.03973.0001	M-GLAS <sup>TM</sup>	500 mL	5 Mounting	Mounting agent for the even coating of cytological smears instead of cover slips (contains toluene)



© 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. MilliporeSigma, the vibrant M, Millipore, Neo-Clear, Neo-Mount, M-Fix, M-Glas, Cytocolor and Neo- Cytocolor are registered trademarks of Merck KGaA, Darmstadt, All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

Lit. No. PF1287ENEU V-4 2018 - 16750 10/2018



800 932 5000 | VWR.COM

Prices and product details are current when published and subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit vwr.com to view our privacy policy, trademark owners, and additional disclaimers. © 2019 Avantor, Inc. All rights reserved.