

## Heated circulating baths

The versatile Optima heating circulator range consists of 4 models - 2 general purpose and 2 advanced. Combine models with any Grant stainless steel or plastic tank or use with a T-CLAMP to attach to other vertical sided tanks.

vear warranty

	General purpose		Adva	inced
	T100	TC120	TX150	TXF200
				Sogr Car
Temperature range*	amb. +5 to 100°C	amb. +5 to 120°C	amb. +5 to 150°C	amb. +5 to 200°C
Stability	±0.05°C	±0.05°C	±0.01°C	±0.01°C
Tank options	5, 12 and 18L plastic / 5, 12, 18, 26 and 38L stainless steel			
VWR catalogue number	89260-838	89260-840	89260-842	89260-844
Prices from	\$1,055.45	\$1,206.95	\$1,767.50	\$2,257.35

## Refrigerated / heating circulating baths

LT ecocool - a new range of innovative, eco friendly, refrigerated / heating circulating baths. Ready to use system supplied with insulated tubing and clips.

	LT ecocool 100	LT ecocool 150
Temperature range	amb20 to 100°C	amb25 to 150°C
Cooling power @ 20°C (W)	210	378
VWR catalogue number	10856-532	10856-534
Prices from	\$3,641.05	\$4,507.13

### Shaking water baths

Te C V

Ρ

OLS

LSB

>

- Patented, combined orbital and linear 26L shaking water bath. Supplied with universal tray.
- > Robust, linear 12L and 18L shaking water bath. Supplied with universal tray.

	LSB	OLS26
Temperature range*	amb. +5 to 99°C	amb. +5 to 99°C
Stability	±0.1°C	±0.1°C
Uniformity	±0.1°C	±0.1°C
VWR catalogue number	10128-126	10158-864
Prices from	\$3,302.70	\$4,537.25

\* Operation at or below ambient temperatures requires optional accessory cooling or a refrigeration unit.



year warranty

#### Unstirred water baths

> Basic range with a choice of 3 models. Supplied with base tray.

- General purpose water bath supplied with base tray and lid.
- Advanced water bath range supplied with base tray and lid.
- SUB AQUA PRO SBB AQUA PLUS

**JB ACADEMY** 

**JB NOVA** 

Robust boiling bath providing continuous 100°C operation.

	JB Academy	JB Academy JB Nova SUB Aqua Pro		SBB Aqua Plus
				Name of Carlos
Temperature range	amb. +5 to 95°C	amb. +5 to 95°C	amb. +5 to 99°C	100°C only
Stability	±0.5°C	±0.5°C	±0.2°C	-
Tank options	5, 12 and 18 L	5, 12, 18 and 26 L	8 models (2-34 L)	5, 12, 18 and 26 L
Drain tap	-	12, 18 and 26 L	12, 18, 26 and 34 L	12, 18 and 26 L
VWR catalogue number	10129-526	89500-368	89500-380	97055-812
Prices from	\$661.55	\$833.25	\$939.30	\$1,146.35

### **Dry block heaters**

QB\*

 General purpose dry block systems to suit most applications in the laboratory with a choice of interchangeable blocks. vear warrantv

BTD BT5D\* > Compact and flexible fixed block system for rapid and precise heating of microtubes.

> Dry block heating system for high temperature applications.

	QB series	BTD	BT5D
Temperature range	amb. +5 to 200°C (QBH2)	amb. +5 to 100°C	amb. +10 to 400°C
Stability	±0.1°C (QBD/QBH)	±0.1°C	±0.5°C
VWR catalogue number	97011-902	97011-930	71003-686
Prices from	\$888.80	\$1,146.35	\$4,034.95

## Ultrasonic baths XUBA\*\* > Entry level baths with analogue controls. Supplied with lid and wire basket. XUB\*\* > Digitally controlled range with frequency LEAP technology, reducing dead spots is



 Digitally controlled range with frequency LEAP technology, reducing dead spots and standing waves. Supplied with lid and wire basket.

	XUBA range	XUB range
	31 10	
Temperature range	amb. +5	to 70°C
Models	1 and 3 L options 5, 10, 12, 18 and 25 L op	
Timer	0 to 15 mins	0 to 99 mins
VWR catalogue number	75845-604 10811-208	
Prices from	\$48.48	\$1,762.45

\* Supplied without blocks. Please order separately.

\*\* Supplied with 1 bottle of M2 general purpose detergent.



# grant 🔊

#### Shakers

- PSU-10i\* PSU-20i\* PMS-1000i
- > Orbital benchtop platform shaker. Max capacity 3kg, 10mm orbit.
- > Multi-functional orbital benchtop multi-platform shaker. Max capacity 8kg, 20mm orbit.
- > Variable speed microplate shaker. 4 plate platform available.

	PSU-10i	PSU-20i	PMS-1000i
Speed	50 to 450 rpm	20 to 250 rpm	150 to 1200 rpm
Timer	1 min to	o 96 hrs	1 min to 23 hrs 59 mins
VWR catalogue number	89194-490	89194-492	89498-120
Prices from	\$1,353.71	\$3,277.45	\$1,040.30

Vortex m	nixers					
PV-1 V-32	<ul> <li>Personal mini vortex mixer with a small footprint, for single tubes.</li> <li>32-socket universal platform for three tube sizes (16 x 1.5ml, 8 x 0.5ml, 8 x 0.2ml) included</li> </ul>					
MPS-1	Kit available,					
	PV-1 V-32 MPS-1					
Speed		750 to 3000 rpm	500 to 3000 rpm	300 to 3200 rpm	1	
Orbit		4 mm	2 mm	3 mm		
VWR catalc	ogue number	97025-568	97025-604	10218-582		
Prices from	l .	\$313.10	\$510.05	\$1,434.20		

## Stirrer / Stirrer hotplate

- > Compact magnetic stirrer for handling small volumes.
- MMS-3000 MSH-300i
- > Digital magnetic hotplate stirrer. Supplied with stirring bar.
- **MMS-3000 MSH-300i** (T-u) Speed 0 to 3000 rpm 250 to 1250 rpm +30 to 330°C Temperature range Stirring volume 20 L VWR catalogue number 89498-132 10809-110 Prices from \$368.65 \$989.80 \* Platforms sold separately.







### Thermoshakers

PCMT\* > Thermoshaker with cooling. Blocks available for microtubes and microplates.
 PHMT > Thermoshaker with blocks available for microtubes and microplates.



- Thermoshaker with blocks available for microtubes and microplates.
   Thermoshaker for 2 or 4 microplates. 3 options available.
- PHMP TS-DW
- > Deep well plate thermoshaker with a choice of interchangeable profiled blocks.

	PCMT series PHMT series PHMP series		PHMP series	TS-DW
Shaking speed	250 to 1400 rpm	250 to 1400 rpm	250 to 1200 rpm	250 to 1400 rpm
Temperature setting range	+4 to 100°C	+25 to 100°C	+25 to 100°C	+25 to 100°C
VWR catalogue number	89498-106	80076-377	97025-552	10809-092
Prices from	\$1,929.10	\$2,186.65	\$2,393.70	\$1,873.55

### Dry blocks for heating and cooling

	PCH-1	PCH-3		
Temperature range	-10 to 100°C			
Stability	± 0.1°C			
Capacity	12 x 1.5 mm or 20 x 0.5 ml	20 x 1.5 ml	20 x 2.0 ml	
VWR catalogue number	97025-548	97025-550	89402-936	
Prices from	\$2,080.60	\$2,080.60	\$2,080.60	

## Centrifuges and combined vortex mixer / centrifuges

LMC* PCV SERIES MICROSPIN12	tubes and microplates.         PCV SERIES         > Choice of 2 combined centrifuge / vortex mixers.					
CVP-2	> All-in-one	e PCR plate centrifuge	e / vortex mixer.			
		LMC	PCV	MICROSPIN 12	CVP-2	]
Speed		100 to 3000 rpm 1000 to 6000 rpm 100 to 14,500 rpm 250 to 1400 rpm				
VWR catalogue nu	umber	89194-510 80076-360 89402-942 10809-038				
Prices from		\$2,449.25	\$732.25	\$1,616.00	\$1,893.75	

\* Supplied without rotor. Must order separately.

### **Rockers and rotators**

- PTR 25\* PTR 35\*
- > 360° vertical mini rotator with a choice of 3 platforms for tubes up to 50ml.
- > 360° vertical multifunction rotator with a choice of 6 platforms for tubes up to 50ml and plates.
- PTR 60\*
- 360° vertical multifunction rotator with a choice of 3 platforms for tubes up to 50ml.

	PTR 25	PTR 35	PTR 60	
Variable speed	5 to 30 rpm	1 to 10	00 rpm	
Max tube capacity	22 tubes	26 tubes 48 tubes		
Timer, with automatic switch-off	1 min to 24 hrs			
VWR catalogue number	89402-918	89194-476	80076-370	
Prices from	\$676.70	\$1,04030	\$1,979.60	

## 2D Platform rockers

PMR-30 PMR-100

- > Fixed tilt platform rocker. Supplied with non slip mat.
- > Adjustable tilt platform rocker. Supplied with non slip mat.



### **3D Platform rockers**

- PS-3D PS-M3D
- > Fixed tilt 3D rocker. Supplied with non slip mat.
- Multi-function 3D rocker. Supplied with non slip mat.

	PS-3D	PS-M3D	
Speed	5 to 60 rpm	1 to 100 rpm	
Orbital diameter	-	22 mm	
Platform dims (working area)	210 x 210 mm		
VWR catalogue number	97025-564	80076-382	
Prices from	\$565.60	\$1,373.60	
* Supplied with platform for tubes up to 15ml			

\* Supplied with platform for tubes up to 15ml





vear warranty

### PCR UV cabinets

UVC/T-M-AR . Stainless steel UV cabinet designed for clean operation with DNA samples available with either access port or internal socket.



voar warrant

- UVT-B-AR > Economy benchtop UV cabinet for protection during DNA / RNA procedure available with either access port or internal socket.
- UVT-S-AR

Large capacity double PCR stainless steel UV cabinet with 3 internal power sockets.



Construction	Stainless steel frame and working area		
Panels	Glass with UV-protective film		
Internal working area	650 x 475 mm	650 x 475 mm	1200 x 520 mm
UV	Built in UV bactericidal cleaner recirculator and UV surface irradiation		
VWR catalogue number	10117-478	10117-476	10117-482
Prices from	\$3974.35	\$3,277.45	\$6,090.30

### Orbital shaker incubators

ES-20\* ES-80\*

Те

Or VV

Pr

> Compact orbital benchtop shaker-incubator. A choice of 5 platforms available.

- >

Orbital shaker-incubator ideal for vigorous or even mixing and incubation of samples.

#### A choice of 5 platforms available.

	ES-20	ES-80
emperature setting range	+25 to 42°C	+25 to 80°C
rbit	10 mm	20 mm
WR catalogue number	10127-586	
rices from	\$3,090.60	\$

## Application specific products



for use in the preparation of TB culture medium, designed to produce large batches of uniform tuberculosis culture medium for up to six times per day.

gradient system for investigating responses to temperature shifts of seeds, small plants insects, mirco-organisms or any small component or material.



#### 1.800.932.5000 | VWR.COM

Prices and product details are current when published and subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or fifliates. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its offliates, unless otherwise noted. | Visit vwr.com to view our privacy policy, trademark owners, and additional disclaimers. © 2019 Avantor, Inc. All rights reserved.

\* Supplied without platform / trays. Must order separately.