














## FOCUS PRODUCT GUIDE SINGLE USE SOLUTIONS

GLOVES	KEY BENEFITS	APPLICATIONS	VWR Cat. No.	SIZE														
<b>MICROFLEX® ULTRAFORM® UF-524</b> 	<ul style="list-style-type: none"> <li>Designed with ERGOFORM™ Ergonomic Design Technology to support musculoskeletal health</li> <li>Thin design for superior tactile sensitivity</li> <li>Soft nitrile formulation forms to hands for comfort during extended wear</li> </ul>	Life Sciences, Healthcare	89235-576 89235-578 89235-580 89235-582 89235-584	XS S M L XL														
<b>MICROFLEX® XCEED® XC-310</b> 	<ul style="list-style-type: none"> <li>Excellent choice for trimming, packaging and racking applications</li> <li>Environmentally friendly, smart packaging with 250 gloves per box</li> <li>Medical examination grade</li> </ul>	Life Sciences, Healthcare	89174-538 89174-540 89174-542 89174-544 89174-546	XS S M L XL														
<b>MICROFLEX® FreeForm® SE FFS-700</b> 	<ul style="list-style-type: none"> <li>Textured fingertips for enhanced grip</li> <li>Non-stick properties resists tape and adhesives</li> <li>Available in half sizes for a unique, tailored fit</li> </ul>	Life Sciences, Healthcare	32916-680 32916-682 32916-684 32916-686 32916-688	XS S M L XL														
<b>MICROFLEX® Supreno® SE SU-690</b> 	<ul style="list-style-type: none"> <li>Durable nitrile formulation for demanding jobs</li> <li>More than 240 minutes of resistance to fentanyl and gastric acid (vomit)</li> <li>Textured fingertips provide secure grip</li> </ul>	Life Sciences, Healthcare	32916-668 SU-690 32916-660 SU-690 32916-662 SU-690 32916-664 SU-690 32916-666 SU-690	XS S M L XL														
<b>MICROFLEX® Supreno® EC SEC-375</b> 	<ul style="list-style-type: none"> <li>Certified by the National Fire Protection Association</li> <li>More than 240 minutes of resistance to fentanyl and gastric acid</li> <li>Approved for use with chemotherapy and cytotoxic drugs</li> </ul>	Life Sciences, Healthcare	76311-656 SEC-375 32916-670 SEC-375 32916-672 SEC-375 32916-674 SEC-375 32916-676 SEC-375 32916-678 SEC-375 89135-222 SEC-375	XS S M L XL 2XL 3XL														
<b>MICROFLEX® MidKnight™ MK-296 &amp; XTRA 93-862</b> 	<ul style="list-style-type: none"> <li>Black color shows hazardous powders and hides stains</li> <li>Fully textured for a reliable, consistent grip</li> <li>More than 240 minutes of resistance to fentanyl and gastric acid (vomit)</li> </ul>	Chemical, Healthcare, Life Sciences,	<table border="1"> <thead> <tr> <th>Standard</th> <th>Extended</th> </tr> </thead> <tbody> <tr> <td>94001-364</td> <td>-</td> </tr> <tr> <td>94001-366</td> <td>76312-344</td> </tr> <tr> <td>94001-368</td> <td>76312-346</td> </tr> <tr> <td>94001-370</td> <td>76312-348</td> </tr> <tr> <td>94001-372</td> <td>76312-350</td> </tr> <tr> <td>94001-374</td> <td>76312-352</td> </tr> </tbody> </table>	Standard	Extended	94001-364	-	94001-366	76312-344	94001-368	76312-346	94001-370	76312-348	94001-372	76312-350	94001-374	76312-352	XS S M L XL 2XL
Standard	Extended																	
94001-364	-																	
94001-366	76312-344																	
94001-368	76312-346																	
94001-370	76312-348																	
94001-372	76312-350																	
94001-374	76312-352																	
<b>MICROFLEX® LIFESTAR EC® LSE-104</b> 	<ul style="list-style-type: none"> <li>Tested against both fentanyl and gastric acid (vomit) to simulate hazardous, real world overdose situations</li> <li>Dual layer, dual color design for two layers of protection</li> <li>Advanced barrier protection (AQL 0.65)</li> <li>Non-stick and non-foaming properties for reduced interference when working</li> </ul>	Healthcare	76201-712 76201-714 76201-702 76201-704 76201-706 76201-708	S M L XL 2XL 3XL														
<b>TouchNTuff® 92-600</b> 	<ul style="list-style-type: none"> <li>Robust proprietary formulation improves durability</li> <li>FDA-compliant soft nitrile provides high levels of comfort</li> <li>Silicone-free design eases paint and finish processes</li> </ul>	Life Sciences, Chemical	76238-380 76238-378 76238-376 76238-382	S M L XL														
<b>MICROFLEX® 93-260</b> 	<ul style="list-style-type: none"> <li>Nitrile &amp; neoprene offer broad resistance against harsh chemicals</li> <li>Extended cuff, 12" length; 7.8 mil palm thickness</li> <li>Silicone-free</li> </ul>	Life Sciences, Chemical	75832-934 75832-936 75832-938 75832-940 75832-942 75832-944	XS S M L XL 2XL														

# CLEAN AND STERILE SOLUTIONS

GLOVES		KEY BENEFITS	APPLICATIONS	VWR Cat. No.		SIZE
<b>BIOCLEAN™ FUSION BFAP &amp; S-BFAP</b> 	<ul style="list-style-type: none"> <li>Low particulate count</li> <li>Powder-free and latex-free</li> <li>Excellent ESD properties</li> <li>Easy double-donning</li> <li>Chemical resistant</li> </ul>	<i>Life Sciences, Chemical, Pharma Compounding</i>	Non-Sterile	Sterile	XS S M L XL 2XL	
			75972-620	75982-304		
<b>MICROFLEX® 93-360</b> 	<ul style="list-style-type: none"> <li>Three layer nitrile and neoprene design for broad chemical resistance against harsh chemicals including acids, solvents and bases*</li> <li>Compatible for cleanroom / controlled environments</li> <li>Silicone free and anti-static</li> </ul>	<i>Life Sciences</i>	76289-850		XS S M L XL 2XL	
			76289-852			
<b>BIOCLEAN™ N-PLUS BNPS</b> 	<ul style="list-style-type: none"> <li>400mm/16" length for extra protection</li> <li>Hand specific sterile nitrile</li> <li>Approved for use with chemotherapy drugs (ASTM D 6978)*</li> </ul>	<i>Life Sciences, Chemical, Healthcare, Pharma Compounding</i>	75834-048		6 6.5 7 7.5 8 8.5 9 10	
			75834-050			
<b>TouchNTuff® 83-500</b> 	<ul style="list-style-type: none"> <li>Powder-free, smooth grip, extended beaded cuff</li> <li>Suitable for Class 100 (ISO 5) / Grade A Clean Room environments</li> <li>Prevents Type I allergies</li> </ul>	<i>Life Sciences, Chemical</i>	89402-724		5.5 6 6.5 7 7.5 8 8.5 9	
			89402-726			
<b>BioClean™ Nitrile Clean RABS/Isolator Gloves CGL &amp; GGL</b> 	<ul style="list-style-type: none"> <li>Consistent 10-week lead time; excellent alternative to CSM/ Hypalon &amp; EPDM</li> <li>Available ISO 4 cleanroom laundered, both validated sterile and non-sterile</li> <li>FDA approved, VHP and IPA resistant, multiple autoclave cycles</li> </ul>	<i>Life Sciences, Pharma Compounding</i>	Non-Sterile	Sterile	6 - 8" 8 - 10" 10 - 12" 12 - 14"	
			76316-252	76311-658		
<b>BioClean™-D Drop-down Sterile Garment with Hood S-BDSH</b> 	<ul style="list-style-type: none"> <li>Innovative quick and easy donning design</li> <li>Lightweight for increased user comfort/ wearability</li> <li>Sterile and Class 10 (ISO 4) compatible</li> <li>Low-linting antistatic CleanTough material</li> </ul>	<i>Life Sciences, Pharma Compounding</i>	75845-800		XS S M L XL 2XL 3XL 4XL 5XL 6XL 7XL 8XL	
			75845-796			
<b>BioClean™ Clearview Autoclavable Panoramic Goggles BCAP</b> 	<ul style="list-style-type: none"> <li>With extra depth and width for increased field of vision</li> <li>Upper vents, indirect ventilation system</li> <li>Latex-free, non-linting head band</li> <li>Optically correct polycarbonate lens with anti- scratch coating</li> <li>PPE Cat 2 certification</li> <li>Suitable for Class 10 (ISO 4) cleanroom environments</li> </ul>	<i>Life Sciences, Pharma Compounding</i>	75845-813		BCAP BCAP-SL BCAP-SS	
			75834-001			
<b>BioClean™ Cut Resistant Liner S-BCRL</b> 	<ul style="list-style-type: none"> <li>ANSI A2 Cut protection</li> <li>Specifically constructed for optimal dexterity, comfort and fit</li> <li>Offer cut protection when handling sharp objects or cleaning apparatus which pose a cut risk</li> <li>Compatible with ISO Class 4 cleanroom or higher: &lt;450 LPC</li> </ul>	<i>Life Sciences, Chemical, Healthcare</i>	76326-064		XS S M L XL	
			76326-066			

WARNING: \*Warning: No glove provides complete protection against all chemicals. Users must test the gloves against the particular chemicals and environment in which they will be used. Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. © 2019 Ansell Limited. All Rights Reserved.



800 932 5000 | VWR.COM

Prices and product details are current when published and subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR, part of Avantor, makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC and/or Avantor, Inc. or affiliates. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last. | Trademarks are owned by Avantor, Inc. or its affiliates, unless otherwise noted. | Visit [vwr.com](http://vwr.com) to view our privacy policy, trademark owners, and additional disclaimers. © 2019 Avantor, Inc. All rights reserved.