

DASH APEX 24 SET & LOCK STAT CENTRIFUGE

Part # 00-084-009-005

Discover a better way to spin STAT with Drucker's DASH Apex 24 STAT centrifuges. Minimize lab error, reduce turnaround time, and streamline training with the DASH Apex's simple controls and powerful performance.

Easy to Monitor

Prevent forgotten samples and reduce TAT with LED lid lighting (patent pending). Bright lights indicate when the centrifuge is ready to load (off), running (on), or done (flashing). Lights continue flashing until the lid is opened.

Easy to Use

The simple two-button interface makes it easy to select a preset or program your custom validated STAT cycles. Use all three presets, or set and lock to a single cycle for maximum repeatability. Spin 75-125 mm (up to 50 mL) tubes with the same rotor and universal tube holders.

High Capacity STAT

The DASH Apex 24 can spin standard 75-100 mm (3-10 mL) blood tubes, 125 mm (15 mL) long tubes, and tubes with volumes up to 50 mL using a variety of different buckets - no small adapters!

Safe and Durable

Enjoy years of worry-free operation with the DASH Apex 24's brushless motor and rugged, reinforced carbon fiber components. Enhance lab safety with imbalance protection and a clear, shatterproof lid, which locks until the centrifuge has stopped completely.

A Great Value


Each centrifuge comes ready to run with a horizontal rotor, universal tube holders, and 2-year warranty included in the affordable price.




2-Stage Horizontal Rotor

Our patented swing-out horizontal rotor design incorporates a unique test tube holder that produces the ideal horizontally separated samples.

Loading Angle



Rotation Angle



Tubes	Applications	Centrifugation	Included	Warranty
24 x Standard Tubes 12 x 125 mm/15 mL 6 x 50 mL	STAT Chemistry, Coag, PPP	Horizontal 3,000 xg Max RCF 4,200 Max RPM	Rotor, Buckets, Tube Holders	2 years Rotor: lifetime warranty Extended warranty available

DASH APEX 24



Free 30-Day Evaluation (U.S. Only)

Part Numbers	
Centrifuge	00-084-009-005
Replacement Tube Holders/Buckets	02-004-0-0012K (6 qty)
50 mL Tube Holders/Buckets	02-004-0-0014K (6 qty)
Adapters, 1.5 to 2 mL	7713065 (1 qty)
1 yr Warranty Extension	03-0-0007-0003
2 yr Warranty Extension	03-0-0007-0004
3 yr Warranty Extension	03-0-0007-0005
* Custom Settings	00-100-100-101

* Add this part number to your centrifuge order to have your custom validated cycles pre-programmed at the factory

Factory Settings			
	RPM	Time	G-Force
1st Setting/Cycle	4,200	5	3,000
2nd Setting/Cycle	4,200	6	3,000
3rd Setting/Cycle	3,500	7	2,000

Specifications	
Sound level	64 dBA
Dimensions (W x D x H)	14.5 x 17 x 9 in 37 x 43 x 23 cm
Weight	39 lbs (17 kg)
Power	95 to 253 VAC – 50/60 Hz



druckerdiagnostics.com
sales@druckerdiagnostics.com

+1-866-265-1486 (U.S. only)
+1-814-692-7661

