

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

1 Identification

- **Product identifier**
- **Trade name:** Acidic Titration Solvent
for Distillates - ASTM D3227-13
- **Article number:** 0125
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 2 H225 Highly flammable liquid and vapor.



GHS07

Eye Irrit. 2A H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS07

- **Signal word** Danger
- **Hazard-determining components of labeling:**
Isopropanol
- **Hazard statements**
Highly flammable liquid and vapor.
Causes serious eye irritation.
May cause drowsiness or dizziness.

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 1)

· **Precautionary statements**

Keep away from heat/sparks/open flames/hot surfaces. No smoking.

Ground/bond container and receiving equipment.

Use explosion-proof electrical/ventilating/lighting/equipment.

Use only non-sparking tools.

Take precautionary measures against static discharge.

Avoid breathing dust/fume/gas/mist/vapors/spray

Wash thoroughly after handling.

Use only outdoors or in a well-ventilated area.

Wear protective gloves/protective clothing/eye protection/face protection.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

Call a POISON CENTER/doctor if you feel unwell.

If eye irritation persists: Get medical advice/attention.

In case of fire: Use for extinction: CO₂, powder or water spray.

Store in a well-ventilated place. Keep container tightly closed.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



Health = 1

Fire = 3

Reactivity = 0

· **HMIS-ratings (scale 0 - 4)**



Health = 2

Fire = 3

Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 67-63-0	Isopropanol	96.658%
--------------	-------------	---------

· **Table of Nonhazardous Ingredients**

CAS: 64-19-7	Acetic Acid	0.612%
CAS: 127-09-3	Sodium Acetate Anhydrous	0.202%
CAS: 7732-18-5	Water	2.528%

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 2)

4 First-aid measures

- **Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

- **PAC-1:**

CAS: 67-63-0	Isopropanol	400 ppm
CAS: 64-19-7	Acetic Acid	5 ppm
CAS: 127-09-3	Sodium Acetate Anhydrous	11 mg/m ³

- **PAC-2:**

CAS: 67-63-0	Isopropanol	2000* ppm
CAS: 64-19-7	Acetic Acid	35 ppm
CAS: 127-09-3	Sodium Acetate Anhydrous	120 mg/m ³

- **PAC-3:**

CAS: 67-63-0	Isopropanol	12000** ppm
CAS: 64-19-7	Acetic Acid	250 ppm

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

CAS: 127-09-3 Sodium Acetate Anhydrous

(Contd. of page 3)

700 mg/m³

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about protection against explosions and fires:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
Keep receptacle tightly sealed.
Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 67-63-0 Isopropanol

PEL	Long-term value: 980 mg/m ³ , 400 ppm
REL	Short-term value: 1225 mg/m ³ , 500 ppm Long-term value: 980 mg/m ³ , 400 ppm
TLV	Short-term value: 984 mg/m ³ , 400 ppm Long-term value: 492 mg/m ³ , 200 ppm
BEI	

- **Ingredients with biological limit values:**

CAS: 67-63-0 Isopropanol

BEI	40 mg/L LD50 Intraperitoneal: urine Time: end of shift at end of workweek LD50: Acetone (background, nonspecific)
-----	--

- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing.
Wash hands before breaks and at the end of work.
Avoid contact with the eyes.
Avoid contact with the eyes and skin.
- **Breathing equipment:** Not required.

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 4)

- **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:**



Tightly sealed goggles

- **Body protection:** Protective work clothing

9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form: Liquid

Color: Clear

- **Odor:** IPA

- **Odor threshold:** Not determined.

- **pH-value:** Not determined.

- **Change in condition**

Melting point/Melting range: -89.5 °C (-129 °F)

Boiling point/Boiling range: 82 °C (180 °F)

- **Flash point:** 13 °C (55 °F)

- **Flammability (solid, gaseous):** Not applicable.

- **Ignition temperature:** 425 °C (797 °F)

- **Decomposition temperature:** Not determined.

- **Auto igniting:** Product is not selfigniting.

- **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.

- **Explosion limits:**

Lower: 2 Vol %

Upper: 12 Vol %

- **Vapor pressure at 20 °C (68 °F):** 43 hPa (32 mm Hg)

- **Density at 20 °C (68 °F):** 0.79172 g/cm³ (6.607 lbs/gal)

- **Relative density** Not determined.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 5)

· Vapor density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with Water:	Fully miscible.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	97.3 %
Water:	2.5 %
VOC content:	97.3 % 770.1 g/l / 6.43 lb/gl
Solids content:	0.2 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

ATE (Acute Toxicity Estimate)

Inhalative	LC50/4 h	31 mg/l (rat)
------------	----------	---------------

CAS: 67-63-0 Isopropanol

Oral	LD50	5045 mg/kg (rat)
Dermal	LD50	12800 mg/kg (rabbit)
Inhalative	LC50/4 h	30 mg/l (rat)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**

The product shows the following dangers according to internally approved calculation methods for preparations:
Irritant

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 6)

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer)**

CAS: 67-63-0 | Isopropanol

3

- **NTP (National Toxicology Program)**

None of the ingredients is listed.

- **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

12 Ecological information

- **Toxicity**

- **Aquatic toxicity:** No further relevant information available.

- **Persistence and degradability** No further relevant information available.

- **Behavior in environmental systems:**

- **Bioaccumulative potential** No further relevant information available.

- **Mobility in soil** No further relevant information available.

- **Additional ecological information:**

- **General notes:**

Water hazard class 1 (Self-assessment): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**

- **Recommendation:**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- **Uncleaned packagings:**

- **Recommendation:** Disposal must be made according to official regulations.

- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

- **UN-Number**

- **DOT, IMDG, IATA**

UN1993

- **UN proper shipping name**

- **DOT**

Flammable liquids, n.o.s. (Isopropanol)

- **IMDG, IATA**

FLAMMABLE LIQUID, N.O.S. (Isopropanol)

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 7)

· **Transport hazard class(es)**

· **DOT**



· **Class** 3 Flammable liquids
 · **Label** 3

· **IMDG, IATA**



· **Class** 3 Flammable liquids
 · **Label** 3

· **Packing group**
 · **DOT, IMDG, IATA** II

· **Environmental hazards:**
 · **Marine pollutant:** No

· **Special precautions for user** Warning: Flammable liquids
 · **Danger code (Kemler):** 33
 · **EMS Number:** F-E, S-E
 · **Stowage Category** B

· **Transport in bulk according to Annex II of
MARPOL73/78 and the IBC Code** Not applicable.

· **Transport/Additional information:**

· **DOT**
 · **Quantity limitations** On passenger aircraft/rail: 5 L
 On cargo aircraft only: 60 L

· **IMDG**

· **Limited quantities (LQ)** 1L
 · **Excepted quantities (EQ)** Code: E2
 Maximum net quantity per inner packaging: 30 ml
 Maximum net quantity per outer packaging: 500 ml

· **UN "Model Regulation":** UN 1993 FLAMMABLE LIQUIDS, N.O.S. (ISOPROPANOL), 3, II

15 Regulatory information

· **Safety, health and environmental regulations/legislation specific for the substance or mixture**
 · **Sara**

· **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 8)

· **Section 313 (Specific toxic chemical listings):**

CAS: 67-63-0 | Isopropanol

· **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

CAS: 67-63-0 | Isopropanol

A4

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

· **Hazard pictograms**



GHS02 GHS07

· **Signal word** *Danger*

· **Hazard-determining components of labeling:**

Isopropanol

· **Hazard statements**

Highly flammable liquid and vapor.

Causes serious eye irritation.

May cause drowsiness or dizziness.

· **Precautionary statements**

Keep away from heat/sparks/open flames/hot surfaces. No smoking.

Ground/bond container and receiving equipment.

Use explosion-proof electrical/ventilating/lighting/equipment.

Use only non-sparking tools.

Take precautionary measures against static discharge.

Avoid breathing dust/fume/gas/mist/vapors/spray

Wash thoroughly after handling.

Use only outdoors or in a well-ventilated area.

Wear protective gloves/protective clothing/eye protection/face protection.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

(Contd. on page 10)

Safety Data Sheet

acc. to OSHA HCS

Printing date 08/07/2017

Reviewed on 08/07/2017

**Trade name: Acidic Titration Solvent
for Distillates - ASTM D3227-13**

(Contd. of page 9)

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Call a POISON CENTER/doctor if you feel unwell.

If eye irritation persists: Get medical advice/attention.

In case of fire: Use for extinction: CO₂, powder or water spray.

Store in a well-ventilated place. Keep container tightly closed.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

Creation date for SDS 01-16-2015. STN

08/07/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

BEI: Biological Exposure Limit

Flam. Liq. 2: Flammable liquids – Category 2

Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A

STOT/SE 3: Specific target organ toxicity (single exposure) – Category 3