



Material	45118-540
Material description	Hexane (mixture of isomers)
Grade	Accusolv™
CAS Number	110-54-3
Molecular mass	86,18

## Characteristics

## Specifications

Assay (n-Hexane)	Min. 60,0 %
Assay (as saturated C6 hydrocarbons)	Min. 99,9 %
Appearance	Clear colourless liquid
Thiophene	Passes test
Acidity	Max. 0,0003 meq/g
Color (Pt-Co)	Max. 5 APHA
Residue on evaporation	Max. 1 mg/l
Sulphur compounds	Max. 50 ppm
Water	Max. 100 ppm
Absorbance (195 nm)	Max. 1,000
Absorbance (225 nm)	Max. 0,050
Absorbance (250 nm)	Max. 0,010
Absorbance (275 nm)	Max. 0,005
Absorbance (300 nm)	Max. 0,005
GC-ECD (as Heptachlor epoxide)	Max. 10 ng/l
Submicron filtered	Passes test
Packaged under nitrogen	Passes test

## Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Alicia Bourdeau, Head of the Laboratory - Rouses Point  
VWR Chemicals, LLC, 3 Lincoln Blvd, Rouses Point, NY  
12979-1045, USA