



Material	01097-540
Material description	Acetonitrile
Grade	Accusolv™
CAS Number	75-05-8
Molecular formula	C ₂ H ₃ N
Molecular mass	41,05

Characteristics	Specifications
-----------------	----------------

Assay (GC, not corrected for water)	Min. 99,9 %
Titration acid	Max. 8 µeq/g
Titration base	Max. 0,6 µeq/g
Residue after evaporation	Max. 1 mg/l
Water	Max. 100 ppm
Absorbance (190 nm)	Max. 1,000
Absorbance (200 nm)	Max. 0,050
Absorbance (225 nm)	Max. 0,010
Absorbance (250 nm)	Max. 0,005
Absorbance (350 nm)	Max. 0,005
Electron capture GC (Heptachlor epoxide)	Max. 10 ng/l

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Alicia Bourdeau, Head of the Laboratory - Rouses Point
VWR Chemicals, LLC, 3 Lincoln Blvd, Rouses Point, NY
12979-1045, USA

