

# Just Prove it.

## Spectroquant® Prove 300

Simplify Drinking Water Analysis  
with a new class of spectrophotometers

### Test now and see yourself

The new Spectrophotometer Prove 300, capable for UV and Vis measurements, is designed to simplify your workflow and ensure reliable results.

In combination with the Spectroquant® Test Kits you can leverage the full potential of this new instrument. With a small footprint, ergonomic design and robust material, it fits perfectly to your lab environment.

The Cell Tests are inserted directly into the instrument and the new Live ID code automatically provides the method, Lot No., expiration date and possible calibration updates. As a result the risk of false measurements is minimized.

The long-lasting xenon lamp ensures reproducible measurements over a long period of time.

Even if you spill liquids the removable cell holder enables easy access for cleaning.

### Your advantages

- Safe & Convenient:
  - Live ID provides the method and selects the right settings. Test-specific lot and expiry data are saved with each result.
  - Direct insertion of round cell tests without opening any lids.
- Robust & Easy-to-clean:
  - Materials and design of Spectroquant® Prove are engineered to last and resistant to most chemicals used in labs.
  - Removable cell holder allows easy cleaning.



# Spectroquant® Prove 300 & Spectroquant® Test Kits



## Ordering Information

VWR Cat. No.	Description
EM1.73017.0001	Spectroquant® Prove 300 UV/VIS spectrophotometer

VWR Cat. No.	Accessories Description
EM1.73020.0001	Case for Spectroquant® Prove spectrophotometer
EM1.74010.0001	Halogen lamp module for Spectroquant® Prove
EM1.14946.0001	Rectangular Cells 10 mm (2 pcs)
EM1.14947.0001	Rectangular Cells 20 mm (2 pcs)
EM1.14944.0001	Rectangular Cells 50 mm (2 pcs)
EM1.00784.0001	Rectangular Cells Quartz 10 mm (2 pcs)

VWR Cat. No.	New Spectroquant® Cell Tests for Drinking Water Analysis
--------------	--

<b>NEW</b> EM1.01812.0001	<b>Sulfate Test</b> 0.5 – 50.0 mg/l SO <sub>4</sub> (100 tests)
EM1.14548.0001	<b>Sulfate Cell Test (USEPA approved)</b> 5 – 250 mg/l SO <sub>4</sub> (25 tests)
EM1.14791.0001	<b>Sulfate Test</b> 25 – 300 mg/l SO <sub>4</sub> (200 tests)
EM1.00617.0001	<b>Sulfate Cell Test</b> 50 – 500 mg/l SO <sub>4</sub> (25 tests)
EM1.14564.0001	<b>Sulfate Cell Test (USEPA approved)</b> 100 – 1,000 mg/l SO <sub>4</sub> (25 tests)
<b>NEW</b> EM1.01846.0001	<b>Manganese Test</b> 0.005 – 2.00 mg/l Mn (250 tests)
EM1.14770.0002	<b>Manganese Test</b> 0.010 – 10.00 mg/l Mn (250 tests)
EM1.14770.0001	<b>Manganese Test</b> 0.010 – 10.00 mg/l Mn (500 tests)
EM1.00816.0001	<b>Manganese Test</b> 0.10 – 5.00 mg/l Mn (25 tests)



Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit [vwr.com](http://vwr.com) to view our privacy policy, trademark owners and additional disclaimers. ©2016 VWR International, LLC. All rights reserved.