



Material C1221-4L
Material description Cyclohexane/2-Propanol blend

Characteristics

Specifications

Assay (Cyclohexane)	65,2 --> 69,2 %
Assay (2-Propanol)	30,8 --> 34,8 %
Appearance	Clear colourless liquid
Acidity	Max. 0,0008 meq/g
Boiling range	68 --> 69 °C
pH of alcohol extract	Min. 5,5
Refractive index (25°C)	1,4045 --> 1,4055
Aromatic esters	Max. 1,3 ppm
Non-volatile residue	Max. 1,5 ppm
Water	Max. 100 ppm
Si (Silicon)	Max. 0,2 ppm
Part Number: SSP7495	Confirmed
Spec and Rev Number: Y102A021-102 REV M	Confirmed

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Alicia Bourdeau, Head of the Laboratory - Rouses Point
VWR Chemicals, LLC, 3 Lincoln Blvd, Rouses Point, NY
12979-1045, USA