



LIBERO W

- Temperature monitoring
- Ready to use
- 100% compliant



TECHNICAL SPECIFICATIONS LIBERO W

LIBERO W

Independent Monitoring Solution for Rooms & Equipment

LIBERO W is the most versatile solution for pharmacies, clinical sites and laboratories. Being wireless and battery operated, there is no need for a complicated installation. Place the sensor in the refrigerator or the piece of equipment you want to monitor, start the LIBERO W base station and you are up and running in no time. Use a preconfigured device which is ready to go or take advantage of different reporting options and customize the device exactly to your application. For a safe and regular readout the device features a reminder function and an integrated USB cable. Peace of mind for your critical environment.

Customizable PDF reports

Embedded raw data.
For various applications.




LIBERO W Base

Audio-visual warnings and alarms.
Stand or wallmount.
Integrated USB cable.



LIBERO W Sensor

Status LEDs.
Buffer memory for uninterrupted measurement.



we prove it.

- Simple installation without cables
- Independent of internet and external power supply
- Uninterrupted record of measuring values
- Automatic and reliable min/max temperature list
- 100 % compliance for pharmacies and clinical sites

Technical Specifications LIBERO W

Type	Wireless PDF datalogger consisting of sensor and base station	
Application area	Temperature monitoring for refrigerators, transport boxes, incubators or climate chambers	
Recording options and mode	Multiple use: loop mode or Start-Stop mode	
Type of probe	NTC probe	
Measurement range (sensor)	-10 °C..+50 °C	
Measurement accuracy	±0.5 °C in the range between -10.0 °C and -0.1 °C ±0.4 °C in the range between 0.0 °C and +25.0 °C ±0.8 °C in the range between +25.1 °C and +50.0 °C	
Operating range (base station)	0 °C..+50 °C	
Measurement interval	1 min to 60 min	
Memory capacity (run time)	2 years using 15 min measurement interval (70'000 measuring points in the base station and up to 1'000 measuring points as buffer in the sensor)	
Exchangeable standard batteries	Base station: 3 × alkaline AAA Sensor: 2 × alkaline AAA	
Certificate	Ilac / NIST / ISO 17025 traceable Production Calibration Certificate	
Programmable alarms	- 8 temperature alarm levels with single or cumulative alarm delays - 2 temperature thresholds with alarm delay	
Programmable warnings	Temperature warning delay Read-out reminder Calibration reminder	
Display	Multifunction LCD, size: 32 × 80 mm (1.26 × 3.15 inch)	
Display functionality	<ul style="list-style-type: none"> - Status: OK, WARNING, ALARM - Current temperature measurement - Indication on actual temperature zone - Audio alarm off - Wireless connection strength - Battery replacement due - Calibration due - Read-out due 	
Report	<p>Built-in PDF file generator automatically establishes an evaluation report with embedded data upon connection to an USB port. Complies with the ISO standard 19005-1 Document Management for the long-term preservation of electronic documents (PDF/A) and FDA 21 CFR Part 11.</p> <p>4 report types: Daily min/max report Status report All data report Event report</p>	
Warning alarm signaling	Audio-visual warnings and alarms (LED, buzzer)	
Case dimension weight	<p>Base station: ABS plastic material 115 × 82.5 × 27 mm (4.53 × 3.25 × 1.06 inch) 195 g (6.88 oz)</p> <p>Sensor: ABS plastic material Ø 86 mm (3.39 inch), 25 mm (0.98 inch) 70 g (2.47 oz)</p>	
Protection class	Base station: IP 54 / NEMA 13 Sensor: IP 64 / NEMA 6	
Data logger configuration and additional analysis software	liberoCONFIG software to create, store and manage individual settings in a data logger profile. elproVIEWER software to access and export embedded data of PDF report, for data analysis and comprehensive report features.	
Technical data wireless connection	Connection between sensor and base station: wireless technology standard to exchange data over short distances in the range of 2.4 GHz.	
Conformity	CE FCC Technical Conformity Mark	

Product Description	ELPRO No.	VWR Cat. No.
LIBERO W Wireless PDF Data Logger with Base and Sensor	801415	76045-176
LIBERO WSI Sensor Only	801416	76045-178



1.800.932.5000 | vwr.com

Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vwr.com to view our privacy policy, trademark owners and additional disclaimers. ©2017 VWR International, LLC. All rights reserved.


elpro.com