

Just Prove it.

Spectroquant® Prove 600

Simplify Process Water Analysis with a new class of spectrophotometers

Test now and see yourself

The new Spectrophotometer Prove 600 with high-end UV/Vis optics and cuvettes of up to 100 mm is designed for complex analysis and sensitive photometric measurements.

In combination with the Spectroquant® Test Kits you can leverage the full potential of this new instrument. With a small footprint, ergonomic design and robust material, it fits perfectly to your lab environment.

The cell tests are inserted directly into the instrument and the new Live ID code automatically provides the method, instrument settings, Lot No. and expiration date. As a result the risk of false measurements is minimized.

The long-lasting xenon lamp ensures reproducible measurements over a long period of time.

Even if you spill liquids the removable cell holder enables easy access for cleaning.



Your advantages

- Safe & Convenient:
 - Live ID provides the method and selects the right settings. Test-specific lot and expiry data are saved with each result.
 - Direct insertion of round cell tests without opening any lids.
- Robust & Easy-to-clean:
 - Materials and design of Spectroquant® Prove are engineered to last and resistant to most chemicals used in labs.
 - Removable cell holder allows easy cleaning.

Spectroquant® Prove 600 & Spectroquant® Test Kits



Ordering Information


VWR Cat. No.	Description
EM1.73018.0001	Spectroquant® Prove 600 UV/VIS spectrophotometer

VWR Cat. No.	Accessories Description
EM1.73020.0001	Case for Spectroquant® Prove spectrophotometer
EM1.74010.0001	Halogen lamp module for Spectroquant® Prove
EM1.14946.0001	Rectangular Cells 10 mm (2 pcs)
EM1.14947.0001	Rectangular Cells 20 mm (2 pcs)
EM1.14944.0001	Rectangular Cells 50 mm (2 pcs)
EM1.00784.0001	Rectangular Cells Quartz 10 mm (2 pcs)

VWR Cat. No.	New Spectroquant® Test Kits for Cooler & Boiler Water Analysis
NEW EM1.01807.0001	Chloride Test 0.10 – 5.00 mg/l Cl (100 tests)
NEW EM1.01804.0001	Chloride Cell Test 0.5 – 15.0 mg/l Cl (25 tests)
NEW EM1.01813.0001	Silicate (silicic acid) Test 0.0005 – 0.5000 mg/l SiO ₂ / 0.0002 – 0.2337 mg/l Si (100 tests)
NEW EM1.01812.0001	Sulfate Test 0.50 – 50.0 mg/l SO ₄ (100 tests)



EMD Millipore, the M Mark, and Spectroquant are registered trademarks of Merck KGaA, Darmstadt, Germany.
LAm-16-12480 05/2016 Printed in the USA.
© 2016 EMD Millipore Corporation, Billerica, MA USA. All rights reserved.

VWR  **1.800.932.5000**
We Enable Science **vwr.com**

Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vwr.com to view our privacy policy, trademark owners and additional disclaimers. ©2016 VWR International, LLC. All rights reserved.

0516 Lit. No. 051622W

05/2016