

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

1 Identification

- **Product identifier**
- **Trade name:** Zinc Nitrate, Reagent Grade
- **Article number:** Z3810
- **CAS Number:**
10196-18-6
- **EC number:**
231-943-8
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS03 Flame over circle

Ox. Liq. 2 H272 May intensify fire; oxidizer.

Ox. Sol. 2 H272 May intensify fire; oxidizer.



GHS07

Acute Tox. 4 H302 Harmful if swallowed.

Skin Irrit. 2 H315 Causes skin irritation.

STOT SE 3 H335 May cause respiratory irritation.

- **Label elements**

- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS03



GHS07

- **Signal word** Danger

- **Hazard statements**

May intensify fire; oxidizer.

May intensify fire; oxidizer.

Harmful if swallowed.

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 1)

Causes skin irritation.

May cause respiratory irritation.

· Precautionary statements

Keep away from heat.

Keep/Store away from clothing/combustible materials.

Take any precaution to avoid mixing with combustibles.

Avoid breathing dust/fume/gas/mist/vapors/spray

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Use only outdoors or in a well-ventilated area.

Wear protective gloves / eye protection / face protection.

If swallowed: Call a poison center/doctor if you feel unwell.

If on skin: Wash with plenty of water.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

Specific treatment (see on this label).

Rinse mouth.

If skin irritation occurs: Get medical advice/attention.

If eye irritation persists: Get medical advice/attention.

Take off contaminated clothing.

Store in a well-ventilated place. Keep container tightly closed.

Store locked up.

Dispose of contents/container to Facility

· Classification system:

· NFPA ratings (scale 0 - 4)



Health = 2

Fire = 3

Reactivity = 3

The substance possesses oxidizing properties.

· HMIS-ratings (scale 0 - 4)



Health = 2

Fire = 3

Reactivity = 3

· Other hazards

· Results of PBT and vPvB assessment

· PBT: Not applicable.

· vPvB: Not applicable.

3 Composition/information on ingredients

· Chemical characterization: Substances

· CAS No. Description

10196-18-6 Zinc Nitrate, Reagent Grade

· Identification number(s)

· EC number: 231-943-8

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 2)

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** Immediately call a doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 27 mg/m³
- **PAC-2:** 300 mg/m³
- **PAC-3:** 1,800 mg/m³

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 3)

· **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
 Keep away from foodstuffs, beverages and feed.
 Immediately remove all soiled and contaminated clothing.
 Wash hands before breaks and at the end of work.
 Avoid contact with the skin.
 Avoid contact with the eyes and skin.
- **Breathing equipment:**
 In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.
- **Protection of hands:**



Protective gloves

- The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
 Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
 Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
 The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.
 - **Penetration time of glove material**
 The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
 - **Eye protection:** Safety glasses
 - **Body protection:** Protective work clothing

9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Crystalline
Color:	Colorless
Odor:	Odorless
Odor threshold:	Not determined.
- **pH-value:** Not applicable.
- **Change in condition**

Melting point/Melting range:	36.4 °C (97.5 °F)
-------------------------------------	-------------------

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 4)

Boiling point/Boiling range:	-125 °C (-193 °F)
· Flash point:	Not applicable.
· Flammability (solid, gaseous):	Product is not flammable.
· Ignition temperature:	
Decomposition temperature:	Not determined.
· Auto igniting:	Not determined.
· Danger of explosion:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapor pressure:	Not applicable.
· Density at 20 °C (68 °F):	2.065 g/cm ³ (17.23243 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not applicable.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with Water at 20 °C (68 °F):	327 g/l
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not applicable.
Kinematic:	Not applicable.
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	500 mg/kg (ATE)
------	------	-----------------

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 5)

- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 3 (Assessment by list): extremely hazardous for water
Do not allow product to reach ground water, water course or sewage system, even in small quantities.
Danger to drinking water if even extremely small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|----------------------------------|--------------|
| · UN-Number | |
| · DOT, IMDG, IATA | UN1514 |
| · UN proper shipping name | |
| · DOT | Zinc nitrate |
| · IMDG, IATA | ZINC NITRATE |

- **Transport hazard class(es)**

- **DOT**



- **Class** 5.1 Oxidizing substances

(Contd. on page 7)

Safety Data Sheet


acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 6)

· Label	5.1
· IMDG, IATA	
	
· Class	5.1 Oxidizing substances
· Label	5.1
· Packing group	II
· DOT, IMDG, IATA	II
· Environmental hazards:	
· Marine pollutant:	No
· Special precautions for user	Warning: Oxidizing substances
· Danger code (Kemler):	50
· EMS Number:	F-H,S-Q
· Segregation groups	Heavy metals and their salts (including their organometallic compounds)
· Stowage Category	A
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· DOT	
· Quantity limitations	On passenger aircraft/rail: 5 kg On cargo aircraft only: 25 kg
· IMDG	
· Limited quantities (LQ)	1 kg
· Excepted quantities (EQ)	Code: E2 Maximum net quantity per inner packaging: 30 g Maximum net quantity per outer packaging: 500 g
· UN "Model Regulation":	UN 1514 ZINC NITRATE, 5.1, II

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.
- **TSCA (Toxic Substances Control Act):**
- **TSCA new (21st Century Act) (Substances not listed)**
- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 7)

- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS03 GHS07

- **Signal word** *Danger*
- **Hazard statements**
 - May intensify fire; oxidizer.*
 - May intensify fire; oxidizer.*
 - Harmful if swallowed.*
 - Causes skin irritation.*
 - May cause respiratory irritation.*
- **Precautionary statements**
 - Keep away from heat.*
 - Keep/Store away from clothing/combustible materials.*
 - Take any precaution to avoid mixing with combustibles.*
 - Avoid breathing dust/fume/gas/mist/vapors/spray*
 - Wash thoroughly after handling.*
 - Do not eat, drink or smoke when using this product.*
 - Use only outdoors or in a well-ventilated area.*
 - Wear protective gloves / eye protection / face protection.*
 - If swallowed: Call a poison center/doctor if you feel unwell.*
 - If on skin: Wash with plenty of water.*
 - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*
 - Specific treatment (see on this label).*
 - Rinse mouth.*
 - If skin irritation occurs: Get medical advice/attention.*
 - If eye irritation persists: Get medical advice/attention.*
 - Take off contaminated clothing.*
 - Store in a well-ventilated place. Keep container tightly closed.*
 - Store locked up.*
 - Dispose of contents/container to Facility*
- **Chemical safety assessment:** *A Chemical Safety Assessment has not been carried out.*

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** *Environment protection department.*
- **Contact:**
- **Date of preparation / last revision**
 - 02-06-2018: review SDS for accuracy. STN*
 - Creation date for SDS 10-06-2014. STN*
 - 02/06/2018 / -*
- **Abbreviations and acronyms:**
 - ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*
 - IMDG: International Maritime Code for Dangerous Goods*
 - DOT: US Department of Transportation*

(Contd. on page 9)

Safety Data Sheet
acc. to OSHA HCS

Printing date 02/06/2018

Reviewed on 02/06/2018

Trade name: Zinc Nitrate, Reagent Grade

(Contd. of page 8)

IATA: International Air Transport Association
ACGIH: American Conference of Governmental Industrial Hygienists
EINECS: European Inventory of Existing Commercial Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
NIOSH: National Institute for Occupational Safety
OSHA: Occupational Safety & Health
TLV: Threshold Limit Value
PEL: Permissible Exposure Limit
REL: Recommended Exposure Limit
Ox. Liq. 2: Oxidizing liquids – Category 2
Ox. Sol. 2: Oxidizing solids – Category 2
Acute Tox. 4: Acute toxicity – Category 4
Skin Irrit. 2: Skin corrosion/irritation – Category 2
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

US