

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

## 1 Identification

- **Product identifier**
- **Trade name:** Iodine 0.025 Normal (N/40)  
Aqueous Solution
- **Article number:** 4650
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtrec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**  
*The product is not classified according to the Globally Harmonized System (GHS).*
- **Label elements**
- **GHS label elements** Not Applicable
- **Hazard pictograms** Not Applicable
- **Signal word** Not Applicable
- **Hazard statements** Not Applicable
- **Precautionary statements**  
*IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.*  
*IF ON SKIN: Wash with plenty of water.*  
*If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*  
*Dispose of contents/container in accordance with local/regional/national/international regulations.*
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**
- |   |   |
|---|---|
| 0 | 0 |
| 0 | 0 |

  - Health = 0
  - Fire = 0
  - Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**
- |            |   |                |
|------------|---|----------------|
| HEALTH     | 2 | Health = 2     |
| FIRE       | 0 | Fire = 0       |
| REACTIVITY | 0 | Reactivity = 0 |
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

· **vPvB:** Not applicable.

(Contd. of page 1)

### 3 Composition/information on ingredients

- **Chemical characterization: Mixtures**
- **Description:** Mixture of the substances listed below with nonhazardous additions.

- **Dangerous components:**

CAS: 7681-11-0	Potassium Iodide	1.968%
----------------	------------------	--------

- **Table of Nonhazardous Ingredients**

CAS: 7553-56-2	Iodine *DEA regulated item	0.312%
----------------	----------------------------	--------

CAS: 7732-18-5	Water	97.72%
----------------	-------	--------

### 4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Dilute with plenty of water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

- **PAC-I:**

CAS: 7681-11-0	Potassium Iodide	1.3 mg/m <sup>3</sup>
----------------	------------------	-----------------------

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 2)

CAS: 7553-56-2	Iodine *DEA regulated item	0.1 ppm
<b>· PAC-2:</b>		
CAS: 7681-11-0	Potassium Iodide	15 mg/m <sup>3</sup>
CAS: 7553-56-2	Iodine *DEA regulated item	0.5 ppm
<b>· PAC-3:</b>		
CAS: 7681-11-0	Potassium Iodide	87 mg/m <sup>3</sup>
CAS: 7553-56-2	Iodine *DEA regulated item	5 ppm

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.

- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

<b>CAS: 7681-11-0 Potassium Iodide</b>	
TLV	Long-term value: 0.01* ppm *as inhalable fraction and vapor

- **Additional information:** The lists that were valid during the creation were used as basis.

- **Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

The usual precautionary measures for handling chemicals should be followed.

- **Breathing equipment:** Not required.

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 3)

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:** Goggles recommended during refilling.

- **Body protection:** Protective work clothing

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

<b>Form:</b>	Liquid
<b>Color:</b>	Dark brown
<b>Odor:</b>	Metallic
<b>Odor threshold:</b>	Not determined.

- **pH-value:** Not determined.

- **Change in condition**

<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	100 °C (212 °F)

- **Flash point:** Not applicable.

- **Flammability (solid, gaseous):** Not applicable.

- **Ignition temperature:**

**Decomposition temperature:** Not determined.

- **Auto igniting:** Product is not selfigniting.

- **Danger of explosion:** Product does not present an explosion hazard.

- **Explosion limits:**

<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.

- **Vapor pressure at 20 °C (68 °F):** 23 hPa (17 mm Hg)

- **Density at 20 °C (68 °F):** 1.01547 g/cm<sup>3</sup> (8.474 lbs/gal)

- **Relative density** Not determined.

- **Vapor density** Not determined.

- **Evaporation rate** Not determined.

- **Solubility in / Miscibility with**

**Water:** Fully miscible.

- **Partition coefficient (n-octanol/water):** Not determined.

- **Viscosity:**

**Dynamic:** Not determined.

**Kinematic:** Not determined.

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 4)

- |   |                      |
|---|----------------------|
| <b>· Solvent content:</b>   |                      |
| <b>Organic solvents:</b>  | 0.0 %                |
| <b>Water:</b>   | 97.7 %               |
| <b>VOC content:</b>   | 0.0 g/l / 0.00 lb/gl |
| <b>· Solids content:</b> 2.3 %  |                      |
| <b>· Other information</b> No further relevant information available. |                      |

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

**ATE (Acute Toxicity Estimate)**

Oral	LD50	50808 mg/kg (mouse)
------	------	---------------------

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**

The product is not subject to classification according to internally approved calculation methods for preparations:

When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

- **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

## 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 5)

- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Generally not hazardous for water
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

## 14 Transport information

· <b>UN-Number</b>	
· <b>DOT, ADN, IMDG, IATA</b>	Not regulated
· <b>UN proper shipping name</b>	
· <b>DOT, ADN, IATA</b>	Not regulated
· <b>IMDG</b>	Not Regulated
· <b>Transport hazard class(es)</b>	
· <b>DOT, ADN, IMDG, IATA</b>	
· <b>Class</b>	Not regulated
· <b>Packing group</b>	
· <b>DOT, IMDG, IATA</b>	Not regulated
· <b>Environmental hazards:</b>	
· <b>Marine pollutant:</b>	No
· <b>Special precautions for user</b>	Not applicable.
· <b>Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>DOT</b>	
· <b>Remarks:</b>	Not regulated
· <b>IMDG</b>	
· <b>Remarks:</b>	Not regulated
· <b>IATA</b>	
· <b>Remarks:</b>	Not regulated

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 6)

· **UN "Model Regulation":** Not regulated

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

- **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

- **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

- **Proposition 65**

- **Chemicals known to cause cancer:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

CAS: 7553-56-2 | Iodine \*DEA regulated item

A4

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **GHS label elements** Not Applicable

- **Hazard pictograms** Not Applicable

- **Signal word** Not Applicable

- **Hazard statements** Not Applicable

- **Precautionary statements**

**IF SWALLOWED:** Call a POISON CENTER/doctor if you feel unwell.

**IF ON SKIN:** Wash with plenty of water.

**If in eyes:** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Dispose of contents/container in accordance with local/regional/national/international regulations.

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

(Contd. on page 8)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 08/16/2017

Reviewed on 08/16/2017

**Trade name: Iodine 0.025 Normal (N/40)**  
**Aqueous Solution**

(Contd. of page 7)

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

Revision 0.1, 03-20-17: Creation Date for SDS . STN  
 08/16/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit