

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017


Reviewed on 10/02/2017

1 Identification

- **Product identifier**
- **Trade name:** Ammonium Carbonate (-30% Ammonia), Laboratory Grade
- **Article number:** A4430
- **CAS Number:**
506-87-6
- **EC number:**
208-058-0
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**
The substance is not classified according to the Globally Harmonized System (GHS).
 - **Label elements**
 - **GHS label elements** Not Applicable
 - **Hazard pictograms** Not Applicable
 - **Signal word** Not Applicable
 - **Hazard statements** Not Applicable
 - **Precautionary statements**
Wear protective gloves / eye protection / face protection.
Collect spillage.
Store in accordance with local/regional/national/international regulations.
Dispose of contents/container in accordance with local/regional/national/international regulations.
 - **Classification system:**
 - **NFPA ratings (scale 0 - 4)**
- 

Health = 1

Fire = 0

Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**
- | | |
|------------|---|
| HEALTH | 2 |
| FIRE | 1 |
| REACTIVITY | 1 |

Health = 2

Fire = 1

Reactivity = 1
- **Other hazards**
 - **Results of PBT and vPvB assessment**
 - **PBT:** Not applicable.

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 1)

· **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization: Substances**
- **CAS No. Description**
506-87-6 Ammonium Carbonate (~ 30% Ammonia), Lumps
- **Identification number(s)**
- **EC number:** 208-058-0

4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** No special measures required.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 0.31 mg/m³
- **PAC-2:** 3.5 mg/m³
- **PAC-3:** 21 mg/m³

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special measures required.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 2)

- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:** Not required.
- **Body protection:** Protective work clothing

9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form:	Solid
Color:	Colorless
Odor:	Strong ammonia odor
Odor threshold:	Not determined.

- **pH-value:** Not applicable.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 3)

· Change in condition	
Melting point/Melting range:	58 °C (136 °F)
Boiling point/Boiling range:	Undetermined.
· Flash point:	Not applicable.
· Flammability (solid, gaseous):	Product is not flammable.
· Ignition temperature:	
Decomposition temperature:	Not determined.
· Auto igniting:	Not determined.
· Danger of explosion:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapor pressure:	Not applicable.
· Density:	Not determined.
· Relative density	Not determined.
· Vapor density	Not applicable.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with Water:	Not determined.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not applicable.
Kinematic:	Not applicable.
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 4)

- **Additional toxicological information:**
When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.
The substance is not subject to classification.
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**

- **Aquatic toxicity:**

EC50	34.7 mg/kg (Human)
------	--------------------

- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Not known to be hazardous to water.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|-------------------------------------|---------------|
| · UN-Number | |
| · DOT, ADN, IMDG, IATA | Not regulated |
| · UN proper shipping name | |
| · DOT, ADN, IATA | Not regulated |
| · IMDG | Not Regulated |
| · Transport hazard class(es) | |
| · DOT, ADN, IMDG, IATA | |
| · Class | Not regulated |
| · Packing group | |
| · DOT, IMDG, IATA | Not regulated |
| · Environmental hazards: | |
| · Marine pollutant: | No |

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 5)

· Special precautions for user	Not applicable.
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· DOT	
· Remarks:	Not regulated
· IMDG	
· Remarks:	Not regulated
· IATA	
· Remarks:	Not regulated
· UN "Model Regulation":	Not regulated

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is not listed.
- **TSCA (Toxic Substances Control Act):** Substance is listed.
- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** Not Applicable
- **Hazard pictograms** Not Applicable
- **Signal word** Not Applicable
- **Hazard statements** Not Applicable
- **Precautionary statements**
- **Wear protective gloves / eye protection / face protection.**
- **Collect spillage.**
- **Store in accordance with local/regional/national/international regulations.**
- **Dispose of contents/container in accordance with local/regional/national/international regulations.**
- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Environment protection department.
- **Contact:**
- **Date of preparation / last revision**
- **Creation date for SDS** 06/11/2014 LS

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/02/2017

Reviewed on 10/02/2017

Trade name: Ammonium Carbonate (-30% Ammonia), Laboratory Grade

(Contd. of page 6)

*10-02-2017: review SDS for accuracy. STN**10/02/2017 / -***· Abbreviations and acronyms:***ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)**IMDG: International Maritime Code for Dangerous Goods**DOT: US Department of Transportation**IATA: International Air Transport Association**ACGIH: American Conference of Governmental Industrial Hygienists**EINECS: European Inventory of Existing Commercial Chemical Substances**CAS: Chemical Abstracts Service (division of the American Chemical Society)**NFPA: National Fire Protection Association (USA)**HMIS: Hazardous Materials Identification System (USA)**PBT: Persistent, Bioaccumulative and Toxic**vPvB: very Persistent and very Bioaccumulative**NIOSH: National Institute for Occupational Safety**OSHA: Occupational Safety & Health**TLV: Threshold Limit Value**PEL: Permissible Exposure Limit**REL: Recommended Exposure Limit*

US