

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

1 Identification

- **Product identifier**
- **Trade name:** 1,10-Phenanthroline
0.1% w/v in Methanol
- **Article number:** 6624
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 2 H225 Highly flammable liquid and vapor.



GHS06 Skull and crossbones

Acute Tox. 3 H331 Toxic if inhaled.



GHS08 Health hazard

STOT SE 1 H370 Causes damage to organs.

- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS06



GHS08

- **Signal word** Danger
- **Hazard-determining components of labeling:**
Methanol (Methyl Alcohol)
- **Hazard statements**
Highly flammable liquid and vapor.
Toxic if inhaled.

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 1)

Causes damage to organs.

· **Precautionary statements**

Keep away from heat/sparks/open flames/hot surfaces. No smoking.

Ground/bond container and receiving equipment.

Use explosion-proof electrical/ventilating/lighting/equipment.

Use only non-sparking tools.

Take precautionary measures against static discharge.

Do not breathe dust/fume/gas/mist/vapors/spray.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Use only outdoors or in a well-ventilated area.

Wear protective gloves/protective clothing/eye protection/face protection.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Specific treatment (see on this label).

In case of fire: Use for extinction: CO2, powder or water spray.

Store in a well-ventilated place. Keep container tightly closed.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



Health = 3

Fire = 3

Reactivity = 0

· **HMIS-ratings (scale 0 - 4)**



Health = 2

Fire = 3

Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 67-56-1	Methanol (Methyl Alcohol)	99.874%
--------------	---------------------------	---------

· **Table of Nonhazardous Ingredients**

CAS: 5144-89-8	1,10-Phenanthroline, Monohydrate	0.126%
----------------	----------------------------------	--------

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 2)

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Remove breathing apparatus only after contaminated clothing have been completely removed.
In case of irregular breathing or respiratory arrest provide artificial respiration.
- **After inhalation:**
Supply fresh air or oxygen; call for doctor.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** *Immediately wash with water and soap and rinse thoroughly.*
- **After eye contact:** *Rinse opened eye for several minutes under running water. Then consult a doctor.*
- **After swallowing:** *If symptoms persist consult doctor.*
- **Information for doctor:**
 - **Most important symptoms and effects, both acute and delayed** *No further relevant information available.*
 - **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** *Water with full jet*
- **Special hazards arising from the substance or mixture** *No further relevant information available.*
- **Advice for firefighters**
- **Protective equipment:** *Mouth respiratory protective device.*

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** *Do not allow to enter sewers/ surface or ground water.*
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

- **PAC-1:**

CAS: 67-56-1	Methanol (Methyl Alcohol)	530 ppm
--------------	---------------------------	---------

- **PAC-2:**

CAS: 67-56-1	Methanol (Methyl Alcohol)	2,100 ppm
--------------	---------------------------	-----------

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 3)

· **PAC-3:**

CAS: 67-56-1 | Methanol (Methyl Alcohol)

7200* ppm

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
 Ensure good ventilation/exhaustion at the workplace.
 Open and handle receptacle with care.
- **Information about protection against explosions and fires:**
 Keep ignition sources away - Do not smoke.
 Protect against electrostatic charges.
 Keep respiratory protective device available.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
 Keep receptacle tightly sealed.
 Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

CAS: 67-56-1 Methanol (Methyl Alcohol)

PEL Long-term value: 260 mg/m³, 200 ppmREL Short-term value: 325 mg/m³, 250 ppm
 Long-term value: 260 mg/m³, 200 ppm
 SkinTLV Short-term value: 328 mg/m³, 250 ppm
 Long-term value: 262 mg/m³, 200 ppm
 Skin; BEI· **Ingredients with biological limit values:**

CAS: 67-56-1 Methanol (Methyl Alcohol)

BEI 15 mg/L
 LD50 Intraperitoneal: urine
 Time: end of shift
 LD50: Methanol (background, nonspecific)

- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
 Keep away from foodstuffs, beverages and feed.
 Immediately remove all soiled and contaminated clothing.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 4)

Wash hands before breaks and at the end of work.

Store protective clothing separately.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** Protective work clothing

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Liquid
Color:	Clear
Odor:	Methanol
Odor threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/Melting range:	-97.8 °C (-144 °F)
Boiling point/Boiling range:	64 °C (147 °F)

· **Flash point:** 11 °C (52 °F)

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 455 °C (851 °F)

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.

· **Explosion limits:**

Lower: 5.5 Vol %

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 5)

Upper:	44 Vol %
· Vapor pressure at 20 °C (68 °F):	128 hPa (96 mm Hg)
· Density at 20 °C (68 °F):	0.7919 g/cm ³ (6.608 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with Water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	99.9 %
VOC content:	99.9 %
	790.9 g/l / 6.60 lb/gl
· Solids content:	0.1 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

ATE (Acute Toxicity Estimate)

Oral	LD50	104513 mg/kg (rat)
Inhalative	LC50/4 h	3 mg/l

CAS: 67-56-1 Methanol (Methyl Alcohol)

Oral	LD50	5628 mg/kg (rat)
Dermal	LD50	15800 mg/kg (rabbit)
Inhalative	LC50/4 h	3 mg/l (ATE)

CAS: 5144-89-8 1,10-Phenanthroline, Monohydrate

Oral	LD50	132 mg/kg (rat)
------	------	-----------------

(Contd. on page 7)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 6)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**

The product shows the following dangers according to internally approved calculation methods for preparations:
 Toxic

- **Carcinogenic categories**

· IARC (International Agency for Research on Cancer)

None of the ingredients is listed.

· NTP (National Toxicology Program)
--

None of the ingredients is listed.

· OSHA-Ca (Occupational Safety & Health Administration)
--

None of the ingredients is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
- Water hazard class 1 (Self-assessment): slightly hazardous for water
- Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|----------------------------------|--------------------------------------|
| · UN-Number | |
| · DOT, IMDG, IATA | UN1993 |
| · UN proper shipping name | |
| · DOT | Flammable liquids, n.o.s. (Methanol) |

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 7)

· **IMDG, IATA** **FLAMMABLE LIQUID, N.O.S. (METHANOL)**

· **Transport hazard class(es)**

· **DOT**



· **Class** 3 Flammable liquids

· **Label** 3

· **IMDG, IATA**



· **Class** 3 Flammable liquids

· **Label** 3

· **Packing group**

· **DOT, IMDG, IATA** II

· **Environmental hazards:**

· **Marine pollutant:** No

· **Special precautions for user** Warning: Flammable liquids

· **Danger code (Kemler):** 336

· **EMS Number:** F-E,S-E

· **Stowage Category** B

· **Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.

· **Transport/Additional information:**

· **DOT**

· **Quantity limitations** On passenger aircraft/rail: 1 L

On cargo aircraft only: 60 L

· **IMDG**

· **Limited quantities (LQ)** 1L

· **Excepted quantities (EQ)** Code: E2

Maximum net quantity per inner packaging: 30 ml

Maximum net quantity per outer packaging: 500 ml

· **UN "Model Regulation":** UN 1993 FLAMMABLE LIQUIDS, N.O.S. (METHANOL), 3, II

15 Regulatory information

· **Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Sara**

· **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 8)

· **Section 313 (Specific toxic chemical listings):**

CAS: 67-56-1 | Methanol (Methyl Alcohol)

· **TSCA (Toxic Substances Control Act):**

CAS: 67-56-1 | Methanol (Methyl Alcohol)

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

CAS: 67-56-1 | Methanol (Methyl Alcohol)

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

· **Hazard pictograms**



GHS02 GHS06 GHS08

· **Signal word** *Danger*

· **Hazard-determining components of labeling:**

Methanol (Methyl Alcohol)

· **Hazard statements**

Highly flammable liquid and vapor.

Toxic if inhaled.

Causes damage to organs.

· **Precautionary statements**

Keep away from heat/sparks/open flames/hot surfaces. No smoking.

Ground/bond container and receiving equipment.

Use explosion-proof electrical/ventilating/lighting/equipment.

Use only non-sparking tools.

Take precautionary measures against static discharge.

Do not breathe dust/fume/gas/mist/vapors/spray.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Use only outdoors or in a well-ventilated area.

Wear protective gloves/protective clothing/eye protection/face protection.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

(Contd. on page 10)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/08/2017

Reviewed on 09/08/2017

Trade name: 1,10-Phenanthroline
0.1% w/v in Methanol

(Contd. of page 9)

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Specific treatment (see on this label).

In case of fire: Use for extinction: CO₂, powder or water spray.

Store in a well-ventilated place. Keep container tightly closed.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

09-08-2017: review SDS for accuracy. STN

Revision 0.0, 03-21-14: Creation Date for SDS . STN

09/08/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

BEI: Biological Exposure Limit

Flam. Liq. 2: Flammable liquids – Category 2

Acute Tox. 3: Acute toxicity – Category 3

STOT SE 1: Specific target organ toxicity (single exposure) – Category 1