

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017


Reviewed on 09/12/2017

1 Identification

- **Product identifier**
- **Trade name:** Conductivity Standard
10,000 umhos @25°C NIST Traceable
- **Article number:** 6936
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**
The product is not classified according to the Globally Harmonized System (GHS).
 - **Label elements**
 - **GHS label elements** Not Applicable
 - **Hazard pictograms** Not Applicable
 - **Signal word** Not Applicable
 - **Hazard statements** Not Applicable
 - **Precautionary statements**
IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.
IF ON SKIN: Wash with plenty of water.
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
Continue rinsing.
Dispose of contents/container in accordance with local/regional/national/international regulations.
 - **Classification system:**
 - **NFPA ratings (scale 0 - 4)**
- | | |
|---|--|
|  | Health = 0
Fire = 0
Reactivity = 0 |
|---|--|
- **HMIS-ratings (scale 0 - 4)**
- | | | | |
|--|------------|---|----------------|
| <table border="1" data-bbox="224 1577 375 1608"><tr><td>HEALTH</td><td>1</td></tr></table> | HEALTH | 1 | Health = 1 |
| HEALTH | 1 | | |
| <table border="1" data-bbox="224 1612 375 1644"><tr><td>FIRE</td><td>0</td></tr></table> | FIRE | 0 | Fire = 0 |
| FIRE | 0 | | |
| <table border="1" data-bbox="224 1648 375 1680"><tr><td>REACTIVITY</td><td>0</td></tr></table> | REACTIVITY | 0 | Reactivity = 0 |
| REACTIVITY | 0 | | |
- **Other hazards**
 - **Results of PBT and vPvB assessment**
 - **PBT:** Not applicable.
 - **vPvB:** Not applicable.

US

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 1)

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Mixture of the substances listed below with nonhazardous additions.
- **Dangerous components:** Not Applicable

· **Table of Nonhazardous Ingredients**

CAS: 7447-40-7	Potassium Chloride	0.526%
CAS: 7732-18-5	Water	99.474%

4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
 No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Dilute with plenty of water.
- **Methods and material for containment and cleaning up:**
 Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
 Dispose contaminated material as waste according to item 13.
- **Reference to other sections**
 See Section 7 for information on safe handling.
 See Section 8 for information on personal protection equipment.
 See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

· **PAC-1:**

None of the ingredients is listed.

· **PAC-2:**

None of the ingredients is listed.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 2)

· **PAC-3:**

None of the ingredients is listed.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** *No special measures required.*
- **Information about protection against explosions and fires:** *No special measures required.*
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** *No special requirements.*
- **Information about storage in one common storage facility:** *Not required.*
- **Further information about storage conditions:** *None.*
- **Specific end use(s)** *No further relevant information available.*

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** *No further data; see item 7.*
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** *The lists that were valid during the creation were used as basis.*
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** *Not required.*
- **Protection of hands:**



Protective gloves

- The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.*
- Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.*
- Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation*
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** *Goggles recommended during refilling.*

(Contd. on page 4)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 3)

· **Body protection:** Protective work clothing

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Liquid
Color:	Colorless
Odor:	Odorless
Odor threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	100 °C (212 °F)

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:**

Decomposition temperature: Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

· **Vapor pressure at 20 °C (68 °F):** 23 hPa (17 mm Hg)

· **Density at 20 °C (68 °F):** 1.00262 g/cm³ (8.367 lbs/gal)

· **Relative density** Not determined.

· **Vapor density** Not determined.

· **Evaporation rate** Not determined.

· **Solubility in / Miscibility with**

Water: Fully miscible.

· **Partition coefficient (n-octanol/water):** Not determined.

· **Viscosity:**

Dynamic:	Not determined.
Kinematic:	Not determined.

· **Solvent content:**

Organic solvents:	0.0 %
Water:	99.5 %
VOC content:	0.0 g/l / 0.00 lb/gl

Solids content: 0.5 %

· **Other information** No further relevant information available.

US

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 4)

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
 The product is not subject to classification according to internally approved calculation methods for preparations:
 When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.
- **Carcinogenic categories**

· IARC (International Agency for Research on Cancer)

None of the ingredients is listed.

· NTP (National Toxicology Program)
--

None of the ingredients is listed.

· OSHA-Ca (Occupational Safety & Health Administration)
--

None of the ingredients is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Generally not hazardous for water
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

US

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 5)

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

<ul style="list-style-type: none"> · UN-Number · DOT, ADN, IMDG, IATA 	Not regulated
<ul style="list-style-type: none"> · UN proper shipping name · DOT, ADN, IATA · IMDG 	Not regulated Not Regulated
<ul style="list-style-type: none"> · Transport hazard class(es) · DOT, ADN, IMDG, IATA · Class 	Not regulated
<ul style="list-style-type: none"> · Packing group · DOT, IMDG, IATA 	Not regulated
<ul style="list-style-type: none"> · Environmental hazards: · Marine pollutant: 	No
<ul style="list-style-type: none"> · Special precautions for user 	Not applicable.
<ul style="list-style-type: none"> · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code 	Not applicable.
<ul style="list-style-type: none"> · UN "Model Regulation": 	Not regulated

15 Regulatory information

<ul style="list-style-type: none"> · Safety, health and environmental regulations/legislation specific for the substance or mixture · Sara 	
<ul style="list-style-type: none"> · Section 355 (extremely hazardous substances): 	None of the ingredients is listed.
<ul style="list-style-type: none"> · Section 313 (Specific toxic chemical listings): 	None of the ingredients is listed.
<ul style="list-style-type: none"> · TSCA (Toxic Substances Control Act): 	All ingredients are listed.
<ul style="list-style-type: none"> · Proposition 65 	
<ul style="list-style-type: none"> · Chemicals known to cause cancer: 	None of the ingredients is listed.
<ul style="list-style-type: none"> · Chemicals known to cause reproductive toxicity for females: 	None of the ingredients is listed.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/12/2017

Reviewed on 09/12/2017

Trade name: Conductivity Standard
10,000 umhos @25°C NIST Traceable

(Contd. of page 6)

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** Not Applicable

· **Hazard pictograms** Not Applicable

· **Signal word** Not Applicable

· **Hazard statements** Not Applicable

· **Precautionary statements**

IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.

IF ON SKIN: Wash with plenty of water.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

09-12-2017: review SDS for accuracy. STN

Creation date for SDS 06-24-2014. STN

09/12/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit