

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

## 1 Identification

- **Product identifier**
- **Trade name:** Potassium Thiocyanate 0.1  
Normal NIST Traceable Solution
- **Article number:** 7725
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtrec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**  
The product is not classified according to the Globally Harmonized System (GHS).
- **Label elements**
- **GHS label elements** Not Applicable
- **Hazard pictograms** Not Applicable
- **Signal word** Not Applicable
- **Hazard statements** Not Applicable
- **Precautionary statements**  
IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.  
IF ON SKIN: Wash with plenty of water.  
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Dispose of contents/container in accordance with local/regional/national/international regulations.
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**

0	0	0
---	---	---

  - Health = 0
  - Fire = 0
  - Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**

HEALTH	2	Health = 2
FIRE	0	Fire = 0
REACTIVITY	0	Reactivity = 0
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

US

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 1)

### 3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Mixture of the substances listed below with nonhazardous additions.
- **Dangerous components:** Not Applicable

· **Table of Nonhazardous Ingredients**

CAS: 333-20-0	Potassium Thiocyanate	0.967%
CAS: 7732-18-5	Water	99.033%

### 4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
 No further relevant information available.

### 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** No special measures required.
- **Methods and material for containment and cleaning up:**  
 Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
 Dispose contaminated material as waste according to item 13.
- **Reference to other sections**  
 See Section 7 for information on safe handling.  
 See Section 8 for information on personal protection equipment.  
 See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

· **PAC-1:**

CAS: 333-20-0	Potassium Thiocyanate	2.6 mg/m <sup>3</sup>
---------------	-----------------------	-----------------------

· **PAC-2:**

CAS: 333-20-0	Potassium Thiocyanate	28 mg/m <sup>3</sup>
---------------	-----------------------	----------------------

(Contd. on page 3)

US

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 2)

· **PAC-3:**

CAS: 333-20-0 Potassium Thiocyanate

170 mg/m<sup>3</sup>

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**  
 The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
 The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

- The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
 Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.  
 Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
 The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
 The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Goggles recommended during refilling.

(Contd. on page 4)

US

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 3)

· **Body protection:** Protective work clothing

## 9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

<b>Form:</b>	Liquid
<b>Color:</b>	Clear
<b>Odor:</b>	Odorless
<b>Odor threshold:</b>	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	100 °C (212 °F)

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:**

**Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.

· **Vapor pressure at 20 °C (68 °F):** 23 hPa (17 mm Hg)

· **Density at 20 °C (68 °F):** 1.00305 g/cm<sup>3</sup> (8.37 lbs/gal)

· **Relative density** Not determined.

· **Vapor density** Not determined.

· **Evaporation rate** Not determined.

· **Solubility in / Miscibility with**

**Water:** Not miscible or difficult to mix.

· **Partition coefficient (n-octanol/water):** Not determined.

· **Viscosity:**

<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.

· **Solvent content:**

<b>Organic solvents:</b>	0.0 %
<b>Water:</b>	99.0 %
<b>VOC content:</b>	0.0 g/l / 0.00 lb/gl

**Solids content:** 1.0 %

· **Other information** No further relevant information available.

US

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 4)

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**  
 The product is not subject to classification according to internally approved calculation methods for preparations:  
 When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.
- **Carcinogenic categories**

· <b>IARC (International Agency for Research on Cancer)</b>
---

None of the ingredients is listed.
------------------------------------

· <b>NTP (National Toxicology Program)</b>
--

None of the ingredients is listed.
------------------------------------

· <b>OSHA-Ca (Occupational Safety &amp; Health Administration)</b>
--

None of the ingredients is listed.
------------------------------------

## 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Generally not hazardous for water
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

US

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 5)

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

## 14 Transport information

<b>· UN-Number</b>	
<b>· DOT, ADN, IMDG, IATA</b>	Not regulated
<b>· UN proper shipping name</b>	
<b>· DOT, ADN, IATA</b>	Not regulated
<b>· IMDG</b>	Not Regulated
<b>· Transport hazard class(es)</b>	
<b>· DOT, ADN, IMDG, IATA</b>	
<b>· Class</b>	Not regulated
<b>· Packing group</b>	
<b>· DOT, IMDG, IATA</b>	Not regulated
<b>· Environmental hazards:</b>	
<b>· Marine pollutant:</b>	No
<b>· Special precautions for user</b>	Not applicable.
<b>· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
<b>· Transport/Additional information:</b>	
<b>· DOT</b>	
<b>· Remarks:</b>	Not regulated
<b>· IMDG</b>	
<b>· Remarks:</b>	Not regulated
<b>· IATA</b>	
<b>· Remarks:</b>	Not regulated
<b>· UN "Model Regulation":</b>	Not regulated

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

**· Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

**· Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 6)

· **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** Not Applicable

· **Hazard pictograms** Not Applicable

· **Signal word** Not Applicable

· **Hazard statements** Not Applicable

· **Precautionary statements**

IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.

IF ON SKIN: Wash with plenty of water.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

09-19-2017: review SDS for accuracy. STN

Creation date for SDS 06/04/2014. STN

09/19/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

(Contd. on page 8)

**Safety Data Sheet**  
*acc. to OSHA HCS*

Printing date 09/19/2017

Reviewed on 09/19/2017

**Trade name: Potassium Thiocyanate 0.1**  
**Normal NIST Traceable Solution**

(Contd. of page 7)

*CAS: Chemical Abstracts Service (division of the American Chemical Society)**NFPA: National Fire Protection Association (USA)**HMIS: Hazardous Materials Identification System (USA)**VOC: Volatile Organic Compounds (USA, EU)**PBT: Persistent, Bioaccumulative and Toxic**vPvB: very Persistent and very Bioaccumulative**NIOSH: National Institute for Occupational Safety**OSHA: Occupational Safety & Health**TLV: Threshold Limit Value**PEL: Permissible Exposure Limit**REL: Recommended Exposure Limit*

US