

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

## 1 Identification

- **Product identifier**
- **Trade name:** Sodium Hydroxide 0.25 Normal  
N.ST Traceable, Solution
- **Article number:** 8635
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtrec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS05 Corrosion

Skin Corr. 1A H314 Causes severe skin burns and eye damage.

Eye Dam. 1 H318 Causes serious eye damage.

- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS05

- **Signal word** Danger
- **Hazard-determining components of labeling:**  
Sodium Hydroxide
- **Hazard statements**  
Causes severe skin burns and eye damage.
- **Precautionary statements**  
Do not breathe dusts or mists.  
Wash thoroughly after handling.  
Wear protective gloves/protective clothing/eye protection/face protection.  
If swallowed: Rinse mouth. Do NOT induce vomiting.  
If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.  
IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Immediately call a POISON CENTER/doctor.  
Specific treatment (see on this label).

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal  
N.ST Traceable, Solution**

(Contd. of page 1)

Wash contaminated clothing before reuse.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**




Health = 3

Fire = 0

Reactivity = 0

· **HMIS-ratings (scale 0 - 4)**



Health = 2

Fire = 0

Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

### 3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 1310-73-2	Sodium Hydroxide	0.995%
----------------	------------------	--------

· **Table of Nonhazardous Ingredients**

CAS: 7732-18-5	Water	99.005%
----------------	-------	---------

### 4 First-aid measures

· **Description of first aid measures**

· **General information:** Immediately remove any clothing soiled by the product.

· **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.

· **After swallowing:** Drink copious amounts of water and provide fresh air. Immediately call a doctor.

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

### 5 Fire-fighting measures

· **Extinguishing media**

· **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.

· **Special hazards arising from the substance or mixture** No further relevant information available.

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 2)

- **Advice for firefighters**
- **Protective equipment:** No special measures required.

## 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Dilute with plenty of water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Use neutralizing agent.  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

- **PAC-1:**

CAS: 1310-73-2	Sodium Hydroxide	0.5 mg/m <sup>3</sup>
----------------	------------------	-----------------------

- **PAC-2:**

CAS: 1310-73-2	Sodium Hydroxide	5 mg/m <sup>3</sup>
----------------	------------------	---------------------

- **PAC-3:**

CAS: 1310-73-2	Sodium Hydroxide	50 mg/m <sup>3</sup>
----------------	------------------	----------------------

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 1310-73-2 Sodium Hydroxide	
---------------------------------	--

PEL	Long-term value: 2 mg/m <sup>3</sup>
-----	--------------------------------------

REL	Ceiling limit value: 2 mg/m <sup>3</sup>
-----	--

TLV	Ceiling limit value: 2 mg/m <sup>3</sup>
-----	--

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 3)

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

· **Breathing equipment:** Not required.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** Protective work clothing

## 9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Liquid

Color: Clear

· **Odor:** Odorless

· **Odor threshold:** Not determined.

· **pH-value at 20 °C (68 °F):** >12

· **Change in condition**

Melting point/Melting range: Undetermined.

Boiling point/Boiling range: 100 °C (212 °F)

· **Flash point:** Not applicable.

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 4)

· <b>Flammability (solid, gaseous):</b>	Not applicable.
· <b>Ignition temperature:</b>	
<b>Decomposition temperature:</b>	Not determined.
· <b>Auto igniting:</b>	Product is not selfigniting.
· <b>Danger of explosion:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b>	
<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.
· <b>Vapor pressure at 20 °C (68 °F):</b>	23 hPa (17 mm Hg)
· <b>Density at 20 °C (68 °F):</b>	1.00531 g/cm <sup>3</sup> (8.389 lbs/gal)
· <b>Relative density</b>	Not determined.
· <b>Vapor density</b>	Not determined.
· <b>Evaporation rate</b>	Not determined.
· <b>Solubility in / Miscibility with Water:</b>	Fully miscible.
· <b>Partition coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	0.0 %
<b>Water:</b>	99.0 %
<b>VOC content:</b>	0.0 g/l / 0.00 lb/gl
<b>Solids content:</b>	1.0 %
· <b>Other information</b>	No further relevant information available.

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** Strong caustic effect on skin and mucous membranes.
- **on the eye:**  
Strong caustic effect.

(Contd. on page 6)

US

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 5)

*Strong irritant with the danger of severe eye injury.*

· **Sensitization:** *No sensitizing effects known.*

· **Additional toxicological information:**

*The product shows the following dangers according to internally approved calculation methods for preparations:*

*Corrosive*

*Irritant*

*Swallowing will lead to a strong caustic effect on mouth and throat and to the danger of perforation of esophagus and stomach.*

· **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

*None of the ingredients is listed.*

· **NTP (National Toxicology Program)**

*None of the ingredients is listed.*

· **OSHA-Ca (Occupational Safety & Health Administration)**

*None of the ingredients is listed.*

## 12 Ecological information

· **Toxicity**

· **Aquatic toxicity:** *No further relevant information available.*

· **Persistence and degradability** *No further relevant information available.*

· **Behavior in environmental systems:**

· **Bioaccumulative potential** *No further relevant information available.*

· **Mobility in soil** *No further relevant information available.*

· **Additional ecological information:**

· **General notes:**

*Generally not hazardous for water*

*Must not reach bodies of water or drainage ditch undiluted or unneutralized.*

*Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.*

· **Results of PBT and vPvB assessment**

· **PBT:** *Not applicable.*

· **vPvB:** *Not applicable.*

· **Other adverse effects** *No further relevant information available.*

## 13 Disposal considerations

· **Waste treatment methods**

· **Recommendation:**

*Must not be disposed of together with household garbage. Do not allow product to reach sewage system.*

· **Uncleaned packagings:**

· **Recommendation:** *Disposal must be made according to official regulations.*

· **Recommended cleansing agent:** *Water, if necessary with cleansing agents.*

US

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 6)

## 14 Transport information

<b>· UN-Number</b>	
<b>· DOT, ADN, IMDG, IATA</b>	Not regulated
<b>· UN proper shipping name</b>	
<b>· DOT</b>	Not regulated
<b>· ADN, IMDG, IATA</b>	Not regulated
<b>· Transport hazard class(es)</b>	
<b>· DOT</b>	Not applicable
<b>· Class</b>	Not regulated
<b>· ADN/R Class:</b>	Not regulated
<b>· Packing group</b>	
<b>· DOT, IMDG, IATA</b>	Not regulated
<b>· Environmental hazards:</b>	
<b>· Marine pollutant:</b>	No
<b>· Special precautions for user</b>	Not applicable.
<b>· Segregation groups</b>	Alkalis
<b>· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
<b>· UN "Model Regulation":</b>	Not regulated

## 15 Regulatory information

<b>· Safety, health and environmental regulations/legislation specific for the substance or mixture</b>	
<b>· Sara</b>	
<b>· Section 355 (extremely hazardous substances):</b>	
None of the ingredients is listed.	
<b>· Section 313 (Specific toxic chemical listings):</b>	
None of the ingredients is listed.	
<b>· TSCA (Toxic Substances Control Act):</b>	
All ingredients are listed.	
<b>· Proposition 65</b>	
<b>· Chemicals known to cause cancer:</b>	
None of the ingredients is listed.	
<b>· Chemicals known to cause reproductive toxicity for females:</b>	
None of the ingredients is listed.	
<b>· Chemicals known to cause reproductive toxicity for males:</b>	
None of the ingredients is listed.	
<b>· Chemicals known to cause developmental toxicity:</b>	
None of the ingredients is listed.	

(Contd. on page 8)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 7)

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS05

- **Signal word** Danger

- **Hazard-determining components of labeling:**

Sodium Hydroxide

- **Hazard statements**

Causes severe skin burns and eye damage.

- **Precautionary statements**

Do not breathe dusts or mists.

Wash thoroughly after handling.

Wear protective gloves/protective clothing/eye protection/face protection.

If swallowed: Rinse mouth. Do NOT induce vomiting.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

Immediately call a POISON CENTER/doctor.

Specific treatment (see on this label).

Wash contaminated clothing before reuse.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Environment protection department.

- **Contact:**

- **Date of preparation / last revision**

Creation date for SDS 06-09-2014. STN

09-21-2017: review SDS for accuracy. STN

09/21/2017 / -

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

(Contd. on page 9)



**Safety Data Sheet**  
**acc. to OSHA HCS**

Printing date 09/21/2017

Reviewed on 09/21/2017

**Trade name: Sodium Hydroxide 0.25 Normal**  
**N.ST Traceable, Solution**

(Contd. of page 8)

*DOT: US Department of Transportation*  
*IATA: International Air Transport Association*  
*ACGIH: American Conference of Governmental Industrial Hygienists*  
*EINECS: European Inventory of Existing Commercial Chemical Substances*  
*ELINCS: European List of Notified Chemical Substances*  
*CAS: Chemical Abstracts Service (division of the American Chemical Society)*  
*NFPA: National Fire Protection Association (USA)*  
*HMIS: Hazardous Materials Identification System (USA)*  
*VOC: Volatile Organic Compounds (USA, EU)*  
*PBT: Persistent, Bioaccumulative and Toxic*  
*vPvB: very Persistent and very Bioaccumulative*  
*NIOSH: National Institute for Occupational Safety*  
*OSHA: Occupational Safety & Health*  
*TLV: Threshold Limit Value*  
*PEL: Permissible Exposure Limit*  
*REL: Recommended Exposure Limit*  
*Skin Corr. 1A: Skin corrosion/irritation – Category 1A*  
*Eye Dam. 1: Serious eye damage/eye irritation – Category 1*

US