

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

## 1 Identification

- **Product identifier**
- **Trade name:** Cupric Sulfate Anhydrous, Reagent Grade
- **Article number:** C8818
- **CAS Number:**  
7758-98-7
- **EC number:**  
231-847-6
- **Index number:**  
029-004-00-0
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**



Acute Tox. 4 H302 Harmful if swallowed.  
Skin Irrit. 2 H315 Causes skin irritation.  
Eye Irrit. 2A H319 Causes serious eye irritation.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS07

- **Signal word** Warning
- **Hazard statements**  
Harmful if swallowed.  
Causes skin irritation.  
Causes serious eye irritation.
- **Precautionary statements**  
Wash thoroughly after handling.  
Do not eat, drink or smoke when using this product.  
Wear protective gloves / eye protection / face protection.  
**IF SWALLOWED:** Call a POISON CENTER/doctor if you feel unwell.

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 1)

**IF ON SKIN:** Wash with plenty of water.

**If in eyes:** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Specific treatment (see on this label).

Rinse mouth.

**If skin irritation occurs:** Get medical advice/attention.

**If eye irritation persists:** Get medical advice/attention.

Take off contaminated clothing and wash it before reuse.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**

HEALTH	2	Health = 2
FIRE	0	Fire = 0
REACTIVITY	0	Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

### 3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

7758-98-7 Copper Sulfate Anhydrous

· **Identification number(s)**

· **EC number:** 231-847-6

· **Index number:** 029-004-00-0

### 4 First-aid measures

· **Description of first aid measures**

· **General information:**

Immediately remove any clothing soiled by the product.

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** Immediately call a doctor.

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 2)

- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

## 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

## 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**  
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 7.5 mg/m<sup>3</sup>
- **PAC-2:** 9.9 mg/m<sup>3</sup>
- **PAC-3:** 59 mg/m<sup>3</sup>

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing.

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 3)

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

· **Breathing equipment:** Not required.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** Protective work clothing

## 9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

**Form:** Powder

**Color:** Blue

· **Odor:** Odorless

· **Odor threshold:** Not determined.

· **pH-value:** Not applicable.

· **Change in condition**

**Melting point/Melting range:** 200 °C (392 °F)

**Boiling point/Boiling range:** Undetermined.

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Product is not flammable.

· **Ignition temperature:**

**Decomposition temperature:** Not determined.

· **Auto igniting:** Not determined.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

**Lower:** Not determined.

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 4)

<b>Upper:</b>	Not determined.
· <b>Vapor pressure:</b>	Not applicable.
· <b>Density at 20 °C (68 °F):</b>	3.603 g/cm <sup>3</sup> (30.067 lbs/gal)
· <b>Relative density</b>	Not determined.
· <b>Vapor density</b>	Not applicable.
· <b>Evaporation rate</b>	Not applicable.
· <b>Solubility in / Miscibility with Water:</b>	Not determined.
· <b>Partition coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not applicable.
<b>Kinematic:</b>	Not applicable.
· <b>Other information</b>	No further relevant information available.

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	300 mg/kg (rat)
------	------	-----------------

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

## 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**


(Contd. of page 5)

- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
*Water hazard class 2 (Assessment by list): hazardous for water*  
*Do not allow product to reach ground water, water course or sewage system.*  
*Danger to drinking water if even small quantities leak into the ground.*
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**  
*Must not be disposed of together with household garbage. Do not allow product to reach sewage system.*
- **Uncleaned packagings:**
- **Recommendation:** *Disposal must be made according to official regulations.*

## 14 Transport information

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>· <b>UN-Number</b></li> <li>· <b>DOT, IMDG, IATA</b></li> </ul>   | <p style="margin-left: 20px;">UN3077</p>  |
| <ul style="list-style-type: none"> <li>· <b>UN proper shipping name</b></li> <li>· <b>DOT</b></li> <li>· <b>IMDG</b></li> <li>· <b>IATA</b></li> </ul>   | <p style="margin-left: 20px;"><i>Environmentally hazardous substances, solid, n.o.s. (Copper Sulfate Anhydrous)</i><br/> <b>ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Copper Sulfate Anhydrous), MARINE POLLUTANT</b><br/> <b>ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Copper Sulfate Anhydrous)</b></p> |
| <ul style="list-style-type: none"> <li>· <b>Transport hazard class(es)</b></li> <li>· <b>DOT, IMDG, IATA</b></li> </ul> <div style="text-align: center; margin: 10px 0;">  </div> | <p style="margin-left: 20px;">9 Miscellaneous dangerous substances and articles<br/>9</p>   |
| <ul style="list-style-type: none"> <li>· <b>Packing group</b></li> <li>· <b>DOT, IMDG, IATA</b></li> </ul>   | <p style="margin-left: 20px;">III</p>   |
| <ul style="list-style-type: none"> <li>· <b>Environmental hazards:</b></li> <li>· <b>Marine pollutant:</b></li> <li>· <b>Special marking (IATA):</b></li> </ul>  | <p style="margin-left: 20px;"><i>Yes (P)</i><br/> <i>Symbol (fish and tree)</i><br/> <i>Symbol (fish and tree)</i></p>  |
| <ul style="list-style-type: none"> <li>· <b>Special precautions for user</b></li> <li>· <b>Danger code (Kemler):</b></li> <li>· <b>EMS Number:</b></li> </ul>  | <p style="margin-left: 20px;"><i>Warning: Miscellaneous dangerous substances and articles</i><br/>           90<br/>           F-A,S-F</p>  |

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 6)

· <b>Stowage Category</b>	A
· <b>Stowage Code</b>	SW23 When transported in BK3 bulk container, see 7.6.2.12 and 7.7.3.9.
· <b>Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>DOT</b>	
· <b>Quantity limitations</b>	On passenger aircraft/rail: No limit On cargo aircraft only: No limit
· <b>Hazardous substance:</b>	10 lbs, 4.54 kg
· <b>Remarks:</b>	Special marking with the symbol (fish and tree).
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	5 kg
· <b>Excepted quantities (EQ)</b>	Code: E1 Maximum net quantity per inner packaging: 30 g Maximum net quantity per outer packaging: 1000 g
· <b>UN "Model Regulation":</b>	UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCES, SOLID, N.O.S. (COPPER SULFATE ANHYDROUS), 9, III

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.
- **TSCA (Toxic Substances Control Act):** Substance is listed.
- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS07

- **Signal word** Warning
- **Hazard statements**  
Harmful if swallowed.  
Causes skin irritation.  
Causes serious eye irritation.

(Contd. on page 8)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

**Trade name: Cupric Sulfate Anhydrous, Reagent Grade**

(Contd. of page 7)

· **Precautionary statements**

*Wash thoroughly after handling.*

*Do not eat, drink or smoke when using this product.*

*Wear protective gloves / eye protection / face protection.*

*IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.*

*IF ON SKIN: Wash with plenty of water.*

*If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*

*Specific treatment (see on this label).*

*Rinse mouth.*

*If skin irritation occurs: Get medical advice/attention.*

*If eye irritation persists: Get medical advice/attention.*

*Take off contaminated clothing and wash it before reuse.*

*Dispose of contents/container in accordance with local/regional/national/international regulations.*

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

*Creation date for SDS 02-03-2014. STN*

*10-18-2017: review SDS for accuracy. STN*

*10/18/2017 / -*

· **Abbreviations and acronyms:**

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*IMDG: International Maritime Code for Dangerous Goods*

*DOT: US Department of Transportation*

*IATA: International Air Transport Association*

*P: Marine Pollutant*

*ACGIH: American Conference of Governmental Industrial Hygienists*

*EINECS: European Inventory of Existing Commercial Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*NFPA: National Fire Protection Association (USA)*

*HMIS: Hazardous Materials Identification System (USA)*

*LC50: Lethal concentration, 50 percent*

*LD50: Lethal dose, 50 percent*

*PBT: Persistent, Bioaccumulative and Toxic*

*vPvB: very Persistent and very Bioaccumulative*

*NIOSH: National Institute for Occupational Safety*

*OSHA: Occupational Safety & Health*

*TLV: Threshold Limit Value*

*PEL: Permissible Exposure Limit*

*REL: Recommended Exposure Limit*

*Acute Tox. 4: Acute toxicity – Category 4*

*Skin Irrit. 2: Skin corrosion/irritation – Category 2*

*Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A*