

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

## 1 Identification


- **Product identifier**
- **Trade name:** Total Organic Carbon Std.  
5.0 mg/L (ppm), Certified
- **Article number:** 9563
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtrec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**  
The product is not classified according to the Globally Harmonized System (GHS).

---

  - **Label elements**
  - **GHS label elements** Not Applicable
  - **Hazard pictograms** Not Applicable
  - **Signal word** Not Applicable
  - **Hazard statements** Not Applicable
  - **Precautionary statements**  
IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.  
IF ON SKIN: Wash with plenty of water.  
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Dispose of contents/container in accordance with local/regional/national/international regulations.
  - **Classification system:**
  - **NFPA ratings (scale 0 - 4)**
- 

Health = 0  
Fire = 0  
Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**
- |            |   |                |
|------------|---|----------------|
| HEALTH     | 0 | Health = 0     |
| FIRE       | 0 | Fire = 0       |
| REACTIVITY | 0 | Reactivity = 0 |
- **Other hazards**
  - **Results of PBT and vPvB assessment**
  - **PBT:** Not applicable.
  - **vPvB:** Not applicable.

US

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

(Contd. of page 1)

### 3 Composition/information on ingredients

- **Chemical characterization: Mixtures**
- **Description:** Mixture of the substances listed below with nonhazardous additions.
- **Dangerous components:** Not Applicable

· **Table of Nonhazardous Ingredients**

CAS: 7647-01-0	Hydrochloric Acid	0.115%
CAS: 877-24-7	Potassium Hydrogen Phthalate	0.001%
CAS: 7732-18-5	Water	99.884%

### 4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Dilute with plenty of water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

· **PAC-1:**

CAS: 7647-01-0	Hydrochloric Acid	1.8 ppm
CAS: 877-24-7	Potassium Hydrogen Phthalate	9.6 mg/m <sup>3</sup>

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

(Contd. of page 2)

<b>· PAC-2:</b>		
CAS: 7647-01-0	Hydrochloric Acid	22 ppm
CAS: 877-24-7	Potassium Hydrogen Phthalate	110 mg/m <sup>3</sup>
<b>· PAC-3:</b>		
CAS: 7647-01-0	Hydrochloric Acid	100 ppm
CAS: 877-24-7	Potassium Hydrogen Phthalate	630 mg/m <sup>3</sup>

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling:** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s):** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**  
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
 Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

(Contd. of page 3)

- **Eye protection:** Goggles recommended during refilling.
- **Body protection:** Protective work clothing

## 9 Physical and chemical properties

### · Information on basic physical and chemical properties

#### · General Information

#### · Appearance:

<b>Form:</b>	Liquid
<b>Color:</b>	Clear
<b>Odor:</b>	Odorless
<b>Odor threshold:</b>	Not determined.

· **pH-value:** Not determined.

#### · Change in condition

<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	100 °C (212 °F)

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

#### · Ignition temperature:

**Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product does not present an explosion hazard.

#### · Explosion limits:

<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.

· **Vapor pressure at 20 °C (68 °F):** 23 hPa (17 mm Hg)

· **Density at 20 °C (68 °F):** 1.00015 g/cm<sup>3</sup> (8.346 lbs/gal)

· **Relative density** Not determined.

· **Vapor density** Not determined.

· **Evaporation rate** Not determined.

#### · Solubility in / Miscibility with

**Water:** Fully miscible.

· **Partition coefficient (n-octanol/water):** Not determined.

#### · Viscosity:

<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.

#### · Solvent content:

<b>Organic solvents:</b>	0.0 %
<b>Water:</b>	99.9 %
<b>VOC content:</b>	0.0 g/l / 0.00 lb/gl

· **Other information** No further relevant information available.

US

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

(Contd. of page 4)

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**  
 The product is not subject to classification according to internally approved calculation methods for preparations:  
 When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.
- **Carcinogenic categories**

· <b>IARC (International Agency for Research on Cancer)</b>
---

None of the ingredients is listed.
------------------------------------

· <b>NTP (National Toxicology Program)</b>
--

None of the ingredients is listed.
------------------------------------

· <b>OSHA-Ca (Occupational Safety &amp; Health Administration)</b>
--

None of the ingredients is listed.
------------------------------------

## 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Generally not hazardous for water
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

US

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

(Contd. of page 5)

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

## 14 Transport information

<b>· UN-Number</b>	
<b>· DOT, ADN, IMDG, IATA</b>	Not regulated
<b>· UN proper shipping name</b>	
<b>· DOT, ADN, IATA</b>	Not regulated
<b>· IMDG</b>	Not Regulated
<b>· Transport hazard class(es)</b>	
<b>· DOT, ADN, IMDG, IATA</b>	
<b>· Class</b>	Not regulated
<b>· Packing group</b>	
<b>· DOT, IMDG, IATA</b>	Not regulated
<b>· Environmental hazards:</b>	
<b>· Marine pollutant:</b>	No
<b>· Special precautions for user</b>	Not applicable.
<b>· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
<b>· Transport/Additional information:</b>	
<b>· DOT</b>	
<b>· Remarks:</b>	Not regulated
<b>· IMDG</b>	
<b>· Remarks:</b>	Not regulated
<b>· IATA</b>	
<b>· Remarks:</b>	Not regulated
<b>· UN "Model Regulation":</b>	Not regulated

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

**· Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

**· Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.  
5.0 mg/L (ppm), Certified**

(Contd. of page 6)

· **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** Not Applicable

· **Hazard pictograms** Not Applicable

· **Signal word** Not Applicable

· **Hazard statements** Not Applicable

· **Precautionary statements**

IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.

IF ON SKIN: Wash with plenty of water.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

09-27-2017: review SDS for accuracy. STN

Creation date for SDS 05-30-2014. STN

09/27/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

(Contd. on page 8)

**Safety Data Sheet**  
*acc. to OSHA HCS*

Printing date 09/27/2017

Reviewed on 09/27/2017

**Trade name: Total Organic Carbon Std.**  
**5.0 mg/L (ppm), Certified**

CAS: Chemical Abstracts Service (division of the American Chemical Society)  
NFPA: National Fire Protection Association (USA)  
HMIS: Hazardous Materials Identification System (USA)  
VOC: Volatile Organic Compounds (USA, EU)  
PBT: Persistent, Bioaccumulative and Toxic  
vPvB: very Persistent and very Bioaccumulative  
NIOSH: National Institute for Occupational Safety  
OSHA: Occupational Safety & Health  
TLV: Threshold Limit Value  
PEL: Permissible Exposure Limit  
REL: Recommended Exposure Limit

(Contd. of page 7)

US