

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

1 Identification

- **Product identifier**
- **Trade name:** Cyclohexane, Reagent ACS Grade
- **Article number:** C9110
- **CAS Number:**
110-82-7
- **EC number:**
203-806-2
- **Index number:**
601-017-00-1
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 2 H225 Highly flammable liquid and vapor.



GHS08 Health hazard

Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Label elements**

- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS07



GHS08

- **Signal word** *Danger*

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 1)

- **Hazard statements**

Highly flammable liquid and vapor.
 Causes skin irritation.
 May cause drowsiness or dizziness.
 May be fatal if swallowed and enters airways.

- **Precautionary statements**

Keep away from heat/sparks/open flames/hot surfaces. No smoking.
 Ground/bond container and receiving equipment.
 Use explosion-proof electrical/ventilating/lighting/equipment.
 Use only non-sparking tools.
 Take precautionary measures against static discharge.
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Wash thoroughly after handling.
 Use only outdoors or in a well-ventilated area.
 Wear protective gloves/protective clothing/eye protection/face protection.
 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 Call a POISON CENTER/doctor if you feel unwell.
 Specific treatment (see on this label).
 Do NOT induce vomiting.
 If skin irritation occurs: Get medical advice/attention.
 Take off contaminated clothing and wash it before reuse.
 In case of fire: Use for extinction: CO₂, powder or water spray.
 Store in a well-ventilated place. Keep container tightly closed.
 Store in a well-ventilated place. Keep cool.
 Store locked up.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

- **Classification system:**

- **NFPA ratings (scale 0 - 4)**



- **HMIS-ratings (scale 0 - 4)**

HEALTH	1	Health = 1
FIRE	3	Fire = 3
REACTIVITY	0	Reactivity = 0

- **Other hazards**

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization: Substances**

- **CAS No. Description**

110-82-7 Cyclohexane

- **Identification number(s)**

- **EC number:** 203-806-2

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

· **Index number:** 601-017-00-1

(Contd. of page 2)

4 First-aid measures

- **Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 300 ppm
- **PAC-2:** 1700* ppm
- **PAC-3:** 10000** ppm

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
- **Information about protection against explosions and fires:**
Keep ignition sources away - Do not smoke.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 3)

Protect against electrostatic charges.

- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
 - Keep receptacle tightly sealed.
 - Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 110-82-7 Cyclohexane

PEL Long-term value: 1050 mg/m³, 300 ppm

REL Long-term value: 1050 mg/m³, 300 ppm

TLV Long-term value: 344 mg/m³, 100 ppm

- **Additional information:** The lists that were valid during the creation were used as basis.

- **Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the skin.

Avoid contact with the eyes and skin.

- **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 4)

· Eye protection:



Tightly sealed goggles

· Body protection: Protective work clothing

9 Physical and chemical properties

· Information on basic physical and chemical properties

· General Information

· Appearance:

· Form:	Liquid
· Color:	Colorless
· Odor:	Organic
· Odor threshold:	Not determined.

· pH-value: Not determined.

· Change in condition

· Melting point/Melting range:	6.4 °C (44 °F)
· Boiling point/Boiling range:	81 °C (178 °F)

· Flash point: -18 °C (-0 °F)

· Flammability (solid, gaseous): Not applicable.

· Ignition temperature: 260 °C (500 °F)

· Decomposition temperature: Not determined.

· Auto igniting: Not determined.

· Danger of explosion: Product is not explosive. However, formation of explosive air/vapor mixtures are possible.

· Explosion limits:

· Lower:	1.2 Vol %
· Upper:	8.3 Vol %

· Vapor pressure at 20 °C (68 °F): 104 hPa (78 mm Hg)

· Density at 20 °C (68 °F): 0.78 g/cm³ (6.509 lbs/gal)

· Relative density: Not determined.

· Vapor density: Not determined.

· Evaporation rate: Not determined.

· Solubility in / Miscibility with

Water at 20 °C (68 °F): 0.05 g/l

· Partition coefficient (n-octanol/water): Not determined.

· Viscosity:

· Dynamic at 20 °C (68 °F):	0.94 mPas
· Kinematic:	Not determined.

· Other information: No further relevant information available.

US

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 5)

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	12705 mg/kg (rat)
------	------	-------------------

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
- Water hazard class 2 (Assessment by list): hazardous for water
- Do not allow product to reach ground water, water course or sewage system.
- Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 6)

- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- **UN-Number**
- **DOT, IMDG, IATA** UN1145

- **UN proper shipping name**
- **DOT** Cyclohexane
- **IMDG, IATA** CYCLOHEXANE

- **Transport hazard class(es)**
- **DOT**



- **Class** 3 Flammable liquids
- **Label** 3

- **IMDG, IATA**



- **Class** 3 Flammable liquids
- **Label** 3

- **Packing group**
- **DOT, IMDG, IATA** II

- **Environmental hazards:** Environmentally hazardous substance, liquid
- **Marine pollutant:** No

- **Special precautions for user** Warning: Flammable liquids
- **Danger code (Kemler):** 33
- **EMS Number:** 3-07
- **Stowage Category** E

- **Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.

- **Transport/Additional information:**

- **DOT**
 - **Quantity limitations** On passenger aircraft/rail: 5 L
On cargo aircraft only: 60 L
 - **Hazardous substance:** 1000 lbs, 454 kg
-
- **IMDG**
 - **Limited quantities (LQ)** 1L
 - **Excepted quantities (EQ)** Code: E2
Maximum net quantity per inner packaging: 30 ml
Maximum net quantity per outer packaging: 500 ml

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 7)

· UN "Model Regulation": UN 1145 CYCLOHEXANE, 3, II

15 Regulatory information

- *Safety, health and environmental regulations/legislation specific for the substance or mixture*
- *Sara*
- *Section 355 (extremely hazardous substances): Substance is not listed.*
- *Section 313 (Specific toxic chemical listings): Substance is listed.*
- *TSCA (Toxic Substances Control Act): Substance is listed.*
- *Proposition 65*
- *Chemicals known to cause cancer: Substance is not listed.*
- *Chemicals known to cause reproductive toxicity for females: Substance is not listed.*
- *Chemicals known to cause reproductive toxicity for males: Substance is not listed.*
- *Chemicals known to cause developmental toxicity: Substance is not listed.*
- *Carcinogenic categories*
- *EPA (Environmental Protection Agency) I*
- *TLV (Threshold Limit Value established by ACGIH) Substance is not listed.*
- *NIOSH-Ca (National Institute for Occupational Safety and Health) Substance is not listed.*
- *GHS label elements The substance is classified and labeled according to the Globally Harmonized System (GHS).*
- *Hazard pictograms*



GHS02 GHS07 GHS08

- *Signal word Danger*
- *Hazard statements*
 - Highly flammable liquid and vapor.*
 - Causes skin irritation.*
 - May cause drowsiness or dizziness.*
 - May be fatal if swallowed and enters airways.*
- *Precautionary statements*
 - Keep away from heat/sparks/open flames/hot surfaces. No smoking.*
 - Ground/bond container and receiving equipment.*
 - Use explosion-proof electrical/ventilating/lighting/equipment.*
 - Use only non-sparking tools.*
 - Take precautionary measures against static discharge.*
 - Avoid breathing dust/fume/gas/mist/vapors/spray*
 - Wash thoroughly after handling.*
 - Use only outdoors or in a well-ventilated area.*
 - Wear protective gloves/protective clothing/eye protection/face protection.*
 - IF SWALLOWED: Immediately call a POISON CENTER/ doctor.*
 - If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.*
 - IF INHALED: Remove person to fresh air and keep comfortable for breathing.*
 - Call a POISON CENTER/doctor if you feel unwell.*
 - Specific treatment (see on this label).*
 - Do NOT induce vomiting.*
 - If skin irritation occurs: Get medical advice/attention.*
 - Take off contaminated clothing and wash it before reuse.*
 - In case of fire: Use for extinction: CO2, powder or water spray.*

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/19/2017

Reviewed on 10/19/2017

Trade name: Cyclohexane, Reagent ACS Grade

(Contd. of page 8)

Store in a well-ventilated place. Keep container tightly closed.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

Creation date for SDS 02-03-2014. STN

10-19-2017: review SDS for accuracy. STN

10/19/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Flam. Liq. 2: Flammable liquids – Category 2

Skin Irrit. 2: Skin corrosion/irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Asp. Tox. 1: Aspiration hazard – Category 1