

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

1 Identification

- **Product identifier**
- **Trade name:** Dichloromethane, Reagent ACS Grade
- **Article number:** D4653
- **CAS Number:**
75-09-2
- **EC number:**
200-838-9
- **Index number:**
602-004-00-3
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS08 Health hazard

Carc. 1B H350 May cause cancer.
 STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.



GHS07

Acute Tox. 4 H302 Harmful if swallowed.
 Skin Irrit. 2 H315 Causes skin irritation.
 Eye Irrit. 2A H319 Causes serious eye irritation.
 STOT SE 3 H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS07 GHS08

- **Signal word** *Danger*

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 1)

· **Hazard statements**

- Harmful if swallowed.
- Causes skin irritation.
- Causes serious eye irritation.
- May cause cancer.
- May cause respiratory irritation. May cause drowsiness or dizziness.
- May cause damage to organs through prolonged or repeated exposure.

· **Precautionary statements**

- Obtain special instructions before use.
- Do not handle until all safety precautions have been read and understood.
- Do not breathe dust/fume/gas/mist/vapors/spray.
- Wash thoroughly after handling.
- Do not eat, drink or smoke when using this product.
- Use only outdoors or in a well-ventilated area.
- Wear protective gloves/protective clothing/eye protection/face protection.
- If swallowed: Call a poison center/doctor if you feel unwell.
- If on skin: Wash with plenty of water.
- IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- IF exposed or concerned: Get medical advice/attention.
- Get medical advice/attention if you feel unwell.
- Specific treatment (see on this label).
- Rinse mouth.
- If skin irritation occurs: Get medical advice/attention.
- If eye irritation persists: Get medical advice/attention.
- Take off contaminated clothing and wash it before reuse.
- Store in a well-ventilated place. Keep container tightly closed.
- Store locked up.
- Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

75-09-2 Dichloromethane (Methylene Chloride)

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 2)

- **Identification number(s)**
- **EC number:** 200-838-9
- **Index number:** 602-004-00-3

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Immediately call a doctor.
- **Information for doctor:**
· **Most important symptoms and effects, both acute and delayed** No further relevant information available.
· **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Mount respiratory protective device.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 200 ppm
- **PAC-2:** 560 ppm
- **PAC-3:** 6,900 ppm

US
(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 3)

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
*Ensure good ventilation/exhaustion at the workplace.
 Open and handle receptacle with care.
 Prevent formation of aerosols.*
- **Information about protection against explosions and fires:** *Keep respiratory protective device available.*
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** *No special requirements.*
- **Information about storage in one common storage facility:** *Not required.*
- **Further information about storage conditions:** *Keep receptacle tightly sealed.*
- **Specific end use(s)** *No further relevant information available.*

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** *No further data; see item 7.*
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 75-09-2 Dichloromethane (Methylene Chloride)

| | |
|------------|---|
| <i>PEL</i> | <i>Short-term value: 125 ppm Long-term value: 25 ppm see 29 CFR 1910.1052</i> |
| <i>REL</i> | <i>See Pocket Guide App. A</i> |
| <i>TLV</i> | <i>Long-term value: 174 mg/m³, 50 ppm BEI</i> |

- **Ingredients with biological limit values:**

CAS: 75-09-2 Dichloromethane (Methylene Chloride)

| | |
|------------|--|
| <i>BEI</i> | <i>0.3 mg/L LD50 Intraperitoneal: urine Time: end of shift LD50: Dichloromethane (semi-quantitative)</i> |
|------------|--|

- **Additional information:** *The lists that were valid during the creation were used as basis.*

- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
*Keep away from foodstuffs, beverages and feed.
 Immediately remove all soiled and contaminated clothing.
 Wash hands before breaks and at the end of work.
 Store protective clothing separately.
 Avoid contact with the eyes and skin.*
- **Breathing equipment:**
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 4)

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** Protective work clothing

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

| | |
|------------------------|-----------------|
| Form: | Liquid |
| Color: | Colorless |
| Odor: | Ether-like |
| Odor threshold: | Not determined. |

· **pH-value:** Not determined.

· **Change in condition**

| | |
|-------------------------------------|---------------|
| Melting point/Melting range: | Undetermined. |
| Boiling point/Boiling range: | Undetermined. |

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 605 °C (1,121 °F)

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Not determined.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

| | |
|---------------|----------|
| Lower: | 13 Vol % |
| Upper: | 22 Vol % |

· **Vapor pressure at 20 °C (68 °F):** 453 hPa (339.8 mm Hg)

· **Density at 20 °C (68 °F):** 1.33 g/cm³ (11.09885 lbs/gal)

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 5)

- | | |
|--|--|
| · Relative density | Not determined. |
| · Vapor density | Not determined. |
| · Evaporation rate | Not determined. |
| · Solubility in / Miscibility with Water at 20 °C (68 °F): 20 g/l | |
| · Partition coefficient (n-octanol/water): Not determined. | |
| · Viscosity: | |
| Dynamic at 20 °C (68 °F): | 0.43 mPas |
| Kinematic: | Not determined. |
| · Other information | No further relevant information available. |

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

| | | |
|--------------------|---------------------------|--------------------|
| Oral | LD50 | 1,600 mg/kg (rat) |
| Dermal | LD50 | >2,000 mg/kg (rat) |
| Inhalative | LC50/4 h | 52,000 mg/l (rat) |
| Irritation of skin | Skin Corrosion/Irritation | (rabbit) (Draize) |
| Irritation of eyes | Eye damage/eye irritation | (rabbit) |

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** 2A
- **NTP (National Toxicology Program)** R
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade



(Contd. of page 6)

- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (Assessment by list): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** *Disposal must be made according to official regulations.*

14 Transport information

- | | |
|---|---|
| <ul style="list-style-type: none"> · UN-Number · DOT, IMDG, IATA | <p style="margin-left: 20px;">UN1593</p> |
| <ul style="list-style-type: none"> · UN proper shipping name · DOT · IMDG, IATA | <p style="margin-left: 20px;">Dichloromethane DICHLOROMETHANE</p> |
| <ul style="list-style-type: none"> · Transport hazard class(es) · DOT | <p style="margin-left: 20px;"></p> |
| <ul style="list-style-type: none"> · Class · Label | <p style="margin-left: 20px;">6.1 Toxic substances 6.1</p> |
| <ul style="list-style-type: none"> · IMDG, IATA | <p style="margin-left: 20px;"></p> |
| <ul style="list-style-type: none"> · Class · Label | <p style="margin-left: 20px;">6.1 Toxic substances 6.1</p> |
| <ul style="list-style-type: none"> · Packing group · DOT, IMDG, IATA | <p style="margin-left: 20px;">III</p> |

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 7)

| | |
|--|--|
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Warning: Toxic substances |
| · Danger code (Kemler): | 60 |
| · EMS Number: | F-A,S-A |
| · Segregation groups | Liquid halogenated hydrocarbons |
| · Stowage Category | A |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · Transport/Additional information: | |
| · DOT | |
| · Quantity limitations | On passenger aircraft/rail: 60 L On cargo aircraft only: 220 L |
| · Hazardous substance: | 1000 lbs, 454 kg |
| · IMDG | |
| · Limited quantities (LQ) | 5L |
| · Excepted quantities (EQ) | Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml |
| · UN "Model Regulation": | UN 1593 DICHLOROMETHANE, 6.1, III |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.

· **TSCA (Toxic Substances Control Act):**

Dichloromethane (Methylene Chloride)

- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency) L**
- **TLV (Threshold Limit Value established by ACGIH) A3**
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS07 GHS08

- **Signal word** Danger

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 8)

- **Hazard statements**

Harmful if swallowed.
 Causes skin irritation.
 Causes serious eye irritation.
 May cause cancer.
 May cause respiratory irritation. May cause drowsiness or dizziness.
 May cause damage to organs through prolonged or repeated exposure.

- **Precautionary statements**

Obtain special instructions before use.
 Do not handle until all safety precautions have been read and understood.
 Do not breathe dust/fume/gas/mist/vapors/spray.
 Wash thoroughly after handling.
 Do not eat, drink or smoke when using this product.
 Use only outdoors or in a well-ventilated area.
 Wear protective gloves/protective clothing/eye protection/face protection.
 If swallowed: Call a poison center/doctor if you feel unwell.
 If on skin: Wash with plenty of water.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 IF exposed or concerned: Get medical advice/attention.
 Get medical advice/attention if you feel unwell.
 Specific treatment (see on this label).
 Rinse mouth.
 If skin irritation occurs: Get medical advice/attention.
 If eye irritation persists: Get medical advice/attention.
 Take off contaminated clothing and wash it before reuse.
 Store in a well-ventilated place. Keep container tightly closed.
 Store locked up.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

- **National regulations:**

- **Additional classification according to Decree on Hazardous Materials:**

Carcinogenic hazardous material group I (extremely dangerous).
 Carcinogenic hazardous material group II (very dangerous).
 Carcinogenic hazardous material group III (dangerous).

- **Information about limitation of use:**

Workers are not allowed to be exposed to this hazardous material. Exceptions can be made by the authorities in certain cases.

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Environment protection department.

- **Contact:**

- **Date of preparation / last revision**

Creation date for SDS 02-03-2014. STN
 10-25-2017: review SDS for accuracy. STN
 10/25/2017 / -

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

(Contd. on page 10)

Safety Data Sheet
acc. to OSHA HCS

Printing date 10/25/2017

Reviewed on 10/25/2017

Trade name: Dichloromethane, Reagent ACS Grade

(Contd. of page 9)

IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
ACGIH: American Conference of Governmental Industrial Hygienists
EINECS: European Inventory of Existing Commercial Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
NIOSH: National Institute for Occupational Safety
OSHA: Occupational Safety & Health
TLV: Threshold Limit Value
PEL: Permissible Exposure Limit
REL: Recommended Exposure Limit
BEI: Biological Exposure Limit
Acute Tox. 4: Acute toxicity – Category 4
Skin Irrit. 2: Skin corrosion/irritation – Category 2
Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A
Carc. 1B: Carcinogenicity – Category 1B
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

US