

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

1 Identification

- **Product identifier**
- **Trade name:** Chlorobenzene, Reagent ACS
- **Article number:** C3602
- **CAS Number:**
108-90-7
- **EC number:**
203-628-5
- **Index number:**
602-033-00-1
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 3 H226 Flammable liquid and vapor.



GHS07

Acute Tox. 4 H332 Harmful if inhaled.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS07

- **Signal word** Warning
- **Hazard statements**
Flammable liquid and vapor.
Harmful if inhaled.
- **Precautionary statements**
Keep away from heat/sparks/open flames/hot surfaces. No smoking.
Keep container tightly closed.

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 1)

Ground/bond container and receiving equipment.
 Use explosion-proof electrical/ventilating/lighting/equipment.
 Use only non-sparking tools.
 Take precautionary measures against static discharge.
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Use only outdoors or in a well-ventilated area.
 Wear protective gloves/protective clothing/eye protection/face protection.
 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 Call a POISON CENTER/doctor if you feel unwell.
 In case of fire: Use for extinction: CO₂, powder or water spray.
 Store in a well-ventilated place. Keep cool.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

108-90-7 Chlorobenzene

· **Identification number(s)**

· **EC number:** 203-628-5

· **Index number:** 602-033-00-1

4 First-aid measures

· **Description of first aid measures**

· **General information:**

Immediately remove any clothing soiled by the product.

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:**

Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.

In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately rinse with water.

· **After eye contact:** Rinse opened eye for several minutes under running water.

· **After swallowing:** If symptoms persist consult doctor.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 2)

- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 10 ppm
- **PAC-2:** 150 ppm
- **PAC-3:** 400 ppm

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
- **Information about protection against explosions and fires:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

US

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 3)

8 Exposure controls/personal protection

· **Additional information about design of technical systems:** No further data; see item 7.

· **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

CAS: 108-90-7 Chlorobenzene

PEL Long-term value: 350 mg/m³, 75 ppm

TLV Long-term value: 46 mg/m³, 10 ppm
BEI

· **Ingredients with biological limit values:**

CAS: 108-90-7 Chlorobenzene

BEI 100 mg/g creatinine
LD50 Intraperitoneal: urine
Time: end of shift at end of workweek
LD50: 4-Chlorocatechol with hydrolysis (nonspecific)

20 mg/g creatinine
LD50 Intraperitoneal: urine
Time: end of shift at end of workweek
LD50: p-Chlorophenol with hydrolysis (nonspecific)

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 4)

· **Body protection:** Protective work clothing

9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form:	Liquid
Color:	Colorless
Odor:	Aromatic
Odor threshold:	Not determined.

- **pH-value:** Not determined.

- **Change in condition**

Melting point/Melting range:	-45 °C (-49 °F)
Boiling point/Boiling range:	132 °C (270 °F)

- **Flash point:** 23 °C (73 °F)

- **Flammability (solid, gaseous):** Not applicable.

- **Ignition temperature:** 590 °C (1094 °F)

- **Decomposition temperature:** Not determined.

- **Auto igniting:** Not determined.

- **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.

- **Explosion limits:**

Lower:	1.3 Vol %
Upper:	11 Vol %

- **Vapor pressure at 20 °C (68 °F):** 12 hPa (9 mm Hg)

- **Density at 20 °C (68 °F):** 1.107 g/cm³ (9.238 lbs/gal)

- **Relative density** Not determined.

- **Vapor density** Not determined.

- **Evaporation rate** Not determined.

- **Solubility in / Miscibility with**

- Water at 20 °C (68 °F):** 0.49 g/l

- **Partition coefficient (n-octanol/water):** Not determined.

- **Viscosity:**

Dynamic at 20 °C (68 °F):	0.8 mPas
Kinematic:	Not determined.

- **Other information** No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.

- **Chemical stability**

- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

- **Possibility of hazardous reactions** No dangerous reactions known.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 5)

- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	2290 mg/kg (rat)
Inhalative	LC50/4 h	11 mg/l (ATE)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
- Water hazard class 2 (Assessment by list): hazardous for water
- Do not allow product to reach ground water, water course or sewage system.
- Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

US

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS



Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 6)

14 Transport information

· UN-Number	UN1134
· DOT, IMDG, IATA	
· UN proper shipping name	Chlorobenzene
· DOT	CHLOROBENZENE
· IMDG, IATA	
· Transport hazard class(es)	
· DOT	
	
· Class	3 Flammable liquids
· Label	3
· IMDG, IATA	
	
· Class	3 Flammable liquids
· Label	3
· Packing group	III
· DOT, IMDG, IATA	
· Environmental hazards:	Environmentally hazardous substance, liquid
· Marine pollutant:	No
· Special precautions for user	Warning: Flammable liquids
· Danger code (Kemler):	30
· EMS Number:	F-E,S-D
· Segregation groups	Liquid halogenated hydrocarbons
· Stowage Category	A
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· DOT	
· Quantity limitations	On passenger aircraft/rail: 60 L On cargo aircraft only: 220 L
· Hazardous substance:	100 lbs, 45.4 kg
· IMDG	
· Limited quantities (LQ)	5L
· Excepted quantities (EQ)	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· UN "Model Regulation":	UN 1134 CHLOROBENZENE, 3, III

US

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 7)

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.
- **TSCA (Toxic Substances Control Act):** Substance is listed.
- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency) D**
- **TLV (Threshold Limit Value established by ACGIH) A3**
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02 GHS07

- **Signal word** Warning
- **Hazard statements**
Flammable liquid and vapor.
Harmful if inhaled.
- **Precautionary statements**
Keep away from heat/sparks/open flames/hot surfaces. No smoking.
Keep container tightly closed.
Ground/bond container and receiving equipment.
Use explosion-proof electrical/ventilating/lighting/equipment.
Use only non-sparking tools.
Take precautionary measures against static discharge.
Avoid breathing dust/fume/gas/mist/vapors/spray
Use only outdoors or in a well-ventilated area.
Wear protective gloves/protective clothing/eye protection/face protection.
If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.
Call a POISON CENTER/doctor if you feel unwell.
In case of fire: Use for extinction: CO2, powder or water spray.
Store in a well-ventilated place. Keep cool.
Dispose of contents/container in accordance with local/regional/national/international regulations.
- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Environment protection department.
- **Contact:**

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/18/2017

Reviewed on 10/18/2017

Trade name: Chlorobenzene, Reagent ACS

(Contd. of page 8)

· Date of preparation / last revision*Creation date for SDS 02-17-2014. STN**10-18-2017: review SDS for accuracy. STN**10/18/2017 / -***· Abbreviations and acronyms:***ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)**IMDG: International Maritime Code for Dangerous Goods**DOT: US Department of Transportation**IATA: International Air Transport Association**ACGIH: American Conference of Governmental Industrial Hygienists**EINECS: European Inventory of Existing Commercial Chemical Substances**CAS: Chemical Abstracts Service (division of the American Chemical Society)**NFPA: National Fire Protection Association (USA)**HMIS: Hazardous Materials Identification System (USA)**LC50: Lethal concentration, 50 percent**LD50: Lethal dose, 50 percent**PBT: Persistent, Bioaccumulative and Toxic**vPvB: very Persistent and very Bioaccumulative**NIOSH: National Institute for Occupational Safety**OSHA: Occupational Safety & Health**TLV: Threshold Limit Value**PEL: Permissible Exposure Limit**REL: Recommended Exposure Limit**BEI: Biological Exposure Limit**Flam. Liq. 3: Flammable liquids – Category 3**Acute Tox. 4: Acute toxicity – Category 4*

US