

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

1 Identification

- **Product identifier**
- **Trade name:** N,N-Dimethylformamide, Reagent ACS Grade
- **Article number:** D4850
- **CAS Number:**
68-12-2
- **EC number:**
200-679-5
- **Index number:**
616-001-00-X
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 3 H226 Flammable liquid and vapor.



GHS08 Health hazard

Repr. 1B H360 May damage fertility or the unborn child.



GHS07

Acute Tox. 4 H312 Harmful in contact with skin.

Acute Tox. 4 H332 Harmful if inhaled.

Eye Irrit. 2A H319 Causes serious eye irritation.

- **Label elements**

- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: N,N-Dimethylformamide, Reagent ACS Grade

(Contd. of page 1)

· **Hazard pictograms**



· **Signal word** *Danger*

· **Hazard statements**

*Flammable liquid and vapor.
Harmful in contact with skin or if inhaled.
Causes serious eye irritation.
May damage fertility or the unborn child.*

· **Precautionary statements**

*Obtain special instructions before use.
Do not handle until all safety precautions have been read and understood.
Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
Keep container tightly closed.
Ground/bond container and receiving equipment.
Use explosion-proof electrical/ventilating/lighting/equipment.
Use only non-sparking tools.
Take precautionary measures against static discharge.
Avoid breathing dust/fume/gas/mist/vapors/spray
Wash thoroughly after handling.
Use only outdoors or in a well-ventilated area.
Wear protective gloves/protective clothing/eye protection/face protection.
If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
Continue rinsing.
IF exposed or concerned: Get medical advice/attention.
Call a poison center/doctor if you feel unwell.
Specific treatment (see on this label).
If eye irritation persists: Get medical advice/attention.
Take off contaminated clothing and wash it before reuse.
In case of fire: Use for extinction: CO₂, powder or water spray.
Store in a well-ventilated place. Keep cool.
Store locked up.
Dispose of contents/container in accordance with local/regional/national/international regulations.*

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: *N,N-Dimethylformamide, Reagent ACS Grade*

(Contd. of page 2)

· **vPvB:** *Not applicable.*

3 Composition/information on ingredients

- **Chemical characterization:** *Substances*
- **CAS No. Description**
68-12-2 N,N-Dimethylformamide
- **Identification number(s)**
- **EC number:** *200-679-5*
- **Index number:** *616-001-00-X*

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.
- **After inhalation:**
Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** *Immediately rinse with water.*
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** *If symptoms persist consult doctor.*
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** *No further relevant information available.*
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **Special hazards arising from the substance or mixture** *No further relevant information available.*
- **Advice for firefighters**
- **Protective equipment:** *Mouth respiratory protective device.*

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: N,N-Dimethylformamide, Reagent ACS Grade

(Contd. of page 3)

- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 2 ppm
- **PAC-2:** 91 ppm
- **PAC-3:** 530 ppm

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
Prevent formation of aerosols.
- **Information about protection against explosions and fires:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Keep respiratory protective device available.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 68-12-2 N,N-Dimethylformamide

PEL Long-term value: 30 mg/m³, 10 ppm
Skin

REL Long-term value: 30 mg/m³, 10 ppm
Skin

TLV Long-term value: (30) NIC-15 mg/m³, (10) NIC-5 ppm
NIC-A3; Skin; BEI

- **Ingredients with biological limit values:**

CAS: 68-12-2 N,N-Dimethylformamide

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: *N,N-Dimethylformamide, Reagent ACS Grade*

(Contd. of page 4)

| |
|---|
| <p>BEI 15 mg/L <i>LD50 Intraperitoneal: urine</i> <i>Time: end of shift</i> <i>LD50: N-Methylformamide</i></p> <p>40 mg/L <i>LD50 Intraperitoneal: urine</i> <i>Time: prior to last shift of workweek</i> <i>LD50: N-Acetyl-S-(N-methylcarbamoyl) cysteine (semi-quantitative)</i></p> |
|---|

· **Additional information:** *The lists that were valid during the creation were used as basis.*

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** *Protective work clothing*

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: *Liquid*

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: N,N-Dimethylformamide, Reagent ACS Grade

(Contd. of page 5)

| | |
|---|--|
| · Color: | Colorless |
| · Odor: | Amine-like |
| · Odor threshold: | Not determined. |
| · pH-value: | 7 |
| · Change in condition | |
| Melting point/Melting range: | -61 °C (-77.8 °F) |
| Boiling point/Boiling range: | 152.5-153.5 °C (306.5-308.3 °F) |
| · Flash point: | 58 °C (136.4 °F) |
| · Flammability (solid, gaseous): | Not applicable. |
| · Ignition temperature: | 440 °C (824 °F) |
| · Decomposition temperature: | Not determined. |
| · Auto igniting: | Not determined. |
| · Danger of explosion: | Not determined. |
| · Explosion limits: | |
| Lower: | 2.2 Vol % |
| Upper: | 16 Vol % |
| · Vapor pressure at 20 °C (68 °F): | 3.5 hPa (2.6 mm Hg) |
| · Density at 20 °C (68 °F): | 0.95 g/cm ³ (7.92775 lbs/gal) |
| · Relative density | Not determined. |
| · Vapor density | Not determined. |
| · Evaporation rate | Not determined. |
| · Solubility in / Miscibility with | |
| Water: | Fully miscible. |
| · Partition coefficient (n-octanol/water): | Not determined. |
| · Viscosity: | |
| Dynamic at 20 °C (68 °F): | 0.802 mPas |
| Kinematic: | Not determined. |
| · Other information | No further relevant information available. |

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

US

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: *N,N-Dimethylformamide, Reagent ACS Grade*

(Contd. of page 6)

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

- **LD/LC50 values that are relevant for classification:**

| | | |
|------------|----------|----------------------|
| Oral | LD50 | 2,800 mg/kg (rat) |
| Dermal | LD50 | 4,720 mg/kg (rabbit) |
| Inhalative | LC50/4 h | 9,400 mg/l (mouse) |

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer) 3**
- **NTP (National Toxicology Program) Substance is not listed.**
- **OSHA-Ca (Occupational Safety & Health Administration) Substance is not listed.**

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
- Water hazard class 2 (Assessment by list): hazardous for water
- Do not allow product to reach ground water, water course or sewage system.
- Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

US

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS



Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: *N,N-Dimethylformamide, Reagent ACS Grade*

(Contd. of page 7)

14 Transport information

| | |
|---|---|
| · UN-Number | UN2265 |
| · DOT, IMDG, IATA | |
| · UN proper shipping name | <i>N,N-Dimethylformamide</i> |
| · DOT | <i>N,N-Dimethylformamide</i> |
| · IMDG, IATA | <i>N,N-DIMETHYLFORMAMIDE</i> |
| · Transport hazard class(es) | |
| · DOT | |
|  | |
| · Class | <i>3 Flammable liquids</i> |
| · Label | <i>3</i> |
| · IMDG, IATA | |
|  | |
| · Class | <i>3 Flammable liquids</i> |
| · Label | <i>3</i> |
| · Packing group | |
| · DOT, IMDG, IATA | <i>III</i> |
| · Environmental hazards: | |
| · Marine pollutant: | <i>No</i> |
| · Special precautions for user | <i>Warning: Flammable liquids</i> |
| · Danger code (Kemler): | <i>30</i> |
| · EMS Number: | <i>3-06</i> |
| · Stowage Category | <i>A</i> |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | <i>Not applicable.</i> |
| · Transport/Additional information: | |
| · DOT | |
| · Quantity limitations | <i>On passenger aircraft/rail: 60 L On cargo aircraft only: 220 L</i> |
| · Hazardous substance: | <i>100 lbs, 45.4 kg</i> |
| · IMDG | |
| · Limited quantities (LQ) | <i>5L</i> |
| · Excepted quantities (EQ) | <i>Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml</i> |
| · UN "Model Regulation": | <i>UN 2265 N,N-DIMETHYLFORMAMIDE, 3, III</i> |

US

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: N,N-Dimethylformamide, Reagent ACS Grade

(Contd. of page 8)

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.

| |
|---|
| · TSCA (Toxic Substances Control Act): |
|---|

| |
|-----------------------|
| N,N-Dimethylformamide |
|-----------------------|

- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH) A4**
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02 GHS07 GHS08

- **Signal word** *Danger*
- **Hazard statements**
 - Flammable liquid and vapor.*
 - Harmful in contact with skin or if inhaled.*
 - Causes serious eye irritation.*
 - May damage fertility or the unborn child.*
- **Precautionary statements**
 - Obtain special instructions before use.*
 - Do not handle until all safety precautions have been read and understood.*
 - Keep away from heat/sparks/open flames/hot surfaces. - No smoking.*
 - Keep container tightly closed.*
 - Ground/bond container and receiving equipment.*
 - Use explosion-proof electrical/ventilating/lighting/equipment.*
 - Use only non-sparking tools.*
 - Take precautionary measures against static discharge.*
 - Avoid breathing dust/fume/gas/mist/vapors/spray*
 - Wash thoroughly after handling.*
 - Use only outdoors or in a well-ventilated area.*
 - Wear protective gloves/protective clothing/eye protection/face protection.*
 - If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.*
 - IF INHALED: Remove person to fresh air and keep comfortable for breathing.*
 - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*
 - IF exposed or concerned: Get medical advice/attention.*
 - Call a poison center/doctor if you feel unwell.*
 - Specific treatment (see on this label).*
 - If eye irritation persists: Get medical advice/attention.*
 - Take off contaminated clothing and wash it before reuse.*

(Contd. on page 10)

Safety Data Sheet

acc. to OSHA HCS

Printing date 10/26/2017

Reviewed on 10/26/2017

Trade name: N,N-Dimethylformamide, Reagent ACS Grade

(Contd. of page 9)

In case of fire: Use for extinction: CO2, powder or water spray.

Store in a well-ventilated place. Keep cool.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

Creation date for SDS 02-04-2014. STN

10-26-2017: review SDS for accuracy. STN

10/26/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

BEI: Biological Exposure Limit

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A

Repr. 1B: Reproductive toxicity – Category 1B