

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

## 1 Identification

- **Product identifier**
- **Trade name:** Ethyl Acetate, Reagent ACS Grade
- **Article number:** E2404
- **CAS Number:**  
141-78-6
- **EC number:**  
205-500-4
- **Index number:**  
607-022-00-5
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
Aqua Solutions, Inc.  
6913 Highway 225  
DEER PARK, TX 77536  
USA  
800-256-2586
- **Information department:**  
Technical Coordinator  
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**  
Chemtec: 800-424-9300  
Canutec: 613-996-6666



## 2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 2 H225 Highly flammable liquid and vapor.



GHS07

Eye Irrit. 2A H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Label elements**

· **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS02



GHS07

- **Signal word** *Danger*

- **Hazard statements**

Highly flammable liquid and vapor.

Causes serious eye irritation.

May cause drowsiness or dizziness.

(Contd. on page 2)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

**Trade name: Ethyl Acetate, Reagent ACS Grade**

(Contd. of page 1)

· **Precautionary statements**

- Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
- Ground/bond container and receiving equipment.
- Use explosion-proof electrical/ventilating/lighting/equipment.
- Use only non-sparking tools.
- Take precautionary measures against static discharge.
- Avoid breathing dust/fume/gas/mist/vapors/spray
- Wash thoroughly after handling.
- Use only outdoors or in a well-ventilated area.
- Wear protective gloves/protective clothing/eye protection/face protection.
- If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
- IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- Call a poison center/doctor if you feel unwell.
- If eye irritation persists: Get medical advice/attention.
- In case of fire: Use for extinction: CO<sub>2</sub>, powder or water spray.
- Store in a well-ventilated place. Keep container tightly closed.
- Store in a well-ventilated place. Keep cool.
- Store locked up.
- Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

## 3 Composition/information on ingredients

- **Chemical characterization: Substances**
- **CAS No. Description**  
141-78-6 Ethyl Acetate
- **Identification number(s)**
- **EC number:** 205-500-4
- **Index number:** 607-022-00-5

## 4 First-aid measures

- **Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

**Trade name: Ethyl Acetate, Reagent ACS Grade**

(Contd. of page 2)

- **After skin contact:** Immediately rinse with water.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

## 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

## 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 1,200 ppm
- **PAC-2:** 1,700 ppm
- **PAC-3:** 10000\*\* ppm

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
Prevent formation of aerosols.
- **Information about protection against explosions and fires:**  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

**Trade name: Ethyl Acetate, Reagent ACS Grade**

(Contd. of page 3)

- **Further information about storage conditions:**  
 Keep receptacle tightly sealed.  
 Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.

- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

**CAS: 141-78-6 Ethyl Acetate**

PEL Long-term value: 1400 mg/m<sup>3</sup>, 400 ppm

REL Long-term value: 1400 mg/m<sup>3</sup>, 400 ppm

TLV Long-term value: 1440 mg/m<sup>3</sup>, 400 ppm

- **Additional information:** The lists that were valid during the creation were used as basis.

- **Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

- Keep away from foodstuffs, beverages and feed.
- Immediately remove all soiled and contaminated clothing.
- Wash hands before breaks and at the end of work.
- Avoid contact with the eyes.
- Avoid contact with the eyes and skin.

- **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:**



Tightly sealed goggles

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

Trade name: Ethyl Acetate, Reagent ACS Grade

(Contd. of page 4)

· **Body protection:** Protective work clothing

## 9 Physical and chemical properties

· **Information on basic physical and chemical properties**· **General Information**· **Appearance:**

<b>Form:</b>	Liquid
<b>Color:</b>	Colorless
<b>Odor:</b>	Fruit-like
<b>Odor threshold:</b>	Not determined.

· **pH-value:** Not determined.· **Change in condition**

<b>Melting point/Melting range:</b>	-83.57 °C (-118.4 °F)
<b>Boiling point/Boiling range:</b>	77-78 °C (170.6-172.4 °F)

· **Flash point:** -1 °C (30.2 °F)· **Flammability (solid, gaseous):** Not applicable.· **Ignition temperature:** 460 °C (860 °F)· **Decomposition temperature:** Not determined.· **Auto igniting:** Not determined.· **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.· **Explosion limits:**

<b>Lower:</b>	2.1 Vol %
<b>Upper:</b>	11.5 Vol %

· **Vapor pressure at 20 °C (68 °F):** 97 hPa (72.8 mm Hg)· **Density at 20 °C (68 °F):** 0.9 g/cm<sup>3</sup> (7.5105 lbs/gal)· **Relative density** Not determined.· **Vapor density** Not determined.· **Evaporation rate** Not determined.· **Solubility in / Miscibility with**· **Water at 20 °C (68 °F):** 79 g/l· **Partition coefficient (n-octanol/water):** Not determined.· **Viscosity:**

<b>Dynamic at 20 °C (68 °F):</b>	0.44 mPas
<b>Kinematic:</b>	Not determined.

· **Other information** No further relevant information available.

## 10 Stability and reactivity

· **Reactivity** No further relevant information available.· **Chemical stability**· **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.· **Possibility of hazardous reactions** No dangerous reactions known.

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

**Trade name:** Ethyl Acetate, Reagent ACS Grade

(Contd. of page 5)

- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	5,620 mg/kg (rabbit)
Inhalative	LC50/4 h	1,600 mg/l (rat)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

## 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
- Water hazard class 1 (Assessment by list): slightly hazardous for water
- Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

US

(Contd. on page 7)

# Safety Data Sheet

acc. to OSHA HCS



Printing date 11/06/2017

Reviewed on 11/06/2017

Trade name: Ethyl Acetate, Reagent ACS Grade

(Contd. of page 6)

## 14 Transport information

<b>· UN-Number</b>	UN1173
<b>· DOT, IMDG, IATA</b>	
<b>· UN proper shipping name</b>	Ethyl acetate
<b>· DOT</b>	ETHYL ACETATE
<b>· IMDG, IATA</b>	
<b>· Transport hazard class(es)</b>	
<b>· DOT</b>	
	
<b>· Class</b>	3 Flammable liquids
<b>· Label</b>	3
<b>· IMDG, IATA</b>	
	
<b>· Class</b>	3 Flammable liquids
<b>· Label</b>	3
<b>· Packing group</b>	II
<b>· DOT, IMDG, IATA</b>	
<b>· Environmental hazards:</b>	
<b>· Marine pollutant:</b>	No
<b>· Special precautions for user</b>	Warning: Flammable liquids
<b>· Danger code (Kemler):</b>	33
<b>· EMS Number:</b>	3-07
<b>· Stowage Category</b>	B
<b>· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
<b>· Transport/Additional information:</b>	
<b>· DOT</b>	
<b>· Quantity limitations</b>	On passenger aircraft/rail: 5 L On cargo aircraft only: 60 L
<b>· Hazardous substance:</b>	5000 lbs, 2270 kg
<b>· IMDG</b>	
<b>· Limited quantities (LQ)</b>	1L
<b>· Excepted quantities (EQ)</b>	Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
<b>· UN "Model Regulation":</b>	UN 1173 ETHYL ACETATE, 3, II

US

(Contd. on page 8)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

Trade name: Ethyl Acetate, Reagent ACS Grade

(Contd. of page 7)

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is not listed.

· <b>TSCA (Toxic Substances Control Act):</b>
---

Ethyl Acetate
---------------

- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02    GHS07

- **Signal word** *Danger*
- **Hazard statements**
  - Highly flammable liquid and vapor.*
  - Causes serious eye irritation.*
  - May cause drowsiness or dizziness.*
- **Precautionary statements**
  - Keep away from heat/sparks/open flames/hot surfaces. - No smoking.*
  - Ground/bond container and receiving equipment.*
  - Use explosion-proof electrical/ventilating/lighting/equipment.*
  - Use only non-sparking tools.*
  - Take precautionary measures against static discharge.*
  - Avoid breathing dust/fume/gas/mist/vapors/spray*
  - Wash thoroughly after handling.*
  - Use only outdoors or in a well-ventilated area.*
  - Wear protective gloves/protective clothing/eye protection/face protection.*
  - If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.*
  - IF INHALED: Remove person to fresh air and keep comfortable for breathing.*
  - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*
  - Call a poison center/doctor if you feel unwell.*
  - If eye irritation persists: Get medical advice/attention.*
  - In case of fire: Use for extinction: CO2, powder or water spray.*
  - Store in a well-ventilated place. Keep container tightly closed.*
  - Store in a well-ventilated place. Keep cool.*
  - Store locked up.*
  - Dispose of contents/container in accordance with local/regional/national/international regulations.*

(Contd. on page 9)



# Safety Data Sheet

## acc. to OSHA HCS

Printing date 11/06/2017

Reviewed on 11/06/2017

**Trade name: Ethyl Acetate, Reagent ACS Grade**

(Contd. of page 8)

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### 16 Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

11-06-2017: review SDS for accuracy. STN

Creation date for SDS 02-04-2014 . STN

11/06/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Flam. Liq. 2: Flammable liquids – Category 2

Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

US