

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

1 Identification

- **Product identifier**
- **Trade name:** Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal
- **Article number:** F2530
- **CAS Number:**
7782-61-8
- **EC number:**
233-899-5
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS03 Flame over circle

Ox. Sol. 3 H272 May intensify fire; oxidizer.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2A H319 Causes serious eye irritation.

STOT SE 3 H335 May cause respiratory irritation.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS03 GHS07

- **Signal word** Warning
- **Hazard statements**
May intensify fire; oxidizer.
Causes skin irritation.
Causes serious eye irritation.
May cause respiratory irritation.

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 1)

· **Precautionary statements**

Keep/Store away from clothing/combustible materials.

Avoid breathing dust/fume/gas/mist/vapors/spray

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

Store in a well-ventilated place. Keep container tightly closed.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



Health = 2

Fire = 3

Reactivity = 1

The substance possesses oxidizing properties.

· **HMIS-ratings (scale 0 - 4)**



Health = 2

Fire = 3

Reactivity = 1

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

7782-61-8 Ferric Nitrate

· **Identification number(s)**

· **EC number:** 233-899-5

4 First-aid measures

· **Description of first aid measures**

· **After inhalation:** *In case of unconsciousness place patient stably in side position for transportation.*

· **After skin contact:** *Immediately wash with water and soap and rinse thoroughly.*

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** *If symptoms persist consult doctor.*

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** *No further relevant information available.*

· **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 2)

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** No special measures required.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 22 mg/m³
- **PAC-2:** 110 mg/m³
- **PAC-3:** 640 mg/m³

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing.
Wash hands before breaks and at the end of work.
Avoid contact with the eyes and skin.

(Contd. on page 4)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 3)

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

· **Body protection:** Protective work clothing

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Crystalline
Color:	Pale violet
Odor:	Nitric
Odor threshold:	Not determined.

· **pH-value:** Not applicable.

· **Change in condition**

Melting point/Melting range:	47 °C (116.6 °F)
Boiling point/Boiling range:	100 °C (212 °F)

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Product is not flammable.

· **Ignition temperature:**

Decomposition temperature: Not determined.

· **Auto igniting:** Not determined.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

Lower: Not determined.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 4)

Upper:	Not determined.
· Vapor pressure:	Not applicable.
· Density at 20 °C (68 °F):	1.68 g/cm ³ (14.0196 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not applicable.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with Water:	Not determined.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not applicable.
Kinematic:	Not applicable.
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	3,250 mg/kg (rat)
------	------	-------------------

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal



(Contd. of page 5)

- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Not known to be hazardous to water.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|---|-------------------------------|
| · UN-Number | UN1466 |
| · DOT, IMDG, IATA | |
| · UN proper shipping name | |
| · DOT | Ferric nitrate |
| · IMDG, IATA | FERRIC NITRATE |
| · Transport hazard class(es) | |
| · DOT | |
|  | |
| · Class | 5.1 Oxidizing substances |
| · Label | 5.1 |
| · IMDG, IATA | |
|  | |
| · Class | 5.1 Oxidizing substances |
| · Label | 5.1 |
| · Packing group | |
| · DOT, IMDG, IATA | III |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Warning: Oxidizing substances |
| · Poison inhalation hazard: | No |
| · Danger code (Kemler): | 5.1 |
| · EMS Number: | F-A,S-Q |

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 6)

· Stowage Category	A
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· DOT	
· Hazardous substance:	1000 lbs, 454 kg
· UN "Model Regulation":	UN 1466 FERRIC NITRATE, 5.1, III

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.
- **TSCA (Toxic Substances Control Act):**
- **TSCA new (21st Century Act) (Substances not listed)**
- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency)** Substance is not listed.
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS03 GHS07

- **Signal word** Warning
- **Hazard statements**
 - May intensify fire; oxidizer.
 - Causes skin irritation.
 - Causes serious eye irritation.
 - May cause respiratory irritation.
- **Precautionary statements**
 - Keep/Store away from clothing/combustible materials.
 - Avoid breathing dust/fume/gas/mist/vapors/spray
 - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 - Store in a well-ventilated place. Keep container tightly closed.
 - Store locked up.
 - Dispose of contents/container in accordance with local/regional/national/international regulations.

(Contd. on page 8)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 11/16/2017

Reviewed on 11/16/2017

Trade name: Ferric Nitrate Nonahydrate, Reagent ACS Grade Crystal

(Contd. of page 7)

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

11-16-2017: review SDS for accuracy. STN

Creation date for SDS 06-03-2014. STN

11/16/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Ox. Sol. 3: Oxidizing solids – Category 3

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3