

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

1 Identification

- **Product identifier**
- **Trade name:** Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃Mg,Ca,50 ppm MDEA in 2 mM HNO₃
- **Article number:** MOT009
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**
The product is not classified according to the Globally Harmonized System (GHS).
- **Label elements**
- **GHS label elements** Not Applicable
- **Hazard pictograms** Not Applicable
- **Signal word** Not Applicable
- **Hazard statements** Not Applicable
- **Precautionary statements**
If swallowed: Call a poison center/doctor if you feel unwell.
If on skin: Wash with plenty of water.
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Dispose of contents/container in accordance with local/regional/national/international regulations.
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**

	Health = 0
	Fire = 0
	Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**

<table border="1" style="display: inline-table;"><tr><td style="background-color: #0000FF; color: white; padding: 2px;">HEALTH</td><td style="width: 20px; text-align: center;">0</td></tr></table>	HEALTH	0	Health = 0
HEALTH	0		
<table border="1" style="display: inline-table;"><tr><td style="background-color: #FF0000; color: white; padding: 2px;">FIRE</td><td style="width: 20px; text-align: center;">0</td></tr></table>	FIRE	0	Fire = 0
FIRE	0		
<table border="1" style="display: inline-table;"><tr><td style="background-color: #FFFF00; padding: 2px;">REACTIVITY</td><td style="width: 20px; text-align: center;">0</td></tr></table>	REACTIVITY	0	Reactivity = 0
REACTIVITY	0		
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

US

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 1)

3 Composition/information on ingredients

- **Chemical characterization: Mixtures**
- **Description:** Mixture of the substances listed below with nonhazardous additions.
- **Dangerous components:** Not Applicable

· Table of Nonhazardous Ingredients

CAS: 7697-37-2	Nitric Acid	0.2%
CAS: 7447-40-7	Potassium Chloride	0.0095%
CAS: 7647-14-5	Sodium Chloride	0.0076%
CAS: 105-59-9	N-Methyldiethanolamine, 99%	0.005%
CAS: 7791-18-6	Magnesium Chloride Hexahydrate	0.0042%
CAS: 7447-41-8	Lithium Chloride	0.0031%
CAS: 10035-04-8	Calcium Chloride Dihydrate	0.0018%
CAS: 12125-02-9	Ammonium Chloride, Reagent ACS Grade	0.0016%
CAS: 141-43-5	2-Aminoethanol (Monoethanolamine), Reagent Grade	0.001%
CAS: 7732-18-5	Water	99.766%

4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

(Contd. on page 3)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 2)

Dispose contaminated material as waste according to item 13.

· **Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

· **Protective Action Criteria for Chemicals**

· **PAC-1:**

CAS: 7697-37-2	Nitric Acid	0.16 ppm
CAS: 7791-18-6	Magnesium Chloride Hexahydrate	34 mg/m ³
CAS: 7447-41-8	Lithium Chloride	2.3 mg/m ³
CAS: 10035-04-8	Calcium Chloride Dihydrate	16 mg/m ³
CAS: 12125-02-9	Ammonium Chloride, Reagent ACS Grade	20 mg/m ³
CAS: 141-43-5	2-Aminoethanol (Monoethanolamine), Reagent Grade	6 ppm

· **PAC-2:**

CAS: 7697-37-2	Nitric Acid	24 ppm
CAS: 7791-18-6	Magnesium Chloride Hexahydrate	370 mg/m ³
CAS: 7447-41-8	Lithium Chloride	25 mg/m ³
CAS: 10035-04-8	Calcium Chloride Dihydrate	170 mg/m ³
CAS: 12125-02-9	Ammonium Chloride, Reagent ACS Grade	54 mg/m ³
CAS: 141-43-5	2-Aminoethanol (Monoethanolamine), Reagent Grade	170 ppm

· **PAC-3:**

CAS: 7697-37-2	Nitric Acid	92 ppm
CAS: 7791-18-6	Magnesium Chloride Hexahydrate	1,600 mg/m ³
CAS: 7447-41-8	Lithium Chloride	150 mg/m ³
CAS: 10035-04-8	Calcium Chloride Dihydrate	1,100 mg/m ³
CAS: 12125-02-9	Ammonium Chloride, Reagent ACS Grade	330 mg/m ³
CAS: 141-43-5	2-Aminoethanol (Monoethanolamine), Reagent Grade	1,000 ppm

7 Handling and storage

· **Handling:**

· **Precautions for safe handling** No special measures required.

· **Information about protection against explosions and fires:** No special measures required.

· **Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** No special requirements.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** None.

· **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

· **Additional information about design of technical systems:** No further data; see item 7.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 3)

- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Goggles recommended during refilling.
- **Body protection:** Protective work clothing

9 Physical and chemical properties

· Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Liquid
Color:	Clear
Odor:	Odorless
Odor threshold:	Not determined.

· **pH-value:** Not determined.

· Change in condition

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	100 °C (212 °F)

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

· Ignition temperature:

Decomposition temperature: Not determined.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 4)

· Auto igniting:	Product is not selfigniting.
· Danger of explosion:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapor pressure at 20 °C (68 °F):	23 hPa (17.3 mm Hg)
· Density at 20 °C (68 °F):	1.0188 g/cm ³ (8.50189 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with Water:	Fully miscible.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	0.0 %
Water:	99.8 %
· VOC content:	0.00 %
	0.0 g/l / 0.00 lb/gl
· Solids content:	1.9 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.

(Contd. on page 6)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 5)

· **Additional toxicological information:**

The product is not subject to classification according to internally approved calculation methods for preparations:

When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

· **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

12 Ecological information

· **Toxicity**

· **Aquatic toxicity:** No further relevant information available.

· **Persistence and degradability** No further relevant information available.

· **Behavior in environmental systems:**

· **Bioaccumulative potential** No further relevant information available.

· **Mobility in soil** No further relevant information available.

· **Additional ecological information:**

· **General notes:**

Water hazard class 1 (Self-assessment): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **Other adverse effects** No further relevant information available.

13 Disposal considerations

· **Waste treatment methods**

· **Recommendation:** Smaller quantities can be disposed of with household waste.

· **Uncleaned packagings:**

· **Recommendation:** Disposal must be made according to official regulations.

· **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

· **UN-Number**

· **DOT, ADN, IMDG, IATA** Not regulated

· **UN proper shipping name**

· **DOT, ADN, IATA** Not regulated

· **IMDG** Not Regulated

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 6)

- | | |
|--|-----------------|
| · Transport hazard class(es) | |
| · DOT, ADN, IMDG, IATA | |
| · Class | Not regulated |
| · Packing group | |
| · DOT, IMDG, IATA | Not regulated |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Not applicable. |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | Not regulated |

15 Regulatory information

- Safety, health and environmental regulations/legislation specific for the substance or mixture
- Sara

· Section 355 (extremely hazardous substances):

CAS: 7697-37-2	Nitric Acid
----------------	-------------

· Section 313 (Specific toxic chemical listings):

CAS: 7697-37-2	Nitric Acid
----------------	-------------

· TSCA (Toxic Substances Control Act):

Nitric Acid

Potassium Chloride

Sodium Chloride

N-Methyldiethanolamine, 99%

Lithium Chloride

Ammonium Chloride, Reagent ACS Grade

2-Aminoethanol (Monoethanolamine), Reagent Grade

Water

· TSCA new (21st Century Act) (Substances not listed)

· Proposition 65

· Chemicals known to cause cancer:

None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

· Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/08/2017

Reviewed on 12/08/2017

**Trade name: Mixed IC Std 30ppm Na,10ppm
5 ppm ea:Li,K, NH₃,Mg,Ca,50 ppm MDEA in 2 mM HNO₃**

(Contd. of page 7)

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **GHS label elements** Not Applicable

- **Hazard pictograms** Not Applicable

- **Signal word** Not Applicable

- **Hazard statements** Not Applicable

- **Precautionary statements**

If swallowed: Call a poison center/doctor if you feel unwell.

If on skin: Wash with plenty of water.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Dispose of contents/container in accordance with local/regional/national/international regulations.

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Environment protection department.

- **Contact:**

- **Date of preparation / last revision**

12-08-2017: review SDS for accuracy. STN

Creation date for SDS 12-30-2014. STN

12/08/2017 / -

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit