

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

1 Identification

- **Product identifier**
- **Trade name:** Potassium Permanganate, Laboratory Grade Crystal
- **Article number:** P5444
- **CAS Number:**
7722-64-7
- **EC number:**
231-760-3
- **Index number:**
025-002-00-9
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Aqua Solutions, Inc.
6913 Highway 225
DEER PARK, TX 77536
USA
800-256-2586
- **Information department:**
Technical Coordinator
Sherman Nelson sherman@aquasolutions.org
- **Emergency telephone number:**
Chemtrec: 800-424-9300
Canutec: 613-996-6666



2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS03 Flame over circle

Ox. Sol. 2 H272 May intensify fire; oxidizer.



GHS07

Acute Tox. 4 H302 Harmful if swallowed.

- **Label elements**

- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS03



GHS07

- **Signal word** Danger

- **Hazard statements**

May intensify fire; oxidizer.

Harmful if swallowed.

- **Precautionary statements**

Keep away from heat.

Keep/Store away from clothing/combustible materials.

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 1)

Take any precaution to avoid mixing with combustibles.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Wear protective gloves/protective clothing/eye protection/face protection.

If swallowed: Call a poison center/doctor if you feel unwell.

Rinse mouth.

In case of fire: Use for extinction: CO₂, powder or water spray.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



Health = 1

Fire = 3

Reactivity = 0

The substance possesses oxidizing properties.

· **HMIS-ratings (scale 0 - 4)**



Health = 1

Fire = 3

Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

7722-64-7 Potassium Permanganate

· **Identification number(s)**

· **EC number:** 231-760-3

· **Index number:** 025-002-00-9

4 First-aid measures

· **Description of first aid measures**

· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.

· **After skin contact:** Generally the product does not irritate the skin.

· **After eye contact:** Rinse opened eye for several minutes under running water.

· **After swallowing:** Immediately call a doctor.

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 2)

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**
- **PAC-1:** 8.6 mg/m³
- **PAC-2:** 14 mg/m³
- **PAC-3:** 150 mg/m³

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

CAS: 7722-64-7 Potassium Permanganate

PEL	Ceiling limit value: 5 mg/m ³ as Mn
REL	Short-term value: 3 mg/m ³ Long-term value: 1 mg/m ³ as Mn
TLV	Long-term value: 0.02* 0.1** mg/m ³ as Mn; *respirable **inhalable fraction

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 3)

- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:** Not required.
- **Body protection:** Protective work clothing

9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form:	Crystalline
Color:	Dark purple
Odor:	Mild to odorless
Odor threshold:	Not determined.

- **pH-value:** Not applicable.

- **Change in condition**

Melting point/Melting range:	>240 °C (>464 °F)
Boiling point/Boiling range:	Undetermined.

- **Flash point:** Not applicable.

- **Flammability (solid, gaseous):** Product is not flammable.

- **Ignition temperature:**

Decomposition temperature:	Not determined.
-----------------------------------	-----------------

- **Auto igniting:** Not determined.

- **Danger of explosion:** Product does not present an explosion hazard.

- **Explosion limits:**

Lower:	Not determined.
---------------	-----------------

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 4)

Upper:	Not determined.
· Vapor pressure at 20 °C (68 °F):	0 hPa (0 mm Hg)
· Density at 20 °C (68 °F):	2.703 g/cm ³ (22.55654 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not applicable.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with Water at 20 °C (68 °F):	64.3 g/l
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not applicable.
Kinematic:	Not applicable.
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

Oral	LD50	500 mg/kg (ATE)
------	------	-----------------

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)** Substance is not listed.
- **NTP (National Toxicology Program)** Substance is not listed.
- **OSHA-Ca (Occupational Safety & Health Administration)** Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.

(Contd. on page 6)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal



(Contd. of page 5)

- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
*Water hazard class 3 (Assessment by list): extremely hazardous for water
 Do not allow product to reach ground water, water course or sewage system, even in small quantities.
 Danger to drinking water if even extremely small quantities leak into the ground.*
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|---------------------------------------|-------------------------------------------------------------------------------------|
| · UN-Number | UN1490 |
| · DOT, IMDG, IATA | |
| · UN proper shipping name | Potassium permanganate |
| · DOT | POTASSIUM PERMANGANATE |
| · IMDG, IATA | |
| · Transport hazard class(es) | |
| · DOT | |
| |  |
| · Class | 5.1 Oxidizing substances |
| · Label | 5.1 |
| | |
| · IMDG, IATA | |
| |  |
| · Class | 5.1 Oxidizing substances |
| · Label | 5.1 |
| · Packing group | II |
| · DOT, IMDG, IATA | |
| · Environmental hazards: | Environmentally hazardous substance, solid |
| · Marine pollutant: | No |
| · Special precautions for user | Warning: Oxidizing substances |

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 6)

· Danger code (Kemler):	50
· EMS Number:	F-H,S-Q
· Segregation groups	Permanganates
· Stowage Category	D
· Segregation Code	SG38 Stow "separated from" ammonium compounds. SG49 Stow "separated from" cyanides SG60 Stow "separated from" peroxides

· **Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.

· **Transport/Additional information:**

· **DOT**

· **Quantity limitations** On passenger aircraft/rail: 5 kg
On cargo aircraft only: 25 kg

· **Hazardous substance:** 100 lbs, 45.4 kg

· **IMDG**

· **Limited quantities (LQ)** 1 kg

· **Excepted quantities (EQ)** Code: E2
Maximum net quantity per inner packaging: 30 g
Maximum net quantity per outer packaging: 500 g

· **UN "Model Regulation":** UN 1490 POTASSIUM PERMANGANATE, 5.1, II

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):** Substance is not listed.
- **Section 313 (Specific toxic chemical listings):** Substance is listed.

· **TSCA (Toxic Substances Control Act):**

Potassium Permanganate

- **Proposition 65**
- **Chemicals known to cause cancer:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for females:** Substance is not listed.
- **Chemicals known to cause reproductive toxicity for males:** Substance is not listed.
- **Chemicals known to cause developmental toxicity:** Substance is not listed.
- **Carcinogenic categories**
- **EPA (Environmental Protection Agency) D**
- **TLV (Threshold Limit Value established by ACGIH)** Substance is not listed.
- **NIOSH-Ca (National Institute for Occupational Safety and Health)** Substance is not listed.
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS03 GHS07

- **Signal word** Danger
- **Hazard statements**
May intensify fire; oxidizer.

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2017

Reviewed on 12/22/2017

Trade name: Potassium Permanganate, Laboratory Grade Crystal

(Contd. of page 7)

Harmful if swallowed.

· **Precautionary statements**

Keep away from heat.

Keep/Store away from clothing/combustible materials.

Take any precaution to avoid mixing with combustibles.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Wear protective gloves/protective clothing/eye protection/face protection.

If swallowed: Call a poison center/doctor if you feel unwell.

Rinse mouth.

In case of fire: Use for extinction: CO2, powder or water spray.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:**

· **Date of preparation / last revision**

12-22-2017: review SDS for accuracy. STN

Creation date for SDS 02-06-2014. STN

12/22/2017 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Ox. Sol. 2: Oxidizing solids – Category 2

Acute Tox. 4: Acute toxicity – Category 4