

Safety Data Sheet

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision date: 19.05.2023

Version: 6.3

Print date: 19.05.2023

SECTION 1: Identification

Product identifier

Trade name/designation:	Water Laboratory Reagent
Product No.:	BDH1168
Synonyms:	none
CAS No.:	7732-18-5

Relevant identified uses of the substance or mixture and uses advised against

Recommended use	For Further Manufacturing Use Only
Uses advised against	Not for Human or Animal Drug Use

Details of the supplier of the safety data sheet

Supplier

VWR International LLC

Street	100 Matsonford Road Radnor Corporate Center, Building One, Suite 200 P. O. Box 6660
Postal code/City	Radnor, PA 19087
Telephone	+1-800-932-5000 toll-free within US/Canada +1-610-386-1700
Telefax	+1-610-728-2103

Emergency phone number

Telephone	+1-800-424-9300 (Chemtrec, 24 hrs/day, 7 days/week, USA)
-----------	--

Preparation Information

VWR International - Product Information Compliance

E-mail	SDS@avantorsciences.com
--------	-------------------------

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

GHS Classification in accordance with 29 CFR 1910.1200 (OSHA HCS)

This substance is classified as not hazardous according to regulation 29 CFR 1910.1200 (OSHA HCS).

2.2 Label elements

Labelling in accordance with 29 CFR 1910.1200 (OSHA HCS)

According to regulation 29 CFR 1910.1200 (OSHA HCS) the product does not have to be labelled.

Hazard(s) not otherwise classified (HNOC)
none

SECTION 3: Composition/information on ingredients

3.1 Substances

Substance name	Water
Molecular formula	H ₂ O
Molecular weight	18.02 g/mol
CAS No.	7732-18-5

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

Do not leave affected person unattended.

In case of inhalation

Remove casualty to fresh air and keep warm and at rest. Obtain medical attention if symptoms appear.

In case of skin contact

No special measures are necessary.

After eye contact:

No special measures are necessary.

In case of ingestion

No special measures are necessary.

Self-protection of the first aider

no data available

4.2 Most important symptoms/effects, acute and delayed

No known symptoms to date.

4.3 Indication of any immediate medical attention and special treatment needed

No special information on medical attention and special treatment available.

SECTION 5: Fire fighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.

Extinguishing media which must not be used for safety reasons

The product itself does not burn.

5.2 Specific hazards arising from the chemical

No special fire protection measures are necessary.

In case of fire may be liberated:

Pyrolysis products, toxic

5.3 Advice for firefighters

Non-combustible liquids.

The product itself does not burn.

No special fire protection measures are necessary.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Remove victim out of the danger area. No special measures are necessary.

6.2 Environmental precautions

No special environmental measures are necessary.

6.3 Methods and material for containment and cleaning up

Take up mechanically, placing in appropriate containers for disposal. Dispose according to legislation.

6.4 Reference to other sections

Personal protection equipment (PPE): see section 8 Disposal information: see section 13

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advices on safe handling

No special measures are necessary.

Measures to prevent fire, aerosol and dust generation

No special measures are necessary.

Measures required to protect the environment

No special measures are necessary.

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: Ambient temperature

Storage: Store in a dry place. Store in a closed container. Keep/Store only in original container. Packaging materials: Glass High density polyethylene (HDPE) Unsuitable materials and coatings of containers/equipment: No further relevant information available.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

8.2 Engineering controls

Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

Personal protection equipment (PPE)

Wear suitable protective clothing. When handling with chemical substances, protective clothing must be worn.

Eye/face protection

Eye glasses with side protection

Skin protection

Wear suitable gloves. When handling with chemical substances, protective gloves must be worn. In the case of wanting to use the gloves again, clean them before taking off and air them well. Check leak tightness/impermeability prior to use.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time	> 480 min

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time	> 480 min

Respiratory protection

Usually no personal respirative protection necessary.

Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Color:	colorless
(b) Odor:	no data available
(c) Odor threshold:	no data available

Safety relevant basic data

(d) pH:	5-9 (20 °C)
(e) Melting point/freezing point:	0 °C
(f) Initial boiling point and boiling range:	100 °C (1013 hPa)
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapor pressure:	23 hPa (20 °C)
(l) Vapor density:	no data available
(m) Density:	1 g/cm ³ (4 °C)
(n) Solubility(ies)	
Water solubility:	soluble (20 °C)
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	not applicable
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	0.952 mPa*s (20 °C)
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable
(u) Particle characteristics:	does not apply to liquids

9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

This material is non-reactive under normal conditions.

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

No further relevant information available.

10.4 Conditions to avoid

No further relevant information available.

10.5 Incompatible materials

No further relevant information available.

10.6 Hazardous decomposition products

No known hazardous decomposition products.

Decomposition products in case of fire: see section 5.

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

LD50: > 90 mL/kg - Rat - (Food Research Journal)

Acute dermal toxicity:

no data available

Acute inhalation toxicity:

no data available

Irritant and corrosive effects:

Primary irritation to the skin:

not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitization

In case of skin contact: not sensitizing

In case of inhalation: not sensitizing

STOT-single exposure

not applicable

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

No indication of human carcinogenicity.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

no data available

Daphnia toxicity:

no data available

Algae toxicity:

no data available

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

not applicable

12.6 Endocrine disrupting properties

This substance does not have endocrine disrupting properties with respect to the environment.

12.7 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

no data available

Waste code product: no data available

Appropriate disposal / Package

no data available

Additional information

no data available

SECTION 14: Transport information

Land transport (DOT)

No dangerous good in sense of this transport regulation.

Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
not relevant

Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Toxic Substances Control Act (TSCA)

Listed

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

SARA 313 Components

Not listed.

US State Regulations

Massachusetts Right To Know Components

Not listed.

Pennsylvania Right To Know Components

Not listed.

New Jersey Right To Know Components

Not listed.

California Prop. 65 Components

Not listed.

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists
 DOT - Department of Transportation
 IARC - International Agency for Research on Cancer
 IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
 ICAO-TI - International Civil Aviation Organization-Technical Instructions
 IMDG - International Maritime Code for Dangerous Goods
 LTV - Long Term Value
 NIOSH - National Institute for Occupational Safety and Health
 NTP - National Toxicology Program
 OSHA - Occupational Safety & Health Administration
 PBT - Persistent, Bioaccumulative and Toxic
 PEL - Permissible Exposure Limit
 STV - Short Term Value
 SVHC - Substances of Very High Concern
 TDG - Transport of Dangerous Goods
 TLV - Threshold Limit Value
 vPvB - very Persistent, very Bioaccumulative

Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

Revision date	Version	Print date
19.05.2023	6.3	19.05.2023

Additional information

Indication of changes	none/none
-----------------------	-----------

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guidance. The information in this document is based on the present state knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and his Affiliates shall not be held liable for any damage resulting from handling.