

# Safety Data Sheet

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision date: 14.04.2018

Version: 6.1

Print date: 14.04.2018

## SECTION 1: Identification

### Product identifier

Trade name/designation:	EDTA disodium salt dihydrate USP/ULTRA PURE
Product No.:	0105-INV
Synonyms:	no data available
CAS No.:	6381-92-6
Other means of identification:	

### Relevant identified uses of the substance or mixture and uses advised against

Recommended Use:	For Further Manufacturing Use Only
Uses advised against:	Not for Human or Animal Drug Use

### Details of the supplier of the safety data sheet

#### Supplier

##### **VWR International LLC**

Street	100 Matsonford Road Radnor Corporate Center, Building One, Suite 200 P. O. Box 6660
Postal code/city	Radnor, PA 19087
Telephone	+1-800-932-5000 toll-free within US/Canada +1-610-386-1700
Telefax:	+1-610-728-2103

## Manufacturer

### **VWR Chemicals, LLC**

Street 28600 Fountain Parkway  
Postal code/city Solon, OH 44139

### **Emergency telephone**

Telephone +1-800-424-9300 (Chemtrec, 24 hrs/day, 7 days/week, USA)

### **Preparation Information**

VWR International - Data Compliance

E-mail sds@vwr.com

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

#### **GHS Classification in accordance with 29 CFR 1910.1200 (OSHA HCS)**

This substance is classified as not hazardous according to regulation 29 CFR 1910.1200 (OSHA HCS)

### 2.2 Label elements

#### **Labelling in accordance with 29 CFR 1910.1200 (OSHA HCS)**

According to regulation 29 CFR 1910.1200 (OSHA HCS) the product does not have to be labelled.

#### **Hazards not otherwise classified (HNOC)**

Not regulated

## SECTION 3: Composition / information on ingredients

### 3.1 Substances

Substance name	EDTA disodium salt dihydrate
Molecular formula	C10H14N2O8Na2. 2H2O
Molecular weight	372.24 g/mol
CAS No.	6381-92-6

## SECTION 4: First aid measures

### 4.1 General information

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### **After inhalation**

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

### **In case of skin contact**

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

### **After eye contact**

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

### **In case of ingestion**

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

## **4.2 Most important symptoms/effects, acute and delayed**

no data available

## **4.3 Indication of any immediate medical attention and special treatment needed**

no data available

## **4.4 Self-protection of the first aider**

First aider: Pay attention to self-protection!

## **4.5 Information to physician**

no data available

## **SECTION 5: Firefighting measures**

### **5.1 Extinguishing media**

#### **Suitable extinguishing media**

The product itself does not burn.  
Co-ordinate fire-fighting measures to the fire surroundings.

#### **Extinguishing media which must not be used for safety reasons**

no restriction

### **5.2 Specific hazards arising from the chemical**

In case of fire may be liberated:  
Carbon monoxide  
Carbon dioxide (CO<sub>2</sub>)  
Nitrogen oxides (NO<sub>x</sub>)

### **5.3 Advice for firefighters**

DO NOT fight fire when fire reaches explosives.  
Protective equipment and precautions for firefighters  
Wear a self-contained breathing apparatus and chemical protective clothing.

### **Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses.  
Do not inhale explosion and combustion gases.  
Use water spray/stream to protect personnel and to cool endangered containers.  
In case of fire: Evacuate area.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Avoid dust formation.

### 6.2 Environmental precautions

Do not allow to enter into surface water or drains.

### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Clean contaminated articles and floor according to the environmental legislation. Collect in closed and suitable containers for disposal.

### 6.4 Additional information

Clear spills immediately.

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

Avoid: Inhalation Avoid contact with eyes and skin. Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Protect from moisture.

### 7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: Ambient temperature  
Keep container tightly closed and in a well-ventilated place.

### 7.3 Specific end use(s)

no data available

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Engineering controls

#### Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

#### Personal protection equipment (PPE)

Wear suitable protective clothing. When handling with chemical substances, protective clothing must be worn.

#### *Eye/face protection*

Eye glasses with side protection

#### *Skin protection*

Wear suitable gloves. When handling with chemical substances, protective gloves must be worn. In the case of wanting to use the gloves again, clean them before taking off and air them well. Check leak tightness/impermeability prior to use.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time (maximum wearing time):	> 480 min

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time (maximum wearing time):	> 480 min

*Respiratory protection*

Usually no personal respirative protection necessary.

*Additional information*

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

*Environmental exposure controls*

no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	solid
Color:	white
(b) Odour:	no data available
(c) Odour threshold:	no data available

#### Safety relevant basic data

(d) pH:	4-5 (50 g/l; H <sub>2</sub> O; 20 °C)
(e) Melting point/freezing point:	248 °C
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	100 °C
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Relative density:	no data available
(n) Solubility(ies)	
Water solubility (g/L):	100 g/l (20 °C)
Soluble (g/L) in Ethanol:	no data available
(o) Partition coefficient: n-octanol/water:	-11.7 (20 °C; calculated)
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable

### 9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry constant:	no data available

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

## 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

## 10.3 Possibility of hazardous reactions

no data available

## 10.4 Conditions to avoid

no data available

## 10.5 Incompatible materials

no data available

## 10.6 Hazardous decomposition products

no data available

## 10.7 Additional information

no data available

# SECTION 11: Toxicological information

## 11.1 Information on toxicological effects

### Acute effects

*Acute oral toxicity:*

LD50: < 2000 mg/kg - Rat - (Merck KGaA)

*Acute dermal toxicity:*

no data available

*Acute inhalation toxicity:*

no data available

### Irritant and corrosive effects

*Primary irritation to the skin:*

not applicable

*Irritation to eyes:*

not applicable

*Irritation to respiratory tract:*

not applicable

### Respiratory or skin sensitization

In case of skin contact: not sensitising

After inhalation: not sensitising

### STOT-single exposure

not applicable

### STOT-repeated exposure

not applicable

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

**Carcinogenicity**

The table below indicates whether each agency has listed any ingredient as a carcinogen.

no data available	ACGIH	IARC	NTP	OSHA

**Germ cell mutagenicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

**SECTION 12: Ecological information**

**12.1 Ecotoxicity**

**Fish toxicity:**

no data available

**Daphnia toxicity:**

no data available

**Algae toxicity:**

no data available

**Bacteria toxicity:**

no data available

**12.2 Persistence and degradability**

no data available

**12.3 Bioaccumulative potential**

Partition coefficient: n-octanol/water: -11.7 (20 °C; berechnet)

**12.4 Mobility in soil:**

no data available

**12.5 Results of PBT/vPvB assessment**

no data available



## 12.6 Other adverse effects

no data available

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### Appropriate disposal / Product

Dispose according to legislation. Consult the appropriate local waste disposal expert about waste disposal. Send to a hazardous waste incinerator facility under observation of official regulations.

Waste code product: 160508

#### Appropriate disposal / Package

Dispose according to legislation. Handle contaminated packages in the same way as the substance itself.

#### Additional information

no data available

## SECTION 14: Transport information

### Land transport (DOT)

No dangerous good in sense of this transport regulation.

### Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code  
not relevant

### Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

## SECTION 15: Regulatory information

### Safety, health and environmental regulations/legislation specific for the substance or mixture

#### SARA 313 Components

Not listed.

#### Massachusetts Right To Know Components

Not listed.

#### Pennsylvania Right To Know Components

Not listed.

#### **New Jersey Right To Know Components**

Not listed.

#### **California Prop. 65 Components**

Not listed.

## **SECTION 16: Other information**

### **Abbreviations and acronyms**

ACGIH - American Conference of Governmental Industrial Hygienists  
DOT - Department of Transportation  
IARC - International Agency for Research on Cancer  
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations  
ICAO-TI - International Civil Aviation Organization-Technical Instructions  
IMDG - International Maritime Code for Dangerous Goods  
LTV - Long Term Value  
NIOSH - National Institute for Occupational Safety and Health  
NTP - National Toxicology Program  
OSHA - Occupational Safety & Health Administration  
PBT - Persistent, Bioaccumulative and Toxic  
PEL - Permissible Exposure Limit  
STV - Short Term Value  
SVHC - Substances of Very High Concern  
TDG - Transport of Dangerous Goods  
TLV - Threshold Limit Value  
vPvB - very Persistent, very Bioaccumulative

### **Additional information**

Indication of changes:                      general update

*The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guidance. The information in this document is based on the present state knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and his Affiliates shall not be held liable for any damage resulting from handling.*