

# SAFETY DATA SHEET

According to US Regulation 29 CFR 1910.1200 (HazCom 2012)

## 1. Identification

**Product identifier:** Ammonium Acetate

### Other means of identification

**Synonyms:** Acetic acid, ammonium salt  
**Product No.:** 0596, 0599, 3272

### Recommended restrictions

**Recommended use:** For Laboratory, Research or Manufacturing Use.  
**Restrictions on use:** Not determined.

### Details of the supplier of the safety data sheet

**Company Name:** Avantor Performance Materials, LLC  
**Address:** 100 Matsonford Rd, Suite 200  
Radnor, PA 19087

**Telephone:** Customer Service: 855-282-6867

**Contact Person:** Product Information Compliance  
**E-mail:** info@avantormaterials.com

### Emergency telephone number:

CHEMTREC: 1-800-424-9300 within US and Canada (24 hrs/day, 7 days/week)

## 2. Hazard(s) identification

### Hazard Classification

Not classified

### Label Elements

**Hazard Symbol:** No symbol  
**Signal Word:** No signal word.  
**Hazard Statement:** Not applicable  
**Precautionary Statements** Not applicable

**Hazard(s) not otherwise classified (HNOC):** None.

## 3. Composition/information on ingredients

## Substances

Chemical Identity	CAS number	Content in percent (%)*
Ammonium acetate	631-61-8	97.00 - 100.00%

\* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

## 4. First-aid measures

<b>General information:</b>	Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.
<b>Ingestion:</b>	Rinse mouth thoroughly. Call a POISON CENTER/doctor if you feel unwell.
<b>Inhalation:</b>	Move to fresh air. Get medical attention if symptoms persist.
<b>Skin Contact:</b>	Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing. Wash contaminated clothing before reuse.
<b>Eye contact:</b>	Flush thoroughly with water. If irritation occurs, get medical assistance.

### Most important symptoms/effects, acute and delayed

<b>Symptoms:</b>	May cause irritation to skin, eyes and respiratory tract.
<b>Hazards:</b>	None known.

### Indication of immediate medical attention and special treatment needed

<b>Treatment:</b>	Treat symptomatically. Symptoms may be delayed.
-------------------	---

## 5. Fire-fighting measures

<b>General Fire Hazards:</b>	In case of fire and/or explosion do not breathe fumes.
------------------------------	--

### Suitable (and unsuitable) extinguishing media

<b>Suitable extinguishing media:</b>	Use fire-extinguishing media appropriate for surrounding materials.
<b>Unsuitable extinguishing media:</b>	None known.

<b>Specific hazards arising from the chemical:</b>	During fire, gases hazardous to health may be formed.
--	---

### Special protective equipment and precautions for firefighters

<b>Special fire fighting procedures:</b>	Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.
<b>Special protective equipment for fire-fighters:</b>	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

## 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures:</b>	Keep unauthorized personnel away. Use personal protective equipment. See Section 8 of the SDS for Personal Protective Equipment.
<b>Methods and material for containment and cleaning up:</b>	Sweep up and place in a clearly labeled container for chemical waste. Clean surface thoroughly to remove residual contamination.
<b>Notification Procedures:</b>	Prevent entry into waterways, sewer, basements or confined areas. Inform authorities if large amounts are involved.
<b>Environmental Precautions:</b>	Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

<b>7. Handling and storage</b>
--------------------------------

<b>Precautions for safe handling:</b>	Use personal protective equipment as required. Avoid contact with eyes, skin, and clothing. Avoid inhalation of dust. Wash thoroughly after handling.
<b>Conditions for safe storage, including any incompatibilities:</b>	Keep containers tightly closed. Store in cool, dry place. Store in a well-ventilated place.

<b>8. Exposure controls/personal protection</b>
---

**Control Parameters**

**Occupational Exposure Limits**

None of the components have assigned exposure limits.

**Appropriate Engineering Controls**

Provide sufficient ventilation for operations causing dust formation.

**Individual protection measures, such as personal protective equipment**

**General information:** Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

**Eye/face protection:** Use tight fitting goggles if dust is generated.

**Skin Protection**

**Hand Protection:** Wear protective gloves.

**Other:** Wear suitable protective clothing.

**Respiratory Protection:** In case of inadequate ventilation use suitable respirator.

**Hygiene measures:** Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Provide eyewash station and safety shower.

<b>9. Physical and chemical properties</b>
--

**Appearance**

<b>Physical state:</b>	Solid
<b>Form:</b>	Crystals
<b>Color:</b>	White
<b>Odor:</b>	Slight acetic acid odor
<b>Odor threshold:</b>	No data available.
<b>pH:</b>	6.7 - 7.3 (25 °C) (5% aqueous solution)
<b>Melting point/freezing point:</b>	114 °C
<b>Initial boiling point and boiling range:</b>	No data available.
<b>Flash Point:</b>	No data available.
<b>Evaporation rate:</b>	No data available.
<b>Flammability (solid, gas):</b>	No data available.
<b>Upper/lower limit on flammability or explosive limits</b>	
<b>Flammability limit - upper (%):</b>	No data available.
<b>Flammability limit - lower (%):</b>	No data available.
<b>Explosive limit - upper (%):</b>	No data available.
<b>Explosive limit - lower (%):</b>	No data available.
<b>Vapor pressure:</b>	0.01 kPa (25 °C)
<b>Vapor density:</b>	No data available.
<b>Density:</b>	1.07 mg/l (20 °C)
<b>Relative density:</b>	1.17 (20 °C)
<b>Solubility(ies)</b>	
<b>Solubility in water:</b>	1.4 g/ml (4 °C)
<b>Solubility (other):</b>	Alcohol: Soluble methanol: 0.0789 g/ml (15 °C) acetone: Slightly soluble
<b>Partition coefficient (n-octanol/water):</b>	No data available.
<b>Auto-ignition temperature:</b>	No data available.
<b>Decomposition temperature:</b>	No data available.
<b>Viscosity:</b>	No data available.
<b>Other information</b>	
<b>Molecular weight:</b>	77.08 g/mol (CH <sub>3</sub> CO <sub>2</sub> NH <sub>4</sub> )

**10. Stability and reactivity**

<b>Reactivity:</b>	No dangerous reaction known under conditions of normal use.
<b>Chemical Stability:</b>	Material is stable under normal conditions.
<b>Possibility of hazardous reactions:</b>	Hazardous polymerization does not occur.
<b>Conditions to avoid:</b>	Heat. Moisture. Contact with incompatible materials.
<b>Incompatible Materials:</b>	Strong oxidizing agents. Acids. Sodium hypochlorite.
<b>Hazardous Decomposition Products:</b>	ammonia Nitrogen Oxides

**11. Toxicological information**
**Information on likely routes of exposure**

**Inhalation:** May be harmful if inhaled. May cause irritation to the respiratory system.

**Skin Contact:** Prolonged skin contact may cause temporary irritation.

**Eye contact:** May cause temporary eye irritation.

**Ingestion:** May be harmful if swallowed. May cause irritation of the gastrointestinal tract.

**Information on toxicological effects**

**Acute toxicity (list all possible routes of exposure)**

**Oral**  
**Product:** LD 50 (Rat): 3,250 - 3,550 mg/kg

**Dermal**  
**Product:** LD 50 (Rabbit) > 20,000 mg/kg

**Inhalation**  
**Product:** No data available.

**Repeated dose toxicity**  
**Product:** No data available.

**Skin Corrosion/Irritation**  
**Product:** Prolonged skin contact may cause temporary irritation.

**Serious Eye Damage/Eye Irritation**  
**Product:** May cause temporary eye irritation.

**Respiratory or Skin Sensitization**  
**Product:** Not a skin nor a respiratory sensitizer.

**Carcinogenicity**  
**Product:** This substance has no evidence of carcinogenic properties.

**IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:**  
No carcinogenic components identified

**US. National Toxicology Program (NTP) Report on Carcinogens:**  
No carcinogenic components identified

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):**  
No carcinogenic components identified

**Germ Cell Mutagenicity**

**In vitro**  
**Product:** No mutagenic components identified

**In vivo**  
**Product:** No mutagenic components identified

**Reproductive toxicity**  
**Product:** No components toxic to reproduction

**Specific Target Organ Toxicity - Single Exposure**  
**Product:** No data available.

**Specific Target Organ Toxicity - Repeated Exposure**

**Product:** No data available.

**Aspiration Hazard**

**Product:** Not classified

**Other effects:** None known.

<b>12. Ecological information</b>
-----------------------------------

**Ecotoxicity:**

**Acute hazards to the aquatic environment:**

**Fish**

**Product:** No data available.

**Aquatic Invertebrates**

**Product:** No data available.

**Chronic hazards to the aquatic environment:**

**Fish**

**Product:** No data available.

**Aquatic Invertebrates**

**Product:** No data available.

**Toxicity to Aquatic Plants**

**Product:** No data available.

**Persistence and Degradability**

**Biodegradation**

**Product:** There are no data on the degradability of this product.

**BOD/COD Ratio**

**Product:** No data available.

**Bioaccumulative potential**

**Bioconcentration Factor (BCF)**

**Product:** No data available on bioaccumulation.

**Partition Coefficient n-octanol / water (log Kow)**

**Product:** No data available.

**Mobility in soil:** No data available.

**Other adverse effects:** The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

### 13. Disposal considerations

- Disposal instructions:** Discharge, treatment, or disposal may be subject to national, state, or local laws. Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.
- Contaminated Packaging:** Since emptied containers retain product residue, follow label warnings even after container is emptied.

### 14. Transport information

- DOT**  
Not regulated.
- IMDG**  
Not regulated.
- IATA**  
Not regulated.

### 15. Regulatory information

**US Federal Regulations**

**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**  
None present or none present in regulated quantities.

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)**  
None present or none present in regulated quantities.

**CERCLA Hazardous Substance List (40 CFR 302.4):**

<u>Chemical Identity</u>	<u>Reportable quantity</u>
Ammonium acetate	5000 lbs.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

**Hazard categories**  
Not classified

**SARA 302 Extremely Hazardous Substance**  
None present or none present in regulated quantities.

**SARA 304 Emergency Release Notification**  
None present or none present in regulated quantities.

**SARA 311/312 Hazardous Chemical**

<u>Chemical Identity</u>	<u>Threshold Planning Quantity</u>
Ammonium acetate	10000 lbs.

**SARA 313 (TRI Reporting)**

<u>Chemical Identity</u>	<u>Reporting threshold for other users</u>	<u>Reporting threshold for manufacturing and processing</u>
Ammonium acetate	10000 lbs.	25000 lbs.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):**  
None present or none present in regulated quantities.

**Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3):**

<u><b>Chemical Identity</b></u> Ammonium acetate	<u><b>Reportable quantity</b></u> Reportable quantity: 5000 lbs.
---	---

**US State Regulations**

**US. California Proposition 65**

No ingredient requiring a warning under CA Prop 65.

**US. New Jersey Worker and Community Right-to-Know Act**

**Chemical Identity**  
Ammonium acetate

**US. Massachusetts RTK - Substance List**

**Chemical Identity**  
Ammonium acetate

**US. Pennsylvania RTK - Hazardous Substances**

**Chemical Identity**  
Ammonium acetate

**US. Rhode Island RTK**

No ingredient regulated by RI Right-to-Know Law present.

**International regulations**

**Montreal protocol**

Not applicable

**Stockholm convention**

Not applicable

**Rotterdam convention**

Not applicable

**Kyoto protocol**

Not applicable


**Inventory Status:**

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Japan (ENCS) List:	Not in compliance with the inventory.
Japan ISHL Listing:	Not in compliance with the inventory.
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Mexico INSQ:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Philippines PICCS:	On or in compliance with the inventory
Taiwan Chemical Substance Inventory:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory

**16. Other information, including date of preparation or last revision**



**NFPA Hazard ID**



Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe; RNP - Rating not possible

<b>Issue Date:</b>	07-23-2020
<b>Revision Information:</b>	Not relevant.
<b>Version #:</b>	1.2
<b>Source of information:</b>	Sources of information used in preparing this SDS included one or more of the following: results from in house or supplier toxicology studies, information from the Toxicology Data Network (TOXNET), European Chemical Agency (ECHA) substance dossiers, IARC Monographs, US National Toxicology Program data, the Agency for Toxic Substances and Disease Registry, other manufacturer’s SDSs and other sources, as appropriate.
<b>Further Information:</b>	No data available.
<b>Disclaimer:</b>	The information provided in this Safety Data Sheet (SDS) was prepared based on data believed to be accurate as of the date of this SDS. TO THE GREATEST EXTENT PERMITTED BY LAW, AVANTOR PERFORMANCE MATERIALS (“AVANTOR”) EXPRESSLY DISCLAIMS ANY AND ALL REPRESENTATIONS AND WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN INCLUDING, WITHOUT LIMITATION, AS TO ACCURACY, COMPLETENESS, FITNESS FOR PURPOSE OR USE, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY AND STABILITY. This SDS is intended as a guide to the appropriate use, handling, storage and disposal of the product to which it relates by properly trained personnel, and is not intended to be comprehensive. Users of Avantor’s products are advised to perform their own tests and to exercise their own judgment to determine the safety, suitability and appropriate use, handling, storage and disposal of each product and product combination for their own purposes and uses. TO THE GREATEST EXTENT PERMITTED BY LAW, AVANTOR DISCLAIMS LIABILITY FOR, AND BY USING AVANTOR’S PRODUCTS PURCHASER AGREES THAT UNDER NO CIRCUMSTANCES SHALL AVANTOR BE LIABLE FOR, SPECIAL, INDIRECT, INCIDENTAL , PUNITIVE OR CONSEQUENTIAL DAMAGES OF ANY TYPE OR KIND, INCLUDING WITHOUT LIMITATION, FOR LOSS OF PROFITS, REPUTATIONAL DAMAGE, PRODUCT RECALL OR BUSINESS INTERRUPTION.