Clzyme RI Revision 16 Dec 2016



Section	1. Identification
Product Name	Clzyme RI
<b>Product Code</b>	005-1030
Chemical Name	Purified Collagenase from <i>Clostridium hystolyticum</i> blended with purified neutral protease from <i>Paenibacillus polymyxa</i>
Synonyms	Collagenase Blend and Neutral Protease
Intended Application	Purified enzyme for the release of cells from a tissue matrix
Manufacturer	VitaCyte, LLC
	1341 Sadlier Circle West Drive
	Indianapolis, IN 46239
Technical Phone #	317-917-3457

Section	2. Hazard(s) Identification
Hazard Classification	GHS Classification in accordance with 2012 OSHA Hazard Communication Standard (29 CFR
	1910.1200)

Skin Irritation (Category 2), H315 Eye Irritation (Category 2A), H319

Respiratory Sensitization (Category 1), H334

Specific Target Organ Toxicity – Single Exposure (Category 3), Respiratory System, H335

Pictograms





Signal Word Danger

**Hazard Statements** 

**H315** Causes skin irritation

**H319** Causes serious eye irritation

H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled

**H335** May cause respiratory irritation

**Precautionary Statements** 

**P261** Avoid breathing dust/fume/gas/mist/spray.

P264 Wash skin thoroughly after handling.

**P271** Use only outdoors or in a well-ventilated area.

**P280** Wear eye protection/ face protection.

**P280** Wear protective gloves.

**P285** In case of inadequate ventilation wear respiratory protection.

**P302 + P352** IF ON SKIN: Wash with plenty of soap and water.

P304 + P340 + P312 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Call a POISON CENTER or doctor/ physician if you feel unwell.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and

easy to do. Continue rinsing.

P332 + P313 If skin irritation occurs: Get medical advice/attention.

## **SAFETY DATA SHEET**

Clzyme RI Revision 16 Dec 2016

**P337 + P313** If eye irritation occurs: Get medical advice/attention.

**P342 + P311** If experiencing respiratory symptoms: Call a POISON CENTER or doctor/physician.

P362 Take off contaminated clothing and wash before reuse.

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P501 Dispose of contents/container to an approved waste disposal plant.

Section	3. Composition/In	formation on Ingredients	
Component		CAS-No	Weight %
Purified Collagenase		9001-12-1	5-10 %
Purified B. polymyxa Neutral Protease		42613-33-2	1-5 %
Non-reactive stabilizing agent		Trade Secret	85-94 %

Section	4. First-Aid Measures
Eyes	In case of contact, immediately wash eyes with copious amounts of water for at least 15 minutes.
Skin	In case of contact, wash skin with soap and copious amounts of water. Remove contaminated clothing and shoes.
Inhalation	If swallowed, wash out mouth with water provided person is conscious. Call a physician.
Ingestion	Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Call Poison Control Center or seek medical attention.

Section	5. Fire-Fighting Measures
Suitable Extinguishing Media	Water spray, carbon dioxide, dry chemical powder, or appropriate foam
Unsuitable Extinguishing Media	No information available
<b>Autoignition Temperature</b>	Not applicable
<b>Explosion Hazard</b>	No information available
Hazardous Combustion Products	Carbon monoxide, carbon dioxide
Firefighting Precautions	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear
NFPA Rating	Health 2 / Flammability 0 / Instability 0 / Physical Hazards N/A

Section	6. Accidental Release Measures
Personal Precaution	Keep bottle tightly closed and avoid forming dust.
<b>Emergency Procedures</b>	Ventilate area and evacuate personnel to safe area.
Containment	Soak up liquid with absorbent material and place contaminated material in appropriate sealed container for waste disposal.
Clean-Up	Wash spill site after containment is complete.
Section	7. Handling and Storage
Handling	Avoid dust formation. Do not get in eyes, on skin, on clothing, or breathe dust.

Section	7. Handling and Storage
Handling	Avoid dust formation. Do not get in eyes, on skin, on clothing, or breathe dust.
Storage	Keep in a tightly closed container at -20°C or colder.

Section	8. Exposure Controls/Personal Protection
Permissible Exposure Limits	This product does not have occupational exposure limits.
<b>Engineering Controls</b>	Safety shower, eye wash station and mechanical exhaust system
Eye Protection	Chemical safety goggles or appropriate eye protection
Skin Protection	Compatible chemical-resistant gloves

## **SAFETY DATA SHEET**

Revision 16 Dec 2016 Clzyme RI

**Respiratory Protection** Respiratory protection is not required under normal use of this product. If respiratory protection is

needed use a government approved respirator.

Hygiene Wash thoroughly after handling

Section 9. Physical and Chemical Properties

> White to off-white lyophilized cake **Appearance**

**Physical State** Solid 6 - 8pН

**Molecular Weight** ~115 kDa and ~37 kDa

**Boiling Point/Range** Not determined Melting Point/Range Not determined **Freezing Point** Not determined **Vapor Pressure** Not determined **Vapor Density** Not determined **Evaporation Rate** Not determined **Specific Gravity** Not determined

> Solubility Soluble in water, limit not determined

**Section** 10. Stability and Reactivity

> **Reactive Hazard** None known, based on information available

Stable under ordinary conditions of storage and use Stability

**Conditions to Avoid** Heat and extreme pH

**Incompatible Materials** Strong oxidizing agents, strong acids and bases **Hazardous Decomposition** Nature of decomposition products not known

**Hazardous Polymerization** None under normal processing **Hazardous Reactions** None under normal processing

**Section** 11. Toxicological Information

**Routes of Exposure** Ingestion, inhalation, skin and/or eye contact

No information available **Acute Toxicity Chronic Toxicity** No information available

IARC Carcinogenicity Collagenase

NTP **OSHA ACGIH** Not listed Not listed Not listed Not listed Glycylglycine Not listed Not listed Not listed Not listed Not listed **Calcium Chloride** Not listed Not listed Not listed

Symptoms both acute and delayed

May cause skin, lung and eye irritation. May be harmful if absorbed through the skin, ingested or inhaled.

12. ECOLOGICAL INFORMATION Section

> **Ecotoxicity** No information available

Persistence Unlikely based on information available

**Bioaccumulation** No information available

Mobility Likely to be mobile in the environment due to solubility in water

Section 13. DISPOSAL CONSIDERATIONS

> **Waste Disposal** Recovery or recycling should be managed in an appropriate and approved waste disposal facility.

Processing, use or contamination of this product may change the waste management options. State and local disposal regulations may differ from federal disposal regulations. Dispose of

## **SAFETY DATA SHEET**

Clzyme RI Revision 16 Dec 2016

container and unused contents in accordance with federal, state and local requirements.

Section	14. TRANSPORT INFORMATION
DOT	US, Not regulated
TDG	Canada, Not regulated
IATA	International Air Transport Association, Not regulated
IMDG/IMO	International Maritime Dangerous Goods, Not regulated

15. REGULATORY INFORMATION
Not applicable
Not applicable
Not applicable
Acute health hazard
Not listed
Not listed

**European Union EINECS** 232-582-9/233-966-6 International NLP **ELINCS ENCS** AICS PICCS **IECSC** KECL Not listed Not listed Not listed Not listed Not listed Listed Not listed

Section	16. OTHER
Prepared By	VitaCyte Regulatory Affairs (info@vitacyte.com)
<b>Creation Date</b>	10 Nov 2011
<b>Revision Date</b>	4 Mar 2016
Summary	This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).
Disclaimer	The information provided on this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.