OVitaCyte^{*} Unravelling Cell Isolation

Section	1. Identification			
Product Name	Collagenase Gold			
Product Code	011-1060, 011-1160			
Chemical Name	Enriched Collagenase from Clostridium hystolyticum			
Synonyms	Collagenase, ColG, ColH			
Intended Application	Enzyme for the release of cells from a tissue matrix			
Manufacturer	VitaCyte, LLC			
	1341 Sadlier Circle West Drive			
	Indianapolis, IN 46239			
Technical Phone #	317-917-3457			
• •				
Section	2. Hazard(s) Identification			
Hazard Classification	GHS Classification in accordance with 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)			
	Skin Irritation (Category 2), H315			
	Eye Irritation (Category 2A), H319			
	Respiratory Sensitization (Category 1), H334			
	Specific Target Organ Toxicity – Single Exposure (Category 3), Respiratory System , H335			
Signal Word	Danger			
Hazard Statements				
H315	Causes skin irritation			
H319	Causes serious eye irritation			
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled			
H335	May cause respiratory irritation			
Precautionary Statements				
P261	Avoid breathing dust/fume/gas/mist/spray.			
P264	Wash skin thoroughly after handling.			
P271	Use only outdoors or in a well-ventilated area.			
P280	Wear eye protection/ face protection.			
P280	Wear protective gloves.			
P285	In case of inadequate ventilation wear respiratory protection.			
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.			
P304 + P340 + P312	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/ physician if you feel unwell.			
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.			
P332 + P313	If skin irritation occurs: Get medical advice/attention.			
P337 + P313	If eye irritation occurs: Get medical advice/attention.			
	PAGE 1 OF 4			

SAFETY DATA SHEET

Collagenase Go	ld
-----------------------	----

P342 + P311	If experiencing respiratory symptoms: Call a POISON CENTER or doctor/physician.
P362	Take off contaminated clothing and wash before reuse.
P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.

P501 Dispose of contents/container to an approved waste disposal plant.

Section	3. Composition/Information on Ingredients			
Component	CA	AS-No Weigh	t %	
Enriched Collagen	se 900	20-40	%	
Non-reactive stabilizin	g agent Trade	e Secret 60-80	%	

Section	4. First-Aid Measures
Eyes	In case of contact, immediately wash eyes with copious amounts of water for at least 15 minutes.
Skin	In case of contact, wash skin with soap and copious amounts of water. Remove contaminated clothing and shoes.
Inhalation	If swallowed, wash out mouth with water provided person is conscious. Call a physician.
Ingestion	Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Call Poison Control Center or seek medical attention.

Section	5. Fire-Fighting Measures
Suitable Extinguishing Media	Water spray, carbon dioxide, dry chemical powder, or appropriate foam
Unsuitable Extinguishing Media	No information available
Autoignition Temperature	Not applicable
Explosion Hazard	No information available
Hazardous Combustion Products	Carbon monoxide, carbon dioxide
Firefighting Precautions	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear
NFPA Rating	Health 2 / Flammability 0 / Instability 0 / Physical Hazards N/A
Section	6. Accidental Release Measures
Personal Precaution	Keep bottle tightly closed and avoid forming dust.
Emergency Procedures	Ventilate area and evacuate personnel to safe area.
Containment	Soak up liquid with absorbent material and place contaminated material in appropriate sealed container for waste disposal.
Clean-Up	Wash spill site after containment is complete.
Section	7. Handling and Storage
	Avoid dust formation. Do not get in avoc, on skip, on slothing, or broathe dust

HandlingAvoid dust formation. Do not get in eyes, on skin, on clothing, or breathe dust.StorageKeep in a tightly closed container at -20°C or colder.

Section	8. Exposure Controls/Personal Protection
Permissible Exposure Limits	This product does not have occupational exposure limits.
Engineering Controls	Safety shower, eye wash station and mechanical exhaust system
Eye Protection	Chemical safety goggles or appropriate eye protection
Skin Protection	Compatible chemical-resistant gloves
Respiratory Protection	Respiratory protection is not required under normal use of this product. If respiratory protection is needed use a government approved respirator.

SAFETY DATA SHEET

Collagenase Gold

Revision 16 Dec 2016

Wash thoroughly after handling

Section	9. Physical and Chem	9. Physical and Chemical Properties				
Appearance	White to off-white lyophilized cake					
Physical State	Solid					
рН	6 – 8	6 – 8				
Molecular Weight	~115 kDa	~115 kDa				
Boiling Point/Range	Not determined					
Melting Point/Range	Not determined					
Freezing Point	Not determined					
Vapor Pressure	Not determined					
Vapor Density	Not determined					
Evaporation Rate	Not determined					
Specific Gravity	Not determined					
Solubility	Soluble in water, limit no	ot determined				
Section	10. Stability and Read	tivity				
Reactive Hazard	None known, based on i					
Stability		onditions of storage and us	se			
Conditions to Avoid	Heat and extreme pH					
Incompatible Materials	Strong oxidizing agents,	strong acids and bases				
Hazardous Decomposition	Nature of decomposition	-				
Hazardous Polymerization	None under normal proc	•				
Hazardous Reactions		-				
	None under normal processing					
Section	11. Toxicological Info	rmation				
Routes of Exposure	Ingestion, inhalation, ski	in and/or eye contact				
Acute Toxicity	No information available	9				
Chronic Toxicity	No information available	2				
Carcinogenicity	IARC	NTP	OSHA	ACGIH		
Collagenase	Not listed	Not listed	Not listed	Not listed		
Collagenase Glycylglycine	Not listed Not listed	Not listed Not listed	Not listed Not listed	Not listed Not listed		
-						
Glycylglycine	Not listed Not listed	Not listed	Not listed Not listed	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and	Not listed Not listed May cause skin, lung and	Not listed Not listed d eye irritation. May be ha	Not listed Not listed	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed	Not listed Not listed May cause skin, lung and inhaled.	Not listed Not listed d eye irritation. May be ha	Not listed Not listed	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed Section	Not listed Not listed May cause skin, lung and inhaled. 12. ECOLOGICAL INFO	Not listed Not listed d eye irritation. May be ha	Not listed Not listed	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed Section Ecotoxicity	Not listed Not listed May cause skin, lung and inhaled. 12. ECOLOGICAL INFO No information available	Not listed Not listed d eye irritation. May be ha DRMATION e nation available	Not listed Not listed	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed Section Ecotoxicity Persistence	Not listed Not listed May cause skin, lung and inhaled. 12. ECOLOGICAL INFC No information available Unlikely based on inform No information available	Not listed Not listed d eye irritation. May be ha DRMATION e nation available	Not listed Not listed Irmful if absorbed through	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed Section Ecotoxicity Persistence Bioaccumulation Mobility	Not listed Not listed May cause skin, lung and inhaled. 12. ECOLOGICAL INFO No information available Unlikely based on inform No information available Likely to be mobile in the	Not listed Not listed d eye irritation. May be ha DRMATION e nation available e environment due to solu	Not listed Not listed Irmful if absorbed through	Not listed Not listed		
Glycylglycine Calcium Chloride Symptoms both acute and delayed Section Ecotoxicity Persistence Bioaccumulation	Not listed Not listed May cause skin, lung and inhaled. 12. ECOLOGICAL INFC No information available Unlikely based on inform No information available Likely to be mobile in the 13. DISPOSAL CONSIL	Not listed Not listed d eye irritation. May be ha DRMATION e nation available e environment due to solu	Not listed Not listed Irmful if absorbed through	Not listed Not listed In the skin, ingested or		

SAFETY DATA SHEET

Revision 16 Dec 2016

Collagenase Gold

Section	14. TRANSPORT INFORMATION
DOT	US, Not regulated
TDG	Canada, Not regulated
ΙΑΤΑ	International Air Transport Association, Not regulated
IMDG/IMO	International Maritime Dangerous Goods, Not regulated

Section	15. REGULATORY INFORMATION						
US Federal TSCA 12(b)	Not applicabl	lot applicable					
US Federal CERCLA	Not applicabl	Not applicable					
US Federal SARA 313	Not applicabl	Not applicable					
US Federal 311/312 (US)	Acute health	Acute health hazard					
California Prop 65	Not listed						
Canada DSL/NDSL	Not listed	Not listed					
European Union EINECS	232-582-9						
International	NLP	ELINCS	ENCS	AICS	PICCS	IECSC	KECL
	Not listed	Not listed	Not listed	Not listed	Not listed	Listed	Not listed

Section	16. OTHER
Prepared By	VitaCyte Regulatory Affairs (info@vitacyte.com)
Creation Date	7 Mar 2016
Revision Date	
Summary	This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).
Disclaimer	The information provided on this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.