



3170 Metro Parkway  
Ft. Myers, FL 33916 USA

Telephone: 888-203-7248

CHEMTREC® 24 hr Emergency: US 800-424-9300;  
CHEMTREC® 24 hr Emergency: International 703-527-3887

## Safety Data Sheet

### 1. PRODUCT IDENTIFICATION: 2.0 ppm Reference Standard Solution

Catalog Numbers-HF scientific: 10451 10451A 10453

PRODUCT USE: Analytical \ Laboratory Reagent

NFPA RATINGS: HEALTH: 1 FLAMMABILITY: 0 REACTIVITY: 0

### 2. HAZARDS IDENTIFICATION

TARGET ORGANS: Skin, Eyes, Central Nervous System, Liver, Kidneys

ACUTE TOXICITY: May Cause Skin or Eye Irritation

CHRONIC TOXICITY: Ingestion of Large Amounts May Affect Liver or Kidneys

MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE: Pre-existing Skin or Eye Problems

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Component		Percent
Component	Preservative	< 0.1
CAS No.	Confidential	
Component	Dye	< 0.1
CAS No.	Confidential	
Component	Deionized Water	>99
CAS No.	7732-18-5	

### 4. FIRST AID MEASURES

EYE CONTACT: Immediately Flush with Excess Water for 15 Minutes

SKIN CONTACT: Immediately Flush with Excess Water for 15 Minutes. Remove Contaminated Clothing.

INHALATION: Remove to Fresh Air

INGESTION: Give Large Quantities of Water. Call Physician.

### 5. FIRE FIGHTING MEASURES

FLASH POINT: NA AUTOIGNITION POINT: NA

FLAMMABILITY LIMITS: UPPER: NA LOWER: NA

EXTINGUISHING MEDIA: Foam or Dry Chemical

### 6. ACCIDENTAL RELEASE MEASURES

Wear Proper Personal Protective Equipment. See Section 8 for Additional Information. Remove Liquid with Absorbent Material and Seal in a Bag or Container for Disposal. Wash Spill Area Once Pickup is Complete.

### 7. HANDLING AND STORAGE

HANDLING: Wear Safety Glasses, Latex or Nitrile Gloves, and Lab Coat or Apron.

Avoid Contact with Skin and Eyes. Do Not Ingest.

STORAGE: Store at Room Temperature.

### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

PERSONAL PROTECTIVE EQUIPMENT: Safety Glasses, Latex or Nitrile Gloves, and Lab Coat or Apron.

### 9. PHYSICAL AND CHEMICAL PROPERTIES

PHYSICAL STATE: Liquid

COLOR: Red Solution

ODOR: Odorless

FLASH POINT: NA

FLAMMABLE LIMITS: NA

AUTOIGNITION TEMPERATURE: NA

VAPOR PRESSURE: (mm Hg): 760mm

SPECIFIC GRAVITY: 1.0

BOILING POINT: 100 °C, 212 °F

FREEZING POINT: 0°C, 32°F

MELTING POINT: NA

SOLUBILITY IN WATER: Soluble

pH: Neutral (6.5-7.5)

### 10. STABILITY AND REACTIVITY

Product Stable Under General Use and Storage Conditions. No Hazardous Polymerization Will Occur.

### 11. TOXICOLOGICAL INFORMATION

Route of Exposure: Skin, Eyes, Ingestion

Teratogen Status: None Reported

Mutagen Status: None Reported

Reproductive Toxicity: None Reported

### 12. ECOLOGICAL INFORMATION

No Ecological Data Available

### 13. DISPOSAL CONSIDERATIONS

Dispose of in a manner consistent with Federal, State and Local Regulations.

### 14. TRANSPORT INFORMATION

US DOT (United States Department of Transportation): Not Regulated

IATA (International Air Transport Association): Not Regulated

IMO (International Maritime Organization): Not Regulated

### 15. REGULATORY INFORMATION

HAZARD CODES: Xi Irritant

RISK STATEMENTS: 36, 38 Irritating to the Eyes, Irritating to the Skin

SARA/Title III: No

TSCA Inventory: Yes

Cal. Proposition 65: No

WHMIS: No

DSL: No

NDSL: No

### 16. OTHER INFORMATION

THE ABOVE INFORMATION IS BELIEVED TO BE ACCURATE AND REPRESENTS THE BEST INFORMATION CURRENTLY AVAILABLE TO US. ALL PRODUCTS ARE OFFERED IN ACCORDANCE WITH THE MANUFACTURER'S CURRENT PRODUCTION SPECIFICATIONS AND ARE INTENDED SOLELY FOR USE IN ANALYTICAL TESTING. THE MANUFACTURER SHALL IN NO EVENT BE LIABLE FOR ANY INJURY, LOSS OR DAMAGE RESULTING FROM THE HANDLING, USE OR MISUSE OF THESE PRODUCTS.